

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219567

Luminaire Tested: **MRZ-1-REC-X-4-L35-80-NFL-UNV-X-STD**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219567
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14859)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-4-L35-80-NFL-UNV-X-STD
Description: MRZ INTEGRAL LED DOWNLIGHT
25 DEGREE NARROW FLOOD OPTIC, LIGHT LEVEL 4
Light Source: (1) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1676.1 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.37
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219567

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-NFL-UNV-X-STD

Luminous Intensity Polar Plot





TEST NUMBER: P219567

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-NFL-UNV-X-STD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91	88	86	85
6	99	93	89	86	98	92	88	86	91	88	85		90	87	85		88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	83		87	84	82		86	84	82	81
8	94	87	83	81	93	87	83	81	86	83	80		85	82	80		84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82	80	78	77
10	89	83	79	76	89	83	79	76	82	78	76		81	78	76		81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4277403
5°	3878216
10°	2840116
15°	1158050
20°	395095
25°	230982
30°	129038
35°	69386
40°	37098
45°	24142
50°	10285
55°	6623
60°	3750
65°	2218
70°	2741
75°	3622
80°	0
85°	0



TEST NUMBER: P219567

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-NFL-UNV-X-STD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	677.7	40.4
10°-20°	685.1	40.9
20°-30°	200.1	11.9
30°-40°	76.6	4.6
40°-50°	25.7	1.5
50°-60°	7.0	0.4
60°-70°	2.6	0.2
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1562.9	93.2
0°-40°	1639.5	97.8
0°-60°	1672.3	99.8
0°-90°	1676.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1676.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8670	
5°	7831	678
15°	2267	685
25°	424	200
35°	115	77
45°	35	26
55°	8	7
65°	2	3
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P219567

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-NFL-UNV-X-STD

CANDELA DISTRIBUTION (FULL):

	0°
0°	8669.6
2.5°	8469.9
5°	7830.6
7.5°	6855.4
10°	5669.0
12.5°	4050.7
15°	2267.2
17.5°	1203.7
20°	752.5
22.5°	558.6
25°	424.3
27.5°	316.8
30°	226.5
32.5°	163.2
35°	115.2
37.5°	80.6
40°	57.6
42.5°	44.2
45°	34.6
47.5°	21.1
50°	13.4
52.5°	9.6
55°	7.7
57.5°	5.8
60°	3.8
62.5°	3.8
65°	1.9
67.5°	1.9
70°	1.9
72.5°	1.9
75°	1.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)