

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219877

Luminaire Tested: **MRZ-1-REC-X-4-L35-80-WFL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219877
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14881)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-4-L35-80-WFL-UNV-X-STD-HEX
Description: MRZ INTEGRAL LED DOWNLIGHT
55 DEGREE WIDE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 4
Light Source: (1) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 727.9 lumens
Efficiency: N/A
Efficacy: 46.1 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.67
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219877

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-WFL-UNV-X-STD-HEX

Luminous Intensity Polar Plot





TEST NUMBER: P219877

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-WFL-UNV-X-STD-HEX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	81	78	84	80	78	83	79	77	76
6	92	84	78	75	90	83	78	74	82	77	74	80	76	73	79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62
10	78	69	64	61	77	69	64	60	68	63	60	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	703757
5°	665536
10°	588614
15°	476562
20°	362858
25°	268599
30°	172792
35°	91370
40°	39545
45°	14722
50°	5910
55°	3269
60°	1875
65°	2218
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P219877

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-WFL-UNV-X-STD-HEX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.0	16.9
10°-20°	256.9	35.3
20°-30°	224.0	30.8
30°-40°	99.2	13.6
40°-50°	19.5	2.7
50°-60°	4.0	0.6
60°-70°	1.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	603.9	83.0
0°-40°	703.2	96.6
0°-60°	726.8	99.8
0°-90°	727.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	727.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1426	
5°	1344	123
15°	933	257
25°	493	224
35°	152	99
45°	21	20
55°	4	4
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P219877

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-WFL-UNV-X-STD-HEX

CANDELA DISTRIBUTION (FULL):

0°	
0°	1426.4
2.5°	1397.6
5°	1343.8
7.5°	1270.9
10°	1174.9
12.5°	1057.8
15°	933.0
17.5°	802.4
20°	691.1
22.5°	593.2
25°	493.4
27.5°	397.4
30°	303.3
32.5°	218.8
35°	151.7
37.5°	97.9
40°	61.4
42.5°	34.6
45°	21.1
47.5°	13.4
50°	7.7
52.5°	5.8
55°	3.8
57.5°	3.8
60°	1.9
62.5°	1.9
65°	1.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)