

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219939

Luminaire Tested: **MRZ-1-REC-X-4-L35-80-WFL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219939  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14883)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-4-L35-80-WFL-UNV-X-STD-SFL  
Description: MRZ INTEGRAL LED DOWNLIGHT  
55 DEGREE WIDE FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL 4  
Light Source: (1) 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1465.3 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.9  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 15.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219939

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-WFL-UNV-X-STD-SFL

### Luminous Intensity Polar Plot





TEST NUMBER: P219939

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-WFL-UNV-X-STD-SFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	69	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	725515
5°	720708
10°	693421
15°	639348
20°	575553
25°	506876
30°	411214
35°	300611
40°	205262
45°	135293
50°	88423
55°	56170
60°	36017
65°	22415
70°	16589
75°	11056
80°	5398
85°	0



TEST NUMBER: P219939

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-WFL-UNV-X-STD-SFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.6	9.3
10°-20°	349.2	23.8
20°-30°	422.0	28.8
30°-40°	314.0	21.4
40°-50°	154.7	10.6
50°-60°	61.1	4.2
60°-70°	21.1	1.4
70°-80°	6.3	0.4
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	907.8	62.0
0°-40°	1221.8	83.4
0°-60°	1437.6	98.1
0°-90°	1465.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1465.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1470	
5°	1455	137
15°	1252	349
25°	931	422
35°	499	314
45°	194	155
55°	65	61
65°	19	21
75°	6	6
85°	0	0
90°	0	



TEST NUMBER: P219939

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-WFL-UNV-X-STD-SFL

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1470.5
2.5°	1464.8
5°	1455.2
7.5°	1426.4
10°	1384.1
12.5°	1322.7
15°	1251.7
17.5°	1173.0
20°	1096.2
22.5°	1019.4
25°	931.1
27.5°	831.2
30°	721.8
32.5°	608.6
35°	499.1
37.5°	403.1
40°	318.7
42.5°	249.6
45°	193.9
47.5°	149.7
50°	115.2
52.5°	86.4
55°	65.3
57.5°	48.0
60°	36.5
62.5°	26.9
65°	19.2
67.5°	15.4
70°	11.5
72.5°	7.7
75°	5.8
77.5°	3.8
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)