

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702614

Luminaire Tested: 340-6C-30-D010 / 340-EU4C-3040-9035-4LBW1LI-GFF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-14)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-30-D010 / 340-EU4C-3040-9035-4LBW1LI-GFF
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, FROSTED OUTSIDE KIT.
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1988.4 lumens
Efficiency: N/A
Efficacy: 62.9 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.63
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702614

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9035-4LBW1LI-GFF

Luminous Intensity Polar Plot



TEST NUMBER: P702614

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9035-4LBW1LI-GFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109		104	104	104		99	99	99	96
1	107	102	97	93	104	99	95	91	94	91	88		90	87	84		85	83	81	79
2	98	89	82	77	95	87	81	75	83	78	73		79	75	71		76	72	69	66
3	90	79	71	65	87	77	70	64	74	68	62		71	65	61		68	63	59	57
4	83	71	63	56	80	70	62	56	67	60	54		64	58	53		61	56	52	50
5	77	65	56	49	75	63	55	49	61	54	48		58	52	47		56	51	47	44
6	72	59	50	44	70	58	50	44	56	49	43		54	47	43		52	46	42	40
7	67	54	46	40	65	53	45	40	51	44	39		50	43	39		48	43	38	36
8	63	50	42	37	61	49	42	36	48	41	36		46	40	36		45	39	35	33
9	60	47	39	34	58	46	39	34	45	38	33		43	37	33		42	37	33	31
10	56	44	36	31	55	43	36	31	42	35	31		41	35	31		40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112077
5°	99400
10°	82843
15°	46364
20°	30984
25°	23941
30°	19352
35°	16134
40°	14378
45°	13186
50°	12028
55°	10785
60°	9624
65°	8320
70°	7132
75°	6041
80°	5127
85°	4280

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13186 cd/sqm

TEST NUMBER: P702614

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9035-4LBW1LI-GFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	7.9
10°-20°	275.0	13.8
20°-30°	252.2	12.7
30°-40°	250.7	12.6
40°-50°	260.4	13.1
50°-60°	250.3	12.6
60°-70°	209.4	10.5
70°-80°	154.4	7.8
80°-90°	104.5	5.3
90°-100°	60.6	3.0
100°-110°	12.6	0.6
110°-120°	0.3	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	685.0	34.5
0°-40°	935.8	47.1
0°-60°	1446.5	72.7
0°-90°	1914.9	96.3
90°-120°	73.5	3.7
90°-150°	73.5	3.7
90°-180°	74.0	3.7
0°-180°	1988.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1718	
5°	1698	158
15°	937	275
25°	544	252
35°	396	251
45°	337	260
55°	279	250
65°	211	209
75°	146	154
85°	95	83
90°	75	42
95°	58	41
105°	10	13
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702614

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9035-4LBW1LI-GFF

CANDELA DISTRIBUTION (FULL):

0°	
0°	1717.9
2.5°	1715.4
5°	1698.4
7.5°	1659.6
10°	1550.4
12.5°	1252.0
15°	936.6
17.5°	769.2
20°	667.2
22.5°	596.9
25°	543.5
27.5°	499.8
30°	458.6
32.5°	422.2
35°	395.5
37.5°	376.1
40°	361.5
42.5°	349.4
45°	337.3
47.5°	325.1
50°	310.6
52.5°	296.0
55°	279.0
57.5°	264.5
60°	247.5
62.5°	228.1
65°	211.1
67.5°	194.1
70°	177.1
72.5°	160.1
75°	145.6
77.5°	131.0
80°	118.9
82.5°	106.8
85°	94.6
87.5°	84.9
90°	75.2
92.5°	67.9
95°	58.2
97.5°	43.7
100°	29.1
102.5°	17.0
105°	9.7
107.5°	4.9
110°	2.4

TEST NUMBER: P702614

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9035-4LBW1LI-GFF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)