

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702628

Luminaire Tested: 340-6C-30-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702628  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-30-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF  
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, FROSTED OUTSIDE KIT.  
Light Source: 5000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2031.9 lumens  
Efficiency: N/A  
Efficacy: 64.3 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.63  
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')  
CIE Type: Direct

Input Watts (W): 31.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702628

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF

### Luminous Intensity Polar Plot



TEST NUMBER: P702628

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109		104	104	104		99	99	99	96
1	107	102	97	93	104	99	95	91	94	91	88		90	87	84		85	83	81	79
2	98	89	82	77	95	87	81	75	83	78	73		79	75	71		76	72	69	66
3	90	79	71	65	87	77	70	64	74	68	62		71	65	61		68	63	59	57
4	83	71	63	56	80	70	62	56	67	60	54		64	58	53		61	56	52	50
5	77	65	56	49	75	63	55	49	61	54	48		58	52	47		56	51	47	44
6	72	59	50	44	70	58	50	44	56	49	43		54	47	43		52	46	42	40
7	67	54	46	40	65	53	45	40	51	44	39		50	43	39		48	43	38	36
8	63	50	42	37	61	49	42	36	48	41	36		46	40	36		45	39	35	33
9	60	47	39	34	58	46	39	34	45	38	33		43	37	33		42	37	33	31
10	56	44	36	31	55	43	36	31	42	35	31		41	35	31		40	34	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	114523
5°	101578
10°	84654
15°	47374
20°	31662
25°	24465
30°	19774
35°	16485
40°	14693
45°	13472
50°	12292
55°	11021
60°	9834
65°	8502
70°	7289
75°	6173
80°	5239
85°	4375

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13472 cd/sqm

TEST NUMBER: P702628

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.4	7.9
10°-20°	281.0	13.8
20°-30°	257.7	12.7
30°-40°	256.2	12.6
40°-50°	266.1	13.1
50°-60°	255.8	12.6
60°-70°	214.0	10.5
70°-80°	157.8	7.8
80°-90°	106.8	5.3
90°-100°	61.9	3.0
100°-110°	12.9	0.6
110°-120°	0.3	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	700.0	34.5
0°-40°	956.2	47.1
0°-60°	1478.1	72.7
0°-90°	1956.7	96.3
90°-120°	75.2	3.7
90°-150°	75.2	3.7
90°-180°	75.0	3.7
0°-180°	2031.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1755	
5°	1736	161
15°	957	281
25°	555	258
35°	404	256
45°	345	266
55°	285	256
65°	216	214
75°	149	158
85°	97	84
90°	77	42
95°	60	42
105°	10	13
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702628

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1755.4
2.5°	1752.9
5°	1735.6
7.5°	1695.9
10°	1584.3
12.5°	1279.4
15°	957.0
17.5°	786.0
20°	681.8
22.5°	609.9
25°	555.4
27.5°	510.7
30°	468.6
32.5°	431.4
35°	404.1
37.5°	384.3
40°	369.4
42.5°	357.0
45°	344.6
47.5°	332.2
50°	317.4
52.5°	302.5
55°	285.1
57.5°	270.3
60°	252.9
62.5°	233.1
65°	215.7
67.5°	198.3
70°	181.0
72.5°	163.6
75°	148.8
77.5°	133.9
80°	121.5
82.5°	109.1
85°	96.7
87.5°	86.8
90°	76.9
92.5°	69.4
95°	59.5
97.5°	44.6
100°	29.8
102.5°	17.4
105°	9.9
107.5°	5.0
110°	2.5

TEST NUMBER: P702628

CATALOG NUMBER: 340-6C-30-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)