

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219556

Luminaire Tested: **MRZ-1-REC-X-2-L35-97-NFL-UNV-X-STD**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14859)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-2-L35-97-NFL-UNV-X-STD
Description: MRZ INTEGRAL LED DOWNLIGHT
25 DEGREE NARROW FLOOD OPTIC, LIGHT LEVEL2
Light Source: (1) 3500K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 729.9 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.37
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219556

CATALOG NUMBER: MRZ-1-REC-X-2-L35-97-NFL-UNV-X-STD

Luminous Intensity Polar Plot





TEST NUMBER: P219556

CATALOG NUMBER: MRZ-1-REC-X-2-L35-97-NFL-UNV-X-STD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	83	87	84	82	86	84	82	81
8	94	87	83	81	93	87	83	81	86	83	80	85	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77
10	89	83	79	76	89	83	79	76	82	78	76	81	78	76	81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1862853
5°	1688999
10°	1236896
15°	504348
20°	172057
25°	100602
30°	56230
35°	30236
40°	16166
45°	10466
50°	4529
55°	2839
60°	1677
65°	934
70°	1154
75°	1525
80°	0
85°	0



TEST NUMBER: P219556

CATALOG NUMBER: MRZ-1-REC-X-2-L35-97-NFL-UNV-X-STD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.1	40.4
10°-20°	298.3	40.9
20°-30°	87.2	11.9
30°-40°	33.4	4.6
40°-50°	11.2	1.5
50°-60°	3.1	0.4
60°-70°	1.1	0.2
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	680.6	93.2
0°-40°	714.0	97.8
0°-60°	728.3	99.8
0°-90°	729.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	729.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3776	
5°	3410	295
15°	987	298
25°	185	87
35°	50	33
45°	15	11
55°	3	3
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P219556

CATALOG NUMBER: MRZ-1-REC-X-2-L35-97-NFL-UNV-X-STD

CANDELA DISTRIBUTION (FULL):

0°	
0°	3775.7
2.5°	3688.7
5°	3410.3
7.5°	2985.6
10°	2468.9
12.5°	1764.1
15°	987.4
17.5°	524.2
20°	327.7
22.5°	243.3
25°	184.8
27.5°	138.0
30°	98.7
32.5°	71.1
35°	50.2
37.5°	35.1
40°	25.1
42.5°	19.2
45°	15.0
47.5°	9.2
50°	5.9
52.5°	4.2
55°	3.3
57.5°	2.5
60°	1.7
62.5°	1.7
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)