

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702662

Luminaire Tested: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702662  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC  
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C  
KIT.  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2485.2 lumens  
Efficiency: N/A  
Efficacy: 61.5 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74  
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')  
CIE Type: Direct

Input Watts (W): 40.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702662

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

### Luminous Intensity Polar Plot



TEST NUMBER: P702662

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	76	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	140313
5°	126036
10°	108726
15°	68551
20°	48956
25°	37596
30°	30290
35°	25480
40°	22480
45°	19223
50°	15433
55°	12019
60°	9449
65°	7465
70°	6033
75°	4808
80°	3898
85°	3067

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19223 cd/sqm

TEST NUMBER: P702662

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.5	8.1
10°-20°	399.7	16.1
20°-30°	396.0	15.9
30°-40°	394.5	15.9
40°-50°	376.6	15.2
50°-60°	281.0	11.3
60°-70°	190.5	7.7
70°-80°	124.2	5.0
80°-90°	75.5	3.0
90°-100°	39.4	1.6
100°-110°	5.3	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	998.1	40.2
0°-40°	1392.7	56.0
0°-60°	2050.3	82.5
0°-90°	2440.5	98.2
90°-120°	44.7	1.8
90°-150°	44.7	1.8
90°-180°	45.0	1.8
0°-180°	2485.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2151	
5°	2154	202
15°	1385	400
25°	854	396
35°	625	395
45°	492	377
55°	311	281
65°	189	191
75°	116	124
85°	68	60
90°	51	28
95°	37	26
105°	3	5
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702662

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2150.7
2.5°	2153.5
5°	2153.5
7.5°	2136.6
10°	2034.8
12.5°	1721.1
15°	1384.8
17.5°	1195.5
20°	1054.2
22.5°	941.1
25°	853.5
27.5°	780.0
30°	717.8
32.5°	664.1
35°	624.6
37.5°	593.5
40°	565.2
42.5°	534.1
45°	491.7
47.5°	446.5
50°	398.5
52.5°	353.3
55°	310.9
57.5°	274.1
60°	243.0
62.5°	214.8
65°	189.4
67.5°	169.6
70°	149.8
72.5°	132.8
75°	115.9
77.5°	101.7
80°	90.4
82.5°	79.1
85°	67.8
87.5°	59.3
90°	50.9
92.5°	45.2
95°	36.7
97.5°	28.3
100°	17.0
102.5°	8.5
105°	2.8
107.5°	0.0
110°	0.0

TEST NUMBER: P702662

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)