

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219925

Luminaire Tested: **MRZ-1-REC-X-2-L40-80-WFL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219925  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14883)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-2-L40-80-WFL-UNV-X-STD-SFL  
Description: MRZ INTEGRAL LED DOWNLIGHT  
55 DEGREE WIDE FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL2  
Light Source: (1) 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 850.2 lumens  
Efficiency: N/A  
Efficacy: 96.6 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.9  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 8.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219925

CATALOG NUMBER: MRZ-1-REC-X-2-L40-80-WFL-UNV-X-STD-SFL

### Luminous Intensity Polar Plot





TEST NUMBER: P219925

CATALOG NUMBER: MRZ-1-REC-X-2-L40-80-WFL-UNV-X-STD-SFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	69	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	421001
5°	418201
10°	402396
15°	370982
20°	333980
25°	294131
30°	238650
35°	174428
40°	119087
45°	78496
50°	51273
55°	32601
60°	20919
65°	12959
70°	9665
75°	6291
80°	3125
85°	0



TEST NUMBER: P219925

CATALOG NUMBER: MRZ-1-REC-X-2-L40-80-WFL-UNV-X-STD-SFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.2	9.3
10°-20°	202.6	23.8
20°-30°	244.9	28.8
30°-40°	182.2	21.4
40°-50°	89.8	10.6
50°-60°	35.5	4.2
60°-70°	12.2	1.4
70°-80°	3.7	0.4
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	526.8	62.0
0°-40°	708.9	83.4
0°-60°	834.2	98.1
0°-90°	850.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	850.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	853	
5°	844	79
15°	726	203
25°	540	245
35°	290	182
45°	112	90
55°	38	35
65°	11	12
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P219925

CATALOG NUMBER: MRZ-1-REC-X-2-L40-80-WFL-UNV-X-STD-SFL

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	853.3
2.5°	850.0
5°	844.4
7.5°	827.7
10°	803.2
12.5°	767.5
15°	726.3
17.5°	680.6
20°	636.1
22.5°	591.5
25°	540.3
27.5°	482.3
30°	418.9
32.5°	353.1
35°	289.6
37.5°	233.9
40°	184.9
42.5°	144.8
45°	112.5
47.5°	86.9
50°	66.8
52.5°	50.1
55°	37.9
57.5°	27.8
60°	21.2
62.5°	15.6
65°	11.1
67.5°	8.9
70°	6.7
72.5°	4.5
75°	3.3
77.5°	2.2
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)