

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P226185

Luminaire Tested: **MRZ-1-REC-X-1-L40-97-NFL-UNV-X-STD**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P226185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14859)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-1-L40-97-NFL-UNV-X-STD
Description: MRZ INTEGRAL LED DOWNLIGHT
25 DEGREE NARROW FLOOD OPTIC, LIGHT LEVEL 1
Light Source: (1) 4000K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 495.1 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.37
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 5.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P226185

CATALOG NUMBER: MRZ-1-REC-X-1-L40-97-NFL-UNV-X-STD

Luminous Intensity Polar Plot





TEST NUMBER: P226185

CATALOG NUMBER: MRZ-1-REC-X-1-L40-97-NFL-UNV-X-STD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	104	103	102	101	101	100	99	98	98	97	97	97	97
2	111	108	105	102	109	106	104	101	103	101	99	99	100	99	97	97	98	96	95	95	94	94	94	94
3	108	103	100	97	106	102	99	96	100	97	95	95	97	95	93	93	95	93	92	92	91	91	91	91
4	105	99	96	93	103	98	95	92	96	93	91	91	95	92	90	90	93	91	89	89	88	88	88	88
5	102	96	92	89	100	95	91	89	94	90	88	88	92	89	87	87	91	88	86	86	85	85	85	85
6	99	93	89	86	98	92	88	86	91	88	85	85	90	87	85	85	88	86	84	84	83	83	83	83
7	96	90	86	83	95	89	86	83	88	85	83	83	87	84	82	82	86	84	82	82	81	81	81	81
8	94	87	83	81	93	87	83	81	86	83	80	80	85	82	80	80	84	82	80	80	79	79	79	79
9	91	85	81	78	91	85	81	78	84	80	78	78	83	80	78	78	82	80	78	78	77	77	77	77
10	89	83	79	76	89	83	79	76	82	79	76	76	81	78	76	76	81	78	76	76	75	75	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1263644
5°	1145744
10°	839059
15°	342123
20°	116717
25°	68211
30°	38170
35°	20478
40°	11013
45°	7117
50°	2993
55°	1892
60°	1184
65°	584
70°	721
75°	953
80°	0
85°	0



TEST NUMBER: P226185

CATALOG NUMBER: MRZ-1-REC-X-1-L40-97-NFL-UNV-X-STD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.2	40.4
10°-20°	202.4	40.9
20°-30°	59.1	11.9
30°-40°	22.6	4.6
40°-50°	7.6	1.5
50°-60°	2.1	0.4
60°-70°	0.8	0.2
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	461.7	93.3
0°-40°	484.4	97.8
0°-60°	494.0	99.8
0°-90°	495.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	495.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2561	
5°	2313	200
15°	670	202
25°	125	59
35°	34	23
45°	10	8
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P226185

CATALOG NUMBER: MRZ-1-REC-X-1-L40-97-NFL-UNV-X-STD

CANDELA DISTRIBUTION (FULL):

	0°
0°	2561.2
2.5°	2502.3
5°	2313.4
7.5°	2025.2
10°	1674.8
12.5°	1196.6
15°	669.8
17.5°	355.6
20°	222.3
22.5°	165.1
25°	125.3
27.5°	93.6
30°	67.0
32.5°	48.2
35°	34.0
37.5°	23.8
40°	17.1
42.5°	13.0
45°	10.2
47.5°	6.2
50°	3.9
52.5°	2.9
55°	2.2
57.5°	1.7
60°	1.2
62.5°	1.2
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)