

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702671

Luminaire Tested: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-CC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702671
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-11)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-CC
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2632.7 lumens
Efficiency: N/A
Efficacy: 65.2 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.71
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702671

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-CC

Luminous Intensity Polar Plot



TEST NUMBER: P702671

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-CC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86	83	80	79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	61		68	63	60	59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56	55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53	52
10	70	60	54	50	69	60	54	50	59	54	50		58	53	50		58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	299017
5°	244153
10°	178907
15°	154496
20°	132308
25°	122303
30°	98589
35°	64002
40°	48400
45°	27006
50°	15732
55°	10442
60°	7111
65°	4430
70°	3834
75°	2899
80°	2142
85°	2171

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27006 cd/sqm

TEST NUMBER: P702671

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-CC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	322.3	12.2
10°-20°	640.1	24.3
20°-30°	756.7	28.7
30°-40°	529.5	20.1
40°-50°	247.1	9.4
50°-60°	85.7	3.3
60°-70°	32.6	1.2
70°-80°	13.2	0.5
80°-90°	3.1	0.1
90°-100°	2.0	0.1
100°-110°	1.2	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1719.1	65.3
0°-40°	2248.6	85.4
0°-60°	2581.4	98.1
0°-90°	2630.3	99.9
90°-120°	3.1	0.1
90°-150°	3.1	0.1
90°-180°	3.0	0.1
0°-180°	2632.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4583	
5°	3728	322
15°	2287	640
25°	1699	757
35°	804	530
45°	293	247
55°	92	86
65°	29	33
75°	12	13
85°	3	3
90°	0	0
95°	0	1
105°	0	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702671

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-CC

CANDELA DISTRIBUTION (FULL):

0°	
0°	4583.3
2.5°	4356.6
5°	3728.1
7.5°	3108.2
10°	2700.6
12.5°	2459.6
15°	2287.4
17.5°	2132.4
20°	1905.7
22.5°	1736.3
25°	1699.0
27.5°	1555.5
30°	1308.7
32.5°	1030.3
35°	803.6
37.5°	657.2
40°	568.3
42.5°	442.0
45°	292.7
47.5°	203.8
50°	155.0
52.5°	117.7
55°	91.8
57.5°	71.7
60°	54.5
62.5°	40.2
65°	28.7
67.5°	25.8
70°	20.1
72.5°	17.2
75°	11.5
77.5°	8.6
80°	5.7
82.5°	2.9
85°	2.9
87.5°	2.9
90°	0.0
92.5°	0.0
95°	0.0
97.5°	2.9
100°	2.9
102.5°	2.9
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P702671

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9040-4LBW1LI-CC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)