

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702683

Luminaire Tested: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C
KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2575.9 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702683

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC

Luminous Intensity Polar Plot



TEST NUMBER: P702683

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	76	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145434
5°	130636
10°	112696
15°	71051
20°	50740
25°	38966
30°	31395
35°	26410
40°	23304
45°	19926
50°	15994
55°	12455
60°	9795
65°	7737
70°	6254
75°	4983
80°	4040
85°	3181

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19926 cd/sqm

TEST NUMBER: P702683

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.9	8.1
10°-20°	414.3	16.1
20°-30°	410.4	15.9
30°-40°	408.9	15.9
40°-50°	390.3	15.2
50°-60°	291.3	11.3
60°-70°	197.5	7.7
70°-80°	128.8	5.0
80°-90°	78.2	3.0
90°-100°	40.8	1.6
100°-110°	5.5	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1034.6	40.2
0°-40°	1443.5	56.0
0°-60°	2125.1	82.5
0°-90°	2529.6	98.2
90°-120°	46.3	1.8
90°-150°	46.3	1.8
90°-180°	46.0	1.8
0°-180°	2575.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2229	
5°	2232	210
15°	1435	414
25°	885	410
35°	647	409
45°	510	390
55°	322	291
65°	196	197
75°	120	129
85°	70	63
90°	53	29
95°	38	27
105°	3	5
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702683

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2229.2
2.5°	2232.1
5°	2232.1
7.5°	2214.5
10°	2109.1
12.5°	1783.9
15°	1435.3
17.5°	1239.1
20°	1092.6
22.5°	975.4
25°	884.6
27.5°	808.5
30°	744.0
32.5°	688.4
35°	647.4
37.5°	615.1
40°	585.9
42.5°	553.6
45°	509.7
47.5°	462.8
50°	413.0
52.5°	366.2
55°	322.2
57.5°	284.1
60°	251.9
62.5°	222.6
65°	196.3
67.5°	175.8
70°	155.3
72.5°	137.7
75°	120.1
77.5°	105.5
80°	93.7
82.5°	82.0
85°	70.3
87.5°	61.5
90°	52.7
92.5°	46.9
95°	38.1
97.5°	29.3
100°	17.6
102.5°	8.8
105°	2.9
107.5°	0.0
110°	0.0

TEST NUMBER: P702683

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)