

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701877

Luminaire Tested: 340-4C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P701877
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-8)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC
Description: FARALLON 4" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 774.2 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.34' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P701877

CATALOG NUMBER: 340-4C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC

Luminous Intensity Polar Plot



TEST NUMBER: P701877

CATALOG NUMBER: 340-4C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	94	93	91
2	106	101	96	92	104	99	95	91	95	92	89		92	89	87		89	87	85	83
3	100	93	87	83	98	91	86	82	88	84	80		86	82	79		84	81	78	76
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	89	80	73	68	87	79	72	68	77	71	67		75	70	67		73	69	66	64
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69	65	61	60
7	79	69	63	58	78	69	62	58	67	62	58		66	61	57		65	60	57	55
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	56	53	52
9	71	61	55	50	70	61	54	50	60	54	50		59	53	50		58	53	50	48
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95176
5°	91814
10°	87375
15°	84040
20°	71304
25°	59482
30°	44517
35°	31971
40°	25224
45°	16731
50°	12216
55°	8655
60°	5962
65°	5132
70°	4476
75°	3854
80°	3139
85°	3061

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16731 cd/sqm

TEST NUMBER: P701877

CATALOG NUMBER: 340-4C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.5	9.5
10°-20°	190.8	24.6
20°-30°	209.9	27.1
30°-40°	145.5	18.8
40°-50°	83.0	10.7
50°-60°	39.4	5.1
60°-70°	18.7	2.4
70°-80°	9.1	1.2
80°-90°	2.7	0.3
90°-100°	1.0	0.1
100°-110°	0.6	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	474.2	61.2
0°-40°	619.7	80.0
0°-60°	742.1	95.9
0°-90°	772.6	99.8
90°-120°	1.6	0.2
90°-150°	1.6	0.2
90°-180°	2.0	0.3
0°-180°	774.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	821	
5°	789	73
15°	700	191
25°	465	210
35°	226	146
45°	102	83
55°	43	39
65°	19	19
75°	9	9
85°	2	2
90°	1	1
95°	1	1
105°	1	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P701877

CATALOG NUMBER: 340-4C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC

CANDELA DISTRIBUTION (FULL):

0°	
0°	820.6
1°	815.9
2°	808.1
3°	803.4
4°	796.4
5°	788.6
6°	776.2
7°	763.7
8°	754.4
9°	750.5
10°	741.9
11°	728.7
12°	722.5
13°	719.4
14°	713.1
15°	699.9
16°	682.0
17°	657.9
18°	630.6
19°	601.8
20°	577.7
21°	556.6
22°	535.6
23°	513.8
24°	491.3
25°	464.8
27.5°	397.8
30°	332.4
32.5°	270.9
35°	225.8
37.5°	193.1
40°	166.6
42.5°	133.1
45°	102.0
47.5°	81.7
50°	67.7
52.5°	55.3
55°	42.8
57.5°	32.7
60°	25.7
62.5°	21.8
65°	18.7
67.5°	15.6
70°	13.2
72.5°	10.9

TEST NUMBER: P701877

CATALOG NUMBER: 340-4C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC

CANDELA DISTRIBUTION (continued):

	0°
75°	8.6
77.5°	6.2
80°	4.7
82.5°	3.1
85°	2.3
87.5°	1.6
90°	0.8
92.5°	0.8
95°	0.8
97.5°	0.8
100°	1.6
102.5°	0.8
105°	0.8
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)