

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702684

Luminaire Tested: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-14)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, FROSTED OUTSIDE KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2400.5 lumens
Efficiency: N/A
Efficacy: 59.4 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.63
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702684

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF

Luminous Intensity Polar Plot



TEST NUMBER: P702684

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109		104	104	104		99	99	99	96
1	107	102	97	93	104	99	95	91	94	91	88		90	87	84		85	83	81	79
2	98	89	82	77	95	87	81	75	83	78	73		79	75	71		76	72	69	66
3	90	79	71	65	87	77	70	64	74	68	62		71	65	61		68	63	59	57
4	83	71	63	56	80	70	62	56	67	60	54		64	58	53		61	56	52	50
5	77	65	56	49	75	63	55	49	61	54	48		58	52	47		56	51	47	44
6	72	59	50	44	70	58	50	44	56	49	43		54	47	43		52	46	42	40
7	67	54	46	40	65	53	45	40	51	44	39		50	43	39		48	43	38	36
8	63	50	42	37	61	49	42	36	48	41	36		46	40	36		45	39	35	33
9	60	47	39	34	58	46	39	34	45	38	33		43	37	33		42	37	33	31
10	56	44	36	31	55	43	36	31	42	35	31		41	35	31		40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	135303
5°	120007
10°	100016
15°	55972
20°	37412
25°	28905
30°	23361
35°	19479
40°	17362
45°	15919
50°	14519
55°	13024
60°	11618
65°	10043
70°	8610
75°	7294
80°	6188
85°	5167

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15919 cd/sqm

TEST NUMBER: P702684

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.6	7.9
10°-20°	331.9	13.8
20°-30°	304.5	12.7
30°-40°	302.7	12.6
40°-50°	314.4	13.1
50°-60°	302.2	12.6
60°-70°	252.8	10.5
70°-80°	186.4	7.8
80°-90°	126.2	5.3
90°-100°	73.2	3.0
100°-110°	15.2	0.6
110°-120°	0.4	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	827.0	34.5
0°-40°	1129.7	47.1
0°-60°	1746.4	72.7
0°-90°	2311.7	96.3
90°-120°	88.8	3.7
90°-150°	88.8	3.7
90°-180°	89.0	3.7
0°-180°	2400.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2074	
5°	2050	191
15°	1131	332
25°	656	304
35°	478	303
45°	407	314
55°	337	302
65°	255	253
75°	176	186
85°	114	100
90°	91	50
95°	70	49
105°	12	15
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702684

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF

CANDELA DISTRIBUTION (FULL):

0°	
0°	2073.9
2.5°	2071.0
5°	2050.5
7.5°	2003.6
10°	1871.8
12.5°	1511.5
15°	1130.7
17.5°	928.6
20°	805.6
22.5°	720.6
25°	656.2
27.5°	603.4
30°	553.6
32.5°	509.7
35°	477.5
37.5°	454.0
40°	436.5
42.5°	421.8
45°	407.2
47.5°	392.5
50°	374.9
52.5°	357.4
55°	336.9
57.5°	319.3
60°	298.8
62.5°	275.4
65°	254.8
67.5°	234.3
70°	213.8
72.5°	193.3
75°	175.8
77.5°	158.2
80°	143.5
82.5°	128.9
85°	114.2
87.5°	102.5
90°	90.8
92.5°	82.0
95°	70.3
97.5°	52.7
100°	35.2
102.5°	20.5
105°	11.7
107.5°	5.9
110°	2.9

TEST NUMBER: P702684

CATALOG NUMBER: 340-6C-35-D010 / 340-EU4C-3040-9050-4LBW1LI-GFF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)