

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702703

Luminaire Tested: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GCC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-16)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GCC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA
Light Source: 2400K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2754.1 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.89
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702703

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GCC

Luminous Intensity Polar Plot



TEST NUMBER: P702703

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GCC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90	87	85	83
3	100	93	87	83	98	91	86	82	88	84	81		86	82	79		84	81	78	76
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	74	71	70
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73	69	66	64
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61	59
7	79	69	62	58	78	68	62	57	67	61	57		66	60	57		64	60	56	55
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61	56	52	51
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57	52	49	48
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54	49	46	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	183822
5°	176711
10°	168102
15°	151531
20°	136890
25°	116781
30°	99651
35°	71783
40°	54796
45°	36841
50°	22796
55°	16402
60°	11939
65°	8135
70°	6886
75°	5596
80°	5222
85°	4117

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 36841 cd/sqm

TEST NUMBER: P702703

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GCC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.8	9.2
10°-20°	632.8	23.0
20°-30°	745.9	27.1
30°-40°	579.9	21.1
40°-50°	318.1	11.6
50°-60°	132.6	4.8
60°-70°	56.1	2.0
70°-80°	24.1	0.9
80°-90°	6.8	0.2
90°-100°	3.1	0.1
100°-110°	1.9	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1631.5	59.2
0°-40°	2211.4	80.3
0°-60°	2662.1	96.7
0°-90°	2749.2	99.8
90°-120°	4.9	0.2
90°-150°	4.9	0.2
90°-180°	5.0	0.2
0°-180°	2754.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2818	
5°	2698	253
15°	2244	633
25°	1622	746
35°	901	580
45°	399	318
55°	144	133
65°	53	56
75°	22	24
85°	6	6
90°	3	2
95°	3	2
105°	3	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702703

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GCC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2817.6
2.5°	2787.1
5°	2698.3
7.5°	2617.9
10°	2537.5
12.5°	2390.5
15°	2243.5
17.5°	2149.2
20°	1971.7
22.5°	1758.2
25°	1622.3
27.5°	1489.2
30°	1322.8
32.5°	1120.4
35°	901.3
37.5°	743.2
40°	643.4
42.5°	546.3
45°	399.3
47.5°	288.4
50°	224.6
52.5°	177.5
55°	144.2
57.5°	116.5
60°	91.5
62.5°	66.6
65°	52.7
67.5°	44.4
70°	36.1
72.5°	27.7
75°	22.2
77.5°	16.6
80°	13.9
82.5°	8.3
85°	5.5
87.5°	2.8
90°	2.8
92.5°	2.8
95°	2.8
97.5°	2.8
100°	2.8
102.5°	2.8
105°	2.8
107.5°	0.0
110°	0.0

TEST NUMBER: P702703

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GCC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)