

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702705

Luminaire Tested: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GFF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-14)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GFF
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, FROSTED OUTSIDE KIT.
Light Source: 2400K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2272.7 lumens
Efficiency: N/A
Efficacy: 48.4 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.63
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702705

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GFF

Luminous Intensity Polar Plot



TEST NUMBER: P702705

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109		104	104	104		99	99	99	96
1	107	102	97	93	104	99	95	91	94	91	88		90	87	84		85	83	81	79
2	98	89	82	77	95	87	81	75	83	78	73		79	75	71		76	72	69	66
3	90	79	71	65	87	77	70	64	74	68	62		71	65	61		68	63	59	57
4	83	71	63	56	80	70	62	56	67	60	54		64	58	53		61	56	52	50
5	77	65	56	49	75	63	55	49	61	54	48		58	52	47		56	51	47	44
6	72	59	50	44	70	58	50	44	56	49	43		54	47	43		52	46	42	40
7	67	54	46	40	65	53	45	40	51	44	39		50	43	39		48	43	38	36
8	63	50	42	37	61	49	42	36	48	41	36		46	40	36		45	39	35	33
9	60	47	39	34	58	46	39	34	45	38	33		43	37	33		42	37	33	31
10	56	44	36	31	55	43	36	31	42	35	31		41	35	31		40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128093
5°	113616
10°	94689
15°	52992
20°	35415
25°	27363
30°	22116
35°	18439
40°	16435
45°	15071
50°	13748
55°	12328
60°	11000
65°	9511
70°	8151
75°	6904
80°	5860
85°	4895

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15071 cd/sqm

TEST NUMBER: P702705

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.5	7.9
10°-20°	314.3	13.8
20°-30°	288.2	12.7
30°-40°	286.5	12.6
40°-50°	297.7	13.1
50°-60°	286.1	12.6
60°-70°	239.4	10.5
70°-80°	176.5	7.8
80°-90°	119.5	5.3
90°-100°	69.3	3.0
100°-110°	14.4	0.6
110°-120°	0.4	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	783.0	34.5
0°-40°	1069.5	47.1
0°-60°	1653.3	72.7
0°-90°	2188.6	96.3
90°-120°	84.1	3.7
90°-150°	84.1	3.7
90°-180°	84.0	3.7
0°-180°	2272.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1963	
5°	1941	180
15°	1070	314
25°	621	288
35°	452	287
45°	386	298
55°	319	286
65°	241	239
75°	166	177
85°	108	94
90°	86	48
95°	67	47
105°	11	14
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702705

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GFF

CANDELA DISTRIBUTION (FULL):

0°	
0°	1963.4
2.5°	1960.7
5°	1941.3
7.5°	1896.9
10°	1772.1
12.5°	1431.0
15°	1070.5
17.5°	879.1
20°	762.6
22.5°	682.2
25°	621.2
27.5°	571.3
30°	524.1
32.5°	482.5
35°	452.0
37.5°	429.8
40°	413.2
42.5°	399.3
45°	385.5
47.5°	371.6
50°	355.0
52.5°	338.3
55°	318.9
57.5°	302.3
60°	282.9
62.5°	260.7
65°	241.3
67.5°	221.9
70°	202.4
72.5°	183.0
75°	166.4
77.5°	149.8
80°	135.9
82.5°	122.0
85°	108.2
87.5°	97.1
90°	86.0
92.5°	77.7
95°	66.6
97.5°	49.9
100°	33.3
102.5°	19.4
105°	11.1
107.5°	5.5
110°	2.8

TEST NUMBER: P702705

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9024-4LBW1LI-GFF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)