

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702718

Luminaire Tested: 340-6C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C
KIT.
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2882.3 lumens
Efficiency: N/A
Efficacy: 61.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702718

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

Luminous Intensity Polar Plot



TEST NUMBER: P702718

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	76	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162730
5°	146174
10°	126102
15°	79506
20°	56777
25°	43604
30°	35130
35°	29552
40°	26072
45°	22295
50°	17899
55°	13936
60°	10961
65°	8655
70°	6995
75°	5576
80°	4523
85°	3561

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22295 cd/sqm

TEST NUMBER: P702718

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.8	8.1
10°-20°	463.6	16.1
20°-30°	459.2	15.9
30°-40°	457.6	15.9
40°-50°	436.7	15.2
50°-60°	325.9	11.3
60°-70°	221.0	7.7
70°-80°	144.1	5.0
80°-90°	87.6	3.0
90°-100°	45.6	1.6
100°-110°	6.1	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1157.6	40.2
0°-40°	1615.2	56.0
0°-60°	2377.9	82.5
0°-90°	2830.5	98.2
90°-120°	51.8	1.8
90°-150°	51.8	1.8
90°-180°	52.0	1.8
0°-180°	2882.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2494	
5°	2498	235
15°	1606	464
25°	990	459
35°	724	458
45°	570	437
55°	360	326
65°	220	221
75°	134	144
85°	79	70
90°	59	33
95°	43	30
105°	3	6
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702718

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2494.3
2.5°	2497.6
5°	2497.6
7.5°	2478.0
10°	2360.0
12.5°	1996.1
15°	1606.1
17.5°	1386.5
20°	1222.6
22.5°	1091.5
25°	989.9
27.5°	904.6
30°	832.5
32.5°	770.3
35°	724.4
37.5°	688.3
40°	655.5
42.5°	619.5
45°	570.3
47.5°	517.9
50°	462.2
52.5°	409.7
55°	360.5
57.5°	317.9
60°	281.9
62.5°	249.1
65°	219.6
67.5°	196.7
70°	173.7
72.5°	154.1
75°	134.4
77.5°	118.0
80°	104.9
82.5°	91.8
85°	78.7
87.5°	68.8
90°	59.0
92.5°	52.4
95°	42.6
97.5°	32.8
100°	19.7
102.5°	9.8
105°	3.3
107.5°	0.0
110°	0.0

TEST NUMBER: P702718

CATALOG NUMBER: 340-6C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-GFC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)