

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702253

Luminaire Tested: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-CQ

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702253  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-CQ  
Description: FARALLON 6" LED GLASS DOWNLIGHT CYLINDRICAL FROSTED, QUADRATE ETCHED GLASS KIT.  
Light Source: 2400K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 386.6 lumens  
Efficiency: N/A  
Efficacy: 53.7 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.54  
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702253

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-CQ

### Luminous Intensity Polar Plot



TEST NUMBER: P702253

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-CQ

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	110	105	102	98	107	103	100	97	98	96	93		94	92	90		90	89	87	85
2	102	95	89	84	99	93	87	83	89	84	81		85	82	78		82	79	76	74
3	95	86	79	73	92	84	78	72	81	75	71		78	73	70		75	71	68	66
4	88	78	71	65	86	77	70	64	74	68	63		72	67	62		69	65	61	59
5	83	72	64	59	81	71	63	58	68	62	57		66	61	57		64	60	56	54
6	78	66	59	53	76	65	58	53	63	57	52		62	56	52		60	55	51	49
7	73	62	54	49	71	61	54	49	59	53	48		58	52	48		56	51	47	46
8	69	58	50	45	68	57	50	45	55	49	45		54	48	44		53	48	44	42
9	66	54	47	42	64	53	47	42	52	46	42		51	45	41		50	45	41	40
10	62	51	44	40	61	50	44	39	49	43	39		48	43	39		47	42	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	38577
5°	27712
10°	17579
15°	14073
20°	9683
25°	5370
30°	4207
35°	3537
40°	3106
45°	2576
50°	2114
55°	1674
60°	1334
65°	1048
70°	838
75°	672
80°	543
85°	448

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2576 cd/sqm

TEST NUMBER: P702253

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-CQ

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.5	10.5
10°-20°	77.6	20.1
20°-30°	60.3	15.6
30°-40°	54.8	14.2
40°-50°	50.9	13.2
50°-60°	39.1	10.1
60°-70°	26.8	6.9
70°-80°	17.4	4.5
80°-90°	10.8	2.8
90°-100°	6.3	1.6
100°-110°	2.0	0.5
110°-120°	0.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	178.4	46.1
0°-40°	233.2	60.3
0°-60°	323.2	83.6
0°-90°	378.2	97.8
90°-120°	8.4	2.2
90°-150°	8.4	2.2
90°-180°	8.0	2.1
0°-180°	386.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	591	
5°	474	40
15°	284	78
25°	122	60
35°	87	55
45°	66	51
55°	43	39
65°	27	27
75°	16	17
85°	10	9
90°	7	4
95°	6	4
105°	2	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P702253

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-CQ

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	591.3
2.5°	565.1
5°	473.5
7.5°	385.0
10°	329.0
12.5°	301.5
15°	284.3
17.5°	262.2
20°	208.5
22.5°	145.8
25°	121.9
27.5°	110.1
30°	99.7
32.5°	91.6
35°	86.7
37.5°	83.5
40°	78.1
42.5°	71.8
45°	65.9
47.5°	60.0
50°	54.6
52.5°	48.7
55°	43.3
57.5°	38.8
60°	34.3
62.5°	30.2
65°	26.6
67.5°	23.9
70°	20.8
72.5°	18.5
75°	16.2
77.5°	14.4
80°	12.6
82.5°	11.3
85°	9.9
87.5°	8.6
90°	7.2
92.5°	6.8
95°	5.9
97.5°	5.0
100°	3.6
102.5°	2.7
105°	1.8
107.5°	0.9
110°	0.5

TEST NUMBER: P702253

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9024-4LBW1LI-CQ

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)