

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701934

Luminaire Tested: 340-4C-15-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P701934  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-4C-15-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC  
Description: FARALLON 4" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C  
KIT.  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 983.1 lumens  
Efficiency: N/A  
Efficacy: 62.2 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.65  
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')  
CIE Type: Direct  
  
Input Watts (W): 15.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P701934

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC

### Luminous Intensity Polar Plot



TEST NUMBER: P701934

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	104	100	97	106	102	98	95	97	94	92		93	91	89		89	87	86	83
2	100	93	87	81	98	91	85	80	87	82	78		84	80	76		80	77	74	72
3	93	83	76	70	90	82	75	69	78	73	68		75	71	66		73	69	65	63
4	86	75	67	61	84	74	66	61	71	65	60		69	63	59		66	62	58	56
5	80	69	60	54	78	67	60	54	65	58	53		63	57	53		61	56	52	50
6	75	63	55	49	73	62	54	49	60	53	48		58	52	48		57	51	47	45
7	70	58	50	45	69	57	50	44	56	49	44		54	48	44		53	47	43	41
8	66	54	46	41	65	53	46	41	52	45	40		50	44	40		49	44	40	38
9	62	50	43	38	61	50	42	38	48	42	37		47	41	37		46	41	37	35
10	59	47	40	35	58	47	40	35	45	39	35		44	39	35		44	38	34	33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	114464
5°	97984
10°	69575
15°	43676
20°	30912
25°	22900
30°	18620
35°	15959
40°	13845
45°	11522
50°	9180
55°	7322
60°	5822
65°	4725
70°	3856
75°	3134
80°	2470
85°	2022

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11522 cd/sqm

TEST NUMBER: P701934

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.8	8.8
10°-20°	149.6	15.2
20°-30°	149.8	15.2
30°-40°	154.6	15.7
40°-50°	145.5	14.8
50°-60°	111.6	11.3
60°-70°	79.5	8.1
70°-80°	54.3	5.5
80°-90°	34.0	3.5
90°-100°	16.1	1.6
100°-110°	1.4	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	386.2	39.3
0°-40°	540.8	55.0
0°-60°	797.8	81.2
0°-90°	965.6	98.2
90°-120°	17.6	1.8
90°-150°	17.6	1.8
90°-180°	18.0	1.8
0°-180°	983.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	987	
5°	967	87
15°	529	150
25°	321	150
35°	247	155
45°	190	145
55°	124	112
65°	80	80
75°	51	54
85°	31	27
90°	24	13
95°	14	10
105°	0	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P701934

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	986.9
1°	985.7
2°	977.3
3°	974.9
4°	972.6
5°	966.6
6°	957.1
7°	934.4
8°	893.9
9°	836.7
10°	767.6
11°	697.2
12°	638.8
13°	593.5
14°	559.0
15°	529.2
16°	500.6
17°	475.6
18°	450.5
19°	426.7
20°	405.2
21°	385.0
22°	367.1
23°	350.4
24°	336.1
25°	320.6
27.5°	292.0
30°	275.3
32.5°	259.8
35°	246.7
37.5°	233.6
40°	221.7
42.5°	206.2
45°	189.5
47.5°	171.6
50°	153.8
52.5°	138.3
55°	124.0
57.5°	110.8
60°	98.9
62.5°	88.2
65°	79.9
67.5°	71.5
70°	64.4
72.5°	57.2

TEST NUMBER: P701934

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC

**CANDELA DISTRIBUTION (continued):**

	0°
75°	51.3
77.5°	45.3
80°	39.3
82.5°	34.6
85°	31.0
87.5°	27.4
90°	23.8
92.5°	20.3
95°	14.3
97.5°	9.5
100°	6.0
102.5°	2.4
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)