

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702293

Luminaire Tested: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702293  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC  
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.  
Light Source: 2700K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 470.6 lumens  
Efficiency: N/A  
Efficacy: 65.4 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.71  
Luminous Opening: (L: -0.46 ' x W: 0 ' x H: 0 '  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702293

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC

### Luminous Intensity Polar Plot




TEST NUMBER: P702293

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86	83	80	79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	61		68	63	60	59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56	55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53	52
10	70	60	54	50	69	60	54	50	59	54	50		58	54	50		58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**



**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: -  
 Vertical Angle: -  
 Luminance: -

TEST NUMBER: P702293

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.6	12.2
10°-20°	114.4	24.3
20°-30°	135.3	28.7
30°-40°	94.7	20.1
40°-50°	44.2	9.4
50°-60°	15.3	3.3
60°-70°	5.8	1.2
70°-80°	2.4	0.5
80°-90°	0.5	0.1
90°-100°	0.3	0.1
100°-110°	0.2	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	307.3	65.3
0°-40°	402.0	85.4
0°-60°	461.4	98.1
0°-90°	470.1	99.9
90°-120°	0.5	0.1
90°-150°	0.5	0.1
90°-180°	1.0	0.2
0°-180°	470.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	819	
5°	666	58
15°	409	114
25°	304	135
35°	144	95
45°	52	44
55°	16	15
65°	5	6
75°	2	2
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702293

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	819.3
2.5°	778.8
5°	666.4
7.5°	555.6
10°	482.8
12.5°	439.7
15°	408.9
17.5°	381.2
20°	340.7
22.5°	310.4
25°	303.7
27.5°	278.1
30°	233.9
32.5°	184.2
35°	143.6
37.5°	117.5
40°	101.6
42.5°	79.0
45°	52.3
47.5°	36.4
50°	27.7
52.5°	21.0
55°	16.4
57.5°	12.8
60°	9.7
62.5°	7.2
65°	5.1
67.5°	4.6
70°	3.6
72.5°	3.1
75°	2.1
77.5°	1.5
80°	1.0
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.5
100°	0.5
102.5°	0.5
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P702293

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9727-4LBW1LI-CC

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)