

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701968

Luminaire Tested: 340-4C-15-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P701968
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-8)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-15-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC
Description: FARALLON 4" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA
Light Source: 3000K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1185.1 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.34' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P701968

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC

Luminous Intensity Polar Plot



TEST NUMBER: P701968

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	94	93	91
2	106	101	96	92	104	99	95	91	95	92	89		92	89	87		89	87	85	83
3	100	93	87	83	98	91	86	82	88	84	80		86	82	79		84	81	78	76
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78	75	72	70
5	89	80	73	68	87	79	72	68	77	71	67		75	70	67		73	69	66	64
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69	65	61	60
7	79	69	63	58	78	69	62	58	67	62	58		66	61	57		65	60	57	55
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	56	53	52
9	71	61	55	50	70	61	54	50	60	54	50		59	53	50		58	53	50	48
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145698
5°	140561
10°	133766
15°	128648
20°	109146
25°	91053
30°	68155
35°	48933
40°	38608
45°	25604
50°	18711
55°	13245
60°	9116
65°	7849
70°	6884
75°	5870
80°	4809
85°	4791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25604 cd/sqm

TEST NUMBER: P701968

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.5	9.5
10°-20°	292.1	24.6
20°-30°	321.3	27.1
30°-40°	222.8	18.8
40°-50°	127.0	10.7
50°-60°	60.4	5.1
60°-70°	28.6	2.4
70°-80°	14.0	1.2
80°-90°	4.1	0.3
90°-100°	1.5	0.1
100°-110°	1.0	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	725.9	61.3
0°-40°	948.7	80.0
0°-60°	1136.0	95.9
0°-90°	1182.7	99.8
90°-120°	2.4	0.2
90°-150°	2.4	0.2
90°-180°	2.0	0.2
0°-180°	1185.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1256	
5°	1207	113
15°	1071	292
25°	712	321
35°	346	223
45°	156	127
55°	66	60
65°	29	29
75°	13	14
85°	4	4
90°	1	1
95°	1	1
105°	1	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P701968

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1256.2
1°	1249.0
2°	1237.1
3°	1229.9
4°	1219.2
5°	1207.3
6°	1188.2
7°	1169.2
8°	1154.9
9°	1148.9
10°	1135.8
11°	1115.5
12°	1106.0
13°	1101.2
14°	1091.7
15°	1071.4
16°	1044.0
17°	1007.1
18°	965.4
19°	921.3
20°	884.3
21°	852.1
22°	820.0
23°	786.6
24°	752.0
25°	711.5
27.5°	609.0
30°	508.9
32.5°	414.7
35°	345.6
37.5°	295.6
40°	255.0
42.5°	203.8
45°	156.1
47.5°	125.1
50°	103.7
52.5°	84.6
55°	65.5
57.5°	50.1
60°	39.3
62.5°	33.4
65°	28.6
67.5°	23.8
70°	20.3
72.5°	16.7

TEST NUMBER: P701968

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9730-4LBW1LI-GCC

CANDELA DISTRIBUTION (continued):

	0°
75°	13.1
77.5°	9.5
80°	7.2
82.5°	4.8
85°	3.6
87.5°	2.4
90°	1.2
92.5°	1.2
95°	1.2
97.5°	1.2
100°	2.4
102.5°	1.2
105°	1.2
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)