

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702284

Luminaire Tested: 340-6C-05-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702284  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-05-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC  
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C  
KIT.  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 475.8 lumens  
Efficiency: N/A  
Efficacy: 66.1 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74  
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702284

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

### Luminous Intensity Polar Plot



TEST NUMBER: P702284

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	76	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	26866
5°	24130
10°	20818
15°	13123
20°	9371
25°	7198
30°	5798
35°	4879
40°	4304
45°	3679
50°	2955
55°	2300
60°	1808
65°	1431
70°	1156
75°	921
80°	746
85°	588

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3679 cd/sqm

TEST NUMBER: P702284

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.8	8.1
10°-20°	76.5	16.1
20°-30°	75.8	15.9
30°-40°	75.5	15.9
40°-50°	72.1	15.2
50°-60°	53.8	11.3
60°-70°	36.5	7.7
70°-80°	23.8	5.0
80°-90°	14.5	3.0
90°-100°	7.5	1.6
100°-110°	1.0	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	191.1	40.2
0°-40°	266.6	56.0
0°-60°	392.5	82.5
0°-90°	467.3	98.2
90°-120°	8.5	1.8
90°-150°	8.5	1.8
90°-180°	9.0	1.9
0°-180°	475.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	412	
5°	412	39
15°	265	77
25°	163	76
35°	120	76
45°	94	72
55°	60	54
65°	36	36
75°	22	24
85°	13	12
90°	10	5
95°	7	5
105°	0	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702284

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	411.8
2.5°	412.3
5°	412.3
7.5°	409.1
10°	389.6
12.5°	329.5
15°	265.1
17.5°	228.9
20°	201.8
22.5°	180.2
25°	163.4
27.5°	149.3
30°	137.4
32.5°	127.2
35°	119.6
37.5°	113.6
40°	108.2
42.5°	102.3
45°	94.1
47.5°	85.5
50°	76.3
52.5°	67.6
55°	59.5
57.5°	52.5
60°	46.5
62.5°	41.1
65°	36.3
67.5°	32.5
70°	28.7
72.5°	25.4
75°	22.2
77.5°	19.5
80°	17.3
82.5°	15.2
85°	13.0
87.5°	11.4
90°	9.7
92.5°	8.7
95°	7.0
97.5°	5.4
100°	3.2
102.5°	1.6
105°	0.5
107.5°	0.0
110°	0.0

TEST NUMBER: P702284

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9040-4LBW1LI-GFC

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)