

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701953

Luminaire Tested: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P701953
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-2)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF
Description: FARALLON 4" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 985.2 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.73
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P701953

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

Luminous Intensity Polar Plot



TEST NUMBER: P701953

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		100	100	100	97
1	109	105	102	98	107	103	99	96	98	95	93		94	92	90		90	88	86	84
2	102	95	89	85	99	93	88	83	89	85	81		86	82	79		82	80	77	75
3	95	87	80	75	93	85	79	74	82	77	72		79	75	71		76	73	69	67
4	89	80	73	67	87	78	72	67	76	70	65		73	68	64		71	67	63	61
5	84	74	66	61	82	73	66	61	70	64	60		68	63	59		66	62	58	56
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		62	58	54	52
7	75	64	57	52	73	63	56	52	62	56	51		60	55	51		59	54	50	49
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		55	51	47	45
9	68	57	50	45	66	56	50	45	55	49	45		54	48	44		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108514
5°	93838
10°	80543
15°	69055
20°	58742
25°	39464
30°	15049
35°	11114
40°	8643
45°	6840
50°	5384
55°	4381
60°	3709
65°	3365
70°	3035
75°	2792
80°	2564
85°	2257

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6840 cd/sqm

TEST NUMBER: P701953

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.2	8.8
10°-20°	234.7	23.8
20°-30°	232.2	23.6
30°-40°	108.9	11.1
40°-50°	86.9	8.8
50°-60°	67.1	6.8
60°-70°	56.4	5.7
70°-80°	48.3	4.9
80°-90°	37.7	3.8
90°-100°	21.8	2.2
100°-110°	4.0	0.4
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.0	56.2
0°-40°	662.9	67.3
0°-60°	817.0	82.9
0°-90°	959.5	97.4
90°-120°	25.7	2.6
90°-150°	25.7	2.6
90°-180°	26.0	2.6
0°-180°	985.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	936	
5°	926	87
15°	837	235
25°	552	232
35°	172	109
45°	112	87
55°	74	67
65°	57	56
75°	46	48
85°	35	29
90°	28	16
95°	21	14
105°	2	4
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P701953

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

CANDELA DISTRIBUTION (FULL):

0°	
0°	935.6
2.5°	933.1
5°	925.7
7.5°	910.9
10°	888.6
12.5°	863.9
15°	836.7
17.5°	805.8
20°	770.0
22.5°	715.6
25°	552.5
27.5°	317.6
30°	222.5
32.5°	191.6
35°	171.8
37.5°	155.7
40°	138.4
42.5°	124.8
45°	112.5
47.5°	100.1
50°	90.2
52.5°	81.6
55°	74.2
57.5°	68.0
60°	63.0
62.5°	59.3
65°	56.9
67.5°	54.4
70°	50.7
72.5°	48.2
75°	45.7
77.5°	43.3
80°	40.8
82.5°	37.1
85°	34.6
87.5°	32.1
90°	28.4
92.5°	26.0
95°	21.0
97.5°	13.6
100°	9.9
102.5°	6.2
105°	2.5
107.5°	1.2
110°	0.0

TEST NUMBER: P701953

CATALOG NUMBER: 340-4C-15-D010 / 340-EU4C-1020-9050-4LBW1LI-FF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)