

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702021

Luminaire Tested: 340-4C-20-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702021
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-4)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-20-D010 / 340-EU4C-1020-9730-4LBW1LI-CF
Description: FARALLON 4" LED GLASS DOWNLIGHT. CYLINDRICAL FROSTED GLASS KIT.
Light Source: 3000K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1316.9 lumens
Efficiency: N/A
Efficacy: 60.4 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.45
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702021

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

Luminous Intensity Polar Plot



TEST NUMBER: P702021

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	98	106	103	99	96	98	95	92		94	91	89		90	88	86	84
2	101	94	88	83	98	92	86	82	88	83	80		85	81	77		81	78	75	73
3	94	85	78	72	91	83	76	71	80	74	70		77	72	68		74	70	67	65
4	87	77	70	64	85	76	69	63	73	67	62		71	65	61		68	64	60	58
5	82	71	63	57	80	70	62	57	67	61	56		65	60	55		63	59	55	53
6	77	65	58	52	75	64	57	52	62	56	51		61	55	51		59	54	50	48
7	72	61	53	48	71	60	53	48	58	52	47		57	51	47		55	50	46	45
8	69	57	49	44	67	56	49	44	55	48	44		53	48	43		52	47	43	41
9	65	53	46	41	64	53	46	41	52	45	41		50	45	41		49	44	40	39
10	62	50	43	39	61	50	43	39	49	43	39		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	295026
5°	194722
10°	108315
15°	80221
20°	38716
25°	26364
30°	20493
35°	18307
40°	16424
45°	14216
50°	11752
55°	9536
60°	7694
65°	6091
70°	4789
75°	3855
80°	3092
85°	2504

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14216 cd/sqm

TEST NUMBER: P702021

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.1	11.9
10°-20°	248.0	18.8
20°-30°	172.3	13.1
30°-40°	176.6	13.4
40°-50°	179.0	13.6
50°-60°	145.2	11.0
60°-70°	102.5	7.8
70°-80°	67.0	5.1
80°-90°	42.1	3.2
90°-100°	22.7	1.7
100°-110°	4.3	0.3
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.5	43.9
0°-40°	754.1	57.3
0°-60°	1078.3	81.9
0°-90°	1289.9	98.0
90°-120°	27.0	2.0
90°-150°	27.0	2.0
90°-180°	27.0	2.1
0°-180°	1316.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2544	
5°	1921	157
15°	972	248
25°	369	172
35°	283	177
45°	234	179
55°	162	145
65°	103	103
75°	63	67
85°	38	33
90°	29	16
95°	22	15
105°	3	4
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P702021

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

CANDELA DISTRIBUTION (FULL):

0°	
0°	2543.7
1°	2534.5
2°	2471.4
3°	2326.9
4°	2131.6
5°	1920.9
6°	1708.6
7°	1517.9
8°	1381.1
9°	1273.4
10°	1195.0
11°	1138.1
12°	1091.9
13°	1053.5
14°	1016.6
15°	972.0
16°	901.2
17°	804.3
18°	693.6
19°	587.5
20°	507.5
21°	458.3
22°	426.0
23°	406.0
24°	387.6
25°	369.1
27.5°	329.1
30°	303.0
32.5°	287.6
35°	283.0
37.5°	273.8
40°	263.0
42.5°	249.1
45°	233.8
47.5°	215.3
50°	196.9
52.5°	178.4
55°	161.5
57.5°	146.1
60°	130.7
62.5°	115.3
65°	103.0
67.5°	90.7
70°	80.0
72.5°	70.7

TEST NUMBER: P702021

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

CANDELA DISTRIBUTION (continued):

	0°
75°	63.1
77.5°	55.4
80°	49.2
82.5°	43.1
85°	38.4
87.5°	33.8
90°	29.2
92.5°	26.1
95°	21.5
97.5°	15.4
100°	10.8
102.5°	6.2
105°	3.1
107.5°	1.5
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)