

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702288

Luminaire Tested: 340-6C-05-D010 / 340-EU4C-1020-9050-4LBW1LI-CQ

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-13)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-05-D010 / 340-EU4C-1020-9050-4LBW1LI-CQ
Description: FARALLON 6" LED GLASS DOWNLIGHT CYLINDRICAL FROSTED, QUADRATE ETCHED GLASS KIT.
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 473.5 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.54
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702288

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9050-4LBW1LI-CQ

Luminous Intensity Polar Plot



TEST NUMBER: P702288

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9050-4LBW1LI-CQ

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	110	105	102	98	107	103	100	97	98	96	93		94	92	90		90	89	87	85
2	102	95	89	84	99	93	87	83	89	84	81		85	82	78		82	79	76	74
3	95	86	79	73	92	84	78	72	81	75	71		78	73	70		75	71	68	66
4	88	78	71	65	86	77	70	64	74	68	63		72	67	62		69	65	61	59
5	83	72	64	58	81	71	63	58	68	62	57		66	61	57		64	60	56	54
6	78	66	59	53	76	65	58	53	63	57	52		62	56	52		60	55	51	49
7	73	62	54	49	71	61	54	49	59	53	48		58	52	48		56	51	47	46
8	69	58	50	45	68	57	50	45	55	49	45		54	48	44		53	48	44	42
9	66	54	47	42	64	53	47	42	52	46	42		51	45	41		50	45	41	40
10	62	51	44	40	61	50	44	39	49	43	39		48	43	39		47	42	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47247
5°	33939
10°	21534
15°	17242
20°	11861
25°	6577
30°	5157
35°	4328
40°	3802
45°	3155
50°	2591
55°	2053
60°	1633
65°	1285
70°	1023
75°	826
80°	668
85°	552

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3155 cd/sqm

TEST NUMBER: P702288

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9050-4LBW1LI-CQ

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	10.5
10°-20°	95.1	20.1
20°-30°	73.8	15.6
30°-40°	67.2	14.2
40°-50°	62.3	13.2
50°-60°	48.0	10.1
60°-70°	32.8	6.9
70°-80°	21.3	4.5
80°-90°	13.3	2.8
90°-100°	7.7	1.6
100°-110°	2.4	0.5
110°-120°	0.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	218.5	46.1
0°-40°	285.7	60.3
0°-60°	395.9	83.6
0°-90°	463.3	97.8
90°-120°	10.2	2.2
90°-150°	10.2	2.2
90°-180°	10.0	2.1
0°-180°	473.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	724	
5°	580	50
15°	348	95
25°	149	74
35°	106	67
45°	81	62
55°	53	48
65°	33	33
75°	20	21
85°	12	11
90°	9	5
95°	7	5
105°	2	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P702288

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9050-4LBW1LI-CQ

CANDELA DISTRIBUTION (FULL):

0°	
0°	724.2
2.5°	692.1
5°	579.9
7.5°	471.5
10°	403.0
12.5°	369.3
15°	348.3
17.5°	321.2
20°	255.4
22.5°	178.6
25°	149.3
27.5°	134.9
30°	122.2
32.5°	112.2
35°	106.1
37.5°	102.3
40°	95.6
42.5°	87.9
45°	80.7
47.5°	73.5
50°	66.9
52.5°	59.7
55°	53.1
57.5°	47.5
60°	42.0
62.5°	37.0
65°	32.6
67.5°	29.3
70°	25.4
72.5°	22.7
75°	19.9
77.5°	17.7
80°	15.5
82.5°	13.8
85°	12.2
87.5°	10.5
90°	8.8
92.5°	8.3
95°	7.2
97.5°	6.1
100°	4.4
102.5°	3.3
105°	2.2
107.5°	1.1
110°	0.6

TEST NUMBER: P702288

CATALOG NUMBER: 340-6C-05-D010 / 340-EU4C-1020-9050-4LBW1LI-CQ

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)