

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702351

Luminaire Tested: 340-6C-08-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702351
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-13)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-08-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ
Description: FARALLON 6" LED GLASS DOWNLIGHT CYLINDRICAL FROSTED, QUADRATE ETCHED GLASS KIT.
Light Source: 2700K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 590.4 lumens
Efficiency: N/A
Efficacy: 59.6 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.54
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702351

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ

Luminous Intensity Polar Plot



TEST NUMBER: P702351

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	110	105	102	98	107	103	100	97	98	96	93		94	92	90		90	89	87	85
2	102	95	89	84	99	93	87	83	89	84	81		85	82	78		82	79	76	74
3	95	86	79	73	92	84	78	72	81	75	71		78	73	70		75	71	68	66
4	88	78	71	65	86	77	70	64	74	68	63		72	67	62		69	65	61	59
5	83	72	64	58	81	71	63	58	68	62	57		66	61	57		64	60	56	54
6	78	66	59	53	76	65	58	53	63	57	52		62	56	52		60	55	51	49
7	73	62	54	49	71	61	54	49	59	53	48		58	52	48		56	51	47	46
8	69	58	50	45	68	57	50	45	55	49	45		54	48	44		53	48	44	42
9	66	54	47	42	64	53	47	42	52	46	42		51	45	41		50	45	41	40
10	62	51	44	40	61	50	44	39	49	43	39		48	43	39		47	42	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58906
5°	42314
10°	26850
15°	21494
20°	14786
25°	8198
30°	6427
35°	5397
40°	4741
45°	3933
50°	3230
55°	2559
60°	2038
65°	1604
70°	1277
75°	1029
80°	832
85°	688

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3933 cd/sqm

TEST NUMBER: P702351

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.8	10.5
10°-20°	118.6	20.1
20°-30°	92.0	15.6
30°-40°	83.7	14.2
40°-50°	77.7	13.2
50°-60°	59.8	10.1
60°-70°	40.9	6.9
70°-80°	26.6	4.5
80°-90°	16.5	2.8
90°-100°	9.6	1.6
100°-110°	3.0	0.5
110°-120°	0.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.4	46.1
0°-40°	356.2	60.3
0°-60°	493.6	83.6
0°-90°	577.7	97.8
90°-120°	12.7	2.2
90°-150°	12.7	2.2
90°-180°	13.0	2.2
0°-180°	590.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	903	
5°	723	62
15°	434	119
25°	186	92
35°	132	84
45°	101	78
55°	66	60
65°	41	41
75°	25	27
85°	15	13
90°	11	6
95°	9	7
105°	3	3
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702351

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ

CANDELA DISTRIBUTION (FULL):

0°	
0°	902.9
2.5°	862.9
5°	723.0
7.5°	587.9
10°	502.5
12.5°	460.4
15°	434.2
17.5°	400.5
20°	318.4
22.5°	222.6
25°	186.1
27.5°	168.2
30°	152.3
32.5°	139.9
35°	132.3
37.5°	127.5
40°	119.2
42.5°	109.6
45°	100.6
47.5°	91.7
50°	83.4
52.5°	74.4
55°	66.2
57.5°	59.3
60°	52.4
62.5°	46.2
65°	40.7
67.5°	36.5
70°	31.7
72.5°	28.3
75°	24.8
77.5°	22.1
80°	19.3
82.5°	17.2
85°	15.2
87.5°	13.1
90°	11.0
92.5°	10.3
95°	9.0
97.5°	7.6
100°	5.5
102.5°	4.1
105°	2.8
107.5°	1.4
110°	0.7

TEST NUMBER: P702351

CATALOG NUMBER: 340-6C-08-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)