

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701997

Luminaire Tested: 340-4C-20-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P701997
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-7)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-20-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC
Description: FARALLON 4" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C
KIT.
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1286.4 lumens
Efficiency: N/A
Efficacy: 59.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.65
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P701997

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC

Luminous Intensity Polar Plot



TEST NUMBER: P701997

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	104	100	97	106	102	98	95	97	94	92		93	91	89		89	87	86	83
2	100	93	87	81	98	91	85	80	87	82	78		84	80	76		80	77	74	72
3	93	83	76	70	90	82	75	69	78	73	68		75	71	66		73	69	65	63
4	86	75	67	61	84	74	66	61	71	65	60		69	63	59		66	62	58	56
5	80	69	60	54	78	67	60	54	65	58	53		63	57	53		61	56	52	50
6	75	63	55	49	73	62	54	49	60	53	48		58	52	48		57	51	47	45
7	70	58	50	45	69	57	50	44	56	49	44		54	48	44		53	47	43	41
8	66	54	46	41	65	53	46	41	52	45	40		50	44	40		49	44	40	38
9	62	50	43	38	61	50	42	38	48	42	37		47	41	37		46	41	37	35
10	59	47	40	35	58	47	40	35	45	39	35		44	39	35		44	38	34	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149757
5°	128203
10°	91030
15°	57145
20°	40448
25°	29964
30°	24362
35°	20882
40°	18116
45°	15079
50°	12009
55°	9578
60°	7618
65°	6180
70°	5041
75°	4099
80°	3237
85°	2641

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15079 cd/sqm

TEST NUMBER: P701997

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.5	8.8
10°-20°	195.7	15.2
20°-30°	196.0	15.2
30°-40°	202.3	15.7
40°-50°	190.4	14.8
50°-60°	145.9	11.3
60°-70°	104.0	8.1
70°-80°	71.1	5.5
80°-90°	44.4	3.5
90°-100°	21.1	1.6
100°-110°	1.9	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	505.3	39.3
0°-40°	707.6	55.0
0°-60°	1043.9	81.2
0°-90°	1263.4	98.2
90°-120°	23.0	1.8
90°-150°	23.0	1.8
90°-180°	23.0	1.8
0°-180°	1286.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1291	
5°	1265	114
15°	692	196
25°	420	196
35°	323	202
45°	248	190
55°	162	146
65°	104	104
75°	67	71
85°	40	35
90°	31	17
95°	19	13
105°	0	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P701997

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1291.2
1°	1289.7
2°	1278.8
3°	1275.6
4°	1272.5
5°	1264.7
6°	1252.3
7°	1222.6
8°	1169.6
9°	1094.7
10°	1004.3
11°	912.3
12°	835.9
13°	776.6
14°	731.4
15°	692.4
16°	655.0
17°	622.2
18°	589.5
19°	558.3
20°	530.2
21°	503.7
22°	480.3
23°	458.5
24°	439.8
25°	419.5
27.5°	382.1
30°	360.2
32.5°	340.0
35°	322.8
37.5°	305.7
40°	290.1
42.5°	269.8
45°	248.0
47.5°	224.6
50°	201.2
52.5°	180.9
55°	162.2
57.5°	145.0
60°	129.4
62.5°	115.4
65°	104.5
67.5°	93.6
70°	84.2
72.5°	74.9

TEST NUMBER: P701997

CATALOG NUMBER: 340-4C-20-D010 / 340-EU4C-1020-9035-4LBW1LI-GFC

CANDELA DISTRIBUTION (continued):

	0°
75°	67.1
77.5°	59.3
80°	51.5
82.5°	45.2
85°	40.5
87.5°	35.9
90°	31.2
92.5°	26.5
95°	18.7
97.5°	12.5
100°	7.8
102.5°	3.1
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)