

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702037

Luminaire Tested: 340-4C-25-D010 / 340-EU4C-3040-9027-4LBW1LI-FF

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702037  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-4C-25-D010 / 340-EU4C-3040-9027-4LBW1LI-FF  
Description: FARALLON 4" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1482.7 lumens  
Efficiency: N/A  
Efficacy: 47.1 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.73  
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')  
CIE Type: Direct

Input Watts (W): 31.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702037

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9027-4LBW1LI-FF

### Luminous Intensity Polar Plot



TEST NUMBER: P702037

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9027-4LBW1LI-FF

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		100	100	100	97
1	109	105	102	98	107	103	99	96	98	95	93		94	92	90		90	88	86	84
2	102	95	89	85	99	93	88	83	89	85	81		86	82	79		82	80	77	75
3	95	87	80	75	93	85	79	74	82	77	72		79	75	71		76	73	69	67
4	89	80	73	67	87	78	72	67	76	70	65		73	68	64		71	67	63	61
5	84	74	66	61	82	73	66	61	70	64	60		68	63	59		66	62	58	56
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		62	58	54	52
7	75	64	57	52	73	63	56	52	62	56	51		60	55	51		59	54	50	49
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		55	51	47	45
9	68	57	50	45	66	56	50	45	55	49	45		54	48	44		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	163304
5°	141229
10°	121222
15°	103924
20°	88403
25°	59386
30°	22644
35°	16723
40°	13008
45°	10294
50°	8105
55°	6590
60°	5587
65°	5062
70°	4568
75°	4203
80°	3859
85°	3398

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10294 cd/sqm

TEST NUMBER: P702037

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9027-4LBW1LI-FF

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.2	8.8
10°-20°	353.2	23.8
20°-30°	349.4	23.6
30°-40°	163.9	11.1
40°-50°	130.9	8.8
50°-60°	101.0	6.8
60°-70°	84.8	5.7
70°-80°	72.7	4.9
80°-90°	56.8	3.8
90°-100°	32.8	2.2
100°-110°	6.0	0.4
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.8	56.2
0°-40°	997.7	67.3
0°-60°	1229.6	82.9
0°-90°	1444.0	97.4
90°-120°	38.8	2.6
90°-150°	38.8	2.6
90°-180°	39.0	2.6
0°-180°	1482.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1408	
5°	1393	131
15°	1259	353
25°	831	349
35°	258	164
45°	169	131
55°	112	101
65°	86	85
75°	69	73
85°	52	44
90°	43	24
95°	32	22
105°	4	6
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702037

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9027-4LBW1LI-FF

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1408.0
2.5°	1404.3
5°	1393.2
7.5°	1370.8
10°	1337.4
12.5°	1300.2
15°	1259.2
17.5°	1212.7
20°	1158.8
22.5°	1077.0
25°	831.4
27.5°	478.0
30°	334.8
32.5°	288.3
35°	258.5
37.5°	234.4
40°	208.3
42.5°	187.9
45°	169.3
47.5°	150.7
50°	135.8
52.5°	122.8
55°	111.6
57.5°	102.3
60°	94.9
62.5°	89.3
65°	85.6
67.5°	81.8
70°	76.3
72.5°	72.5
75°	68.8
77.5°	65.1
80°	61.4
82.5°	55.8
85°	52.1
87.5°	48.4
90°	42.8
92.5°	39.1
95°	31.6
97.5°	20.5
100°	14.9
102.5°	9.3
105°	3.7
107.5°	1.9
110°	0.0

TEST NUMBER: P702037

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9027-4LBW1LI-FF

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)