

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702066

Luminaire Tested: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702066
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-8)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC
Description: FARALLON 4" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1991.4 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.34' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702066

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC

Luminous Intensity Polar Plot



TEST NUMBER: P702066

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	94	93	91
2	106	101	96	92	104	99	95	91	95	92	89		92	89	87		89	87	85	83
3	100	93	87	83	98	91	86	82	88	84	80		86	82	79		84	81	78	76
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78	75	72	70
5	89	80	73	68	87	79	72	68	77	71	67		75	70	67		73	69	66	64
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69	65	61	60
7	79	69	63	58	78	69	62	58	67	62	58		66	61	57		65	60	57	55
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	56	53	52
9	71	61	55	50	70	61	54	50	60	54	50		59	53	50		58	53	50	48
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	244817
5°	236194
10°	224769
15°	216182
20°	183412
25°	153005
30°	114520
35°	82235
40°	64892
45°	43024
50°	31432
55°	22263
60°	15333
65°	13201
70°	11530
75°	9859
80°	8015
85°	7985

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43024 cd/sqm

TEST NUMBER: P702066

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	9.5
10°-20°	490.8	24.6
20°-30°	540.0	27.1
30°-40°	374.4	18.8
40°-50°	213.4	10.7
50°-60°	101.4	5.1
60°-70°	48.0	2.4
70°-80°	23.5	1.2
80°-90°	6.8	0.3
90°-100°	2.5	0.1
100°-110°	1.6	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1219.8	61.3
0°-40°	1594.2	80.1
0°-60°	1909.0	95.9
0°-90°	1987.3	99.8
90°-120°	4.1	0.2
90°-150°	4.1	0.2
90°-180°	4.0	0.2
0°-180°	1991.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2111	
5°	2029	189
15°	1800	491
25°	1196	540
35°	581	374
45°	262	213
55°	110	101
65°	48	48
75°	22	23
85°	6	6
90°	2	1
95°	2	2
105°	2	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702066

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2110.8
1°	2098.8
2°	2078.8
3°	2066.7
4°	2048.7
5°	2028.7
6°	1996.7
7°	1964.6
8°	1940.6
9°	1930.6
10°	1908.5
11°	1874.5
12°	1858.5
13°	1850.5
14°	1834.4
15°	1800.4
16°	1754.3
17°	1692.2
18°	1622.2
19°	1548.1
20°	1486.0
21°	1431.9
22°	1377.8
23°	1321.8
24°	1263.7
25°	1195.6
27.5°	1023.4
30°	855.1
32.5°	696.9
35°	580.8
37.5°	496.7
40°	428.6
42.5°	342.5
45°	262.3
47.5°	210.3
50°	174.2
52.5°	142.2
55°	110.1
57.5°	84.1
60°	66.1
62.5°	56.1
65°	48.1
67.5°	40.1
70°	34.0
72.5°	28.0

TEST NUMBER: P702066

CATALOG NUMBER: 340-4C-25-D010 / 340-EU4C-3040-9050-4LBW1LI-GCC

CANDELA DISTRIBUTION (continued):

	0°
75°	22.0
77.5°	16.0
80°	12.0
82.5°	8.0
85°	6.0
87.5°	4.0
90°	2.0
92.5°	2.0
95°	2.0
97.5°	2.0
100°	4.0
102.5°	2.0
105°	2.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)