

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702128

Luminaire Tested: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-FF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-2)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-FF
Description: FARALLON 4" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.
Light Source: 2700K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1738.6 lumens
Efficiency: N/A
Efficacy: 55.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.73
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702128

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-FF

Luminous Intensity Polar Plot



TEST NUMBER: P702128

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-FF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		100	100	100	97
1	109	105	102	98	107	103	99	96	98	95	93		94	92	90		90	88	86	84
2	102	95	89	85	99	93	88	83	89	85	81		86	82	79		82	80	77	75
3	95	87	80	75	93	85	79	74	82	77	72		79	75	71		76	73	69	67
4	89	80	73	67	87	78	72	67	76	70	65		73	68	64		71	67	63	61
5	84	74	66	61	82	73	66	61	70	64	60		68	63	59		66	62	58	56
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		62	58	54	52
7	75	64	57	52	73	63	56	52	62	56	51		60	55	51		59	54	50	49
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		55	51	47	45
9	68	57	50	45	66	56	50	45	55	49	45		54	48	44		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	191500
5°	165598
10°	142142
15°	121867
20°	103661
25°	69643
30°	26553
35°	19614
40°	15256
45°	12069
50°	9502
55°	7729
60°	6546
65°	5932
70°	5352
75°	4930
80°	4525
85°	3985

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12069 cd/sqm

TEST NUMBER: P702128

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-FF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.8	8.8
10°-20°	414.2	23.8
20°-30°	409.7	23.6
30°-40°	192.2	11.1
40°-50°	153.4	8.8
50°-60°	118.5	6.8
60°-70°	99.5	5.7
70°-80°	85.3	4.9
80°-90°	66.6	3.8
90°-100°	38.4	2.2
100°-110°	7.0	0.4
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	977.7	56.2
0°-40°	1169.9	67.3
0°-60°	1441.8	82.9
0°-90°	1693.2	97.4
90°-120°	45.4	2.6
90°-150°	45.4	2.6
90°-180°	45.0	2.6
0°-180°	1738.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1651	
5°	1634	154
15°	1477	414
25°	975	410
35°	303	192
45°	198	153
55°	131	118
65°	100	99
75°	81	85
85°	61	52
90°	50	28
95°	37	25
105°	4	7
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702128

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-FF

CANDELA DISTRIBUTION (FULL):

0°	
0°	1651.1
2.5°	1646.7
5°	1633.6
7.5°	1607.5
10°	1568.2
12.5°	1524.6
15°	1476.6
17.5°	1422.1
20°	1358.8
22.5°	1262.9
25°	975.0
27.5°	560.5
30°	392.6
32.5°	338.1
35°	303.2
37.5°	274.8
40°	244.3
42.5°	220.3
45°	198.5
47.5°	176.7
50°	159.2
52.5°	144.0
55°	130.9
57.5°	120.0
60°	111.2
62.5°	104.7
65°	100.3
67.5°	96.0
70°	89.4
72.5°	85.1
75°	80.7
77.5°	76.3
80°	72.0
82.5°	65.4
85°	61.1
87.5°	56.7
90°	50.2
92.5°	45.8
95°	37.1
97.5°	24.0
100°	17.4
102.5°	10.9
105°	4.4
107.5°	2.2
110°	0.0

TEST NUMBER: P702128

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9727-4LBW1LI-FF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)