

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702100

Luminaire Tested: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-2)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-FF
Description: FARALLON 4" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1807.9 lumens
Efficiency: N/A
Efficacy: 57.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.73
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702100

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

Luminous Intensity Polar Plot



TEST NUMBER: P702100

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		100	100	100	97
1	109	105	102	98	107	103	99	96	98	95	93		94	92	90		90	88	86	84
2	102	95	89	85	99	93	88	83	89	85	81		86	82	79		82	80	77	75
3	95	87	80	75	93	85	79	74	82	77	72		79	75	71		76	73	69	67
4	89	80	73	67	87	78	72	67	76	70	65		73	68	64		71	67	63	61
5	84	74	66	61	82	73	66	61	70	64	60		68	63	59		66	62	58	56
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		62	58	54	52
7	75	64	57	52	73	63	56	52	62	56	51		60	55	51		59	54	50	49
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		55	51	47	45
9	68	57	50	45	66	56	50	45	55	49	45		54	48	44		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	199143
5°	172208
10°	147816
15°	126728
20°	107796
25°	72414
30°	27615
35°	20397
40°	15862
45°	12550
50°	9884
55°	8036
60°	6811
65°	6168
70°	5568
75°	5125
80°	4701
85°	4141

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12550 cd/sqm

TEST NUMBER: P702100

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.0	8.8
10°-20°	430.7	23.8
20°-30°	426.0	23.6
30°-40°	199.8	11.1
40°-50°	159.6	8.8
50°-60°	123.2	6.8
60°-70°	103.4	5.7
70°-80°	88.7	4.9
80°-90°	69.3	3.8
90°-100°	39.9	2.2
100°-110°	7.2	0.4
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1016.7	56.2
0°-40°	1216.6	67.3
0°-60°	1499.3	82.9
0°-90°	1760.7	97.4
90°-120°	47.2	2.6
90°-150°	47.2	2.6
90°-180°	47.0	2.6
0°-180°	1807.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1717	
5°	1699	160
15°	1536	431
25°	1014	426
35°	315	200
45°	206	160
55°	136	123
65°	104	103
75°	84	89
85°	64	54
90°	52	29
95°	39	26
105°	4	7
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702100

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

CANDELA DISTRIBUTION (FULL):

0°	
0°	1717.0
2.5°	1712.4
5°	1698.8
7.5°	1671.6
10°	1630.8
12.5°	1585.4
15°	1535.5
17.5°	1478.8
20°	1413.0
22.5°	1313.2
25°	1013.8
27.5°	582.9
30°	408.3
32.5°	351.6
35°	315.3
37.5°	285.8
40°	254.0
42.5°	229.1
45°	206.4
47.5°	183.7
50°	165.6
52.5°	149.7
55°	136.1
57.5°	124.7
60°	115.7
62.5°	108.9
65°	104.3
67.5°	99.8
70°	93.0
72.5°	88.5
75°	83.9
77.5°	79.4
80°	74.8
82.5°	68.0
85°	63.5
87.5°	59.0
90°	52.2
92.5°	47.6
95°	38.6
97.5°	24.9
100°	18.1
102.5°	11.3
105°	4.5
107.5°	2.3
110°	0.0

TEST NUMBER: P702100

CATALOG NUMBER: 340-4C-30-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)