

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702150

Luminaire Tested: 340-4C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-GCC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-8)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-GCC
Description: FARALLON 4" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2562.7 lumens
Efficiency: N/A
Efficacy: 63.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.34' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702150

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-GCC

Luminous Intensity Polar Plot



TEST NUMBER: P702150

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-GCC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	94	93	91
2	106	101	96	92	104	99	95	91	95	92	89		92	89	87		89	87	85	83
3	100	93	87	83	98	91	86	82	88	84	80		86	82	79		84	81	78	76
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78	75	72	70
5	89	80	73	68	87	79	72	68	77	71	67		75	70	67		73	69	66	64
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69	65	61	60
7	79	69	63	58	78	69	62	58	67	62	58		66	61	57		65	60	57	55
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	56	53	52
9	71	61	55	50	70	61	54	50	60	54	50		59	53	50		58	53	50	48
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	315045
5°	303954
10°	289249
15°	278201
20°	236029
25°	196900
30°	147372
35°	105824
40°	83500
45°	55375
50°	40454
55°	28653
60°	19717
65°	16988
70°	14853
75°	12682
80°	10353
85°	10247

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 55375 cd/sqm

TEST NUMBER: P702150

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-GCC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.3	9.5
10°-20°	631.6	24.6
20°-30°	694.8	27.1
30°-40°	481.8	18.8
40°-50°	274.6	10.7
50°-60°	130.5	5.1
60°-70°	61.8	2.4
70°-80°	30.2	1.2
80°-90°	8.8	0.3
90°-100°	3.2	0.1
100°-110°	2.1	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1569.7	61.3
0°-40°	2051.4	80.1
0°-60°	2456.6	95.9
0°-90°	2557.4	99.8
90°-120°	5.3	0.2
90°-150°	5.3	0.2
90°-180°	5.0	0.2
0°-180°	2562.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2716	
5°	2611	243
15°	2317	632
25°	1539	695
35°	747	482
45°	338	275
55°	142	131
65°	62	62
75°	28	30
85°	8	8
90°	3	2
95°	3	2
105°	3	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702150

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-GCC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2716.3
1°	2700.9
2°	2675.1
3°	2659.6
4°	2636.4
5°	2610.7
6°	2569.4
7°	2528.2
8°	2497.3
9°	2484.4
10°	2456.0
11°	2412.2
12°	2391.6
13°	2381.3
14°	2360.7
15°	2316.9
16°	2257.6
17°	2177.7
18°	2087.5
19°	1992.1
20°	1912.3
21°	1842.7
22°	1773.1
23°	1700.9
24°	1626.2
25°	1538.6
27.5°	1316.9
30°	1100.4
32.5°	896.9
35°	747.4
37.5°	639.1
40°	551.5
42.5°	440.7
45°	337.6
47.5°	270.6
50°	224.2
52.5°	183.0
55°	141.7
57.5°	108.2
60°	85.0
62.5°	72.2
65°	61.9
67.5°	51.5
70°	43.8
72.5°	36.1

TEST NUMBER: P702150

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9027-4LBW1LI-GCC

CANDELA DISTRIBUTION (continued):

	0°
75°	28.3
77.5°	20.6
80°	15.5
82.5°	10.3
85°	7.7
87.5°	5.2
90°	2.6
92.5°	2.6
95°	2.6
97.5°	2.6
100°	5.2
102.5°	2.6
105°	2.6
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)