

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702184

Luminaire Tested: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-FF

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702184  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-FF  
Description: FARALLON 4" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.  
Light Source: 2700K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2054.2 lumens  
Efficiency: N/A  
Efficacy: 50.8 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.73  
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')  
CIE Type: Direct

Input Watts (W): 40.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702184

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-FF

### Luminous Intensity Polar Plot



TEST NUMBER: P702184

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-FF

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		100	100	100	97
1	109	105	102	98	107	103	99	96	98	95	93		94	92	90		90	88	86	84
2	102	95	89	85	99	93	88	83	89	85	81		86	82	79		82	80	77	75
3	95	87	80	75	93	85	79	74	82	77	72		79	75	71		76	73	69	67
4	89	80	73	67	87	78	72	67	76	70	65		73	68	64		71	67	63	61
5	84	74	66	61	82	73	66	61	70	64	60		68	63	59		66	62	58	56
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		62	58	54	52
7	75	64	57	52	73	63	56	52	62	56	51		60	55	51		59	54	50	49
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		55	51	47	45
9	68	57	50	45	66	56	50	45	55	49	45		54	48	44		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	226272
5°	195675
10°	167956
15°	143994
20°	122489
25°	82286
30°	31376
35°	23172
40°	18023
45°	14258
50°	11227
55°	9129
60°	7735
65°	7008
70°	6328
75°	5828
80°	5342
85°	4709

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14258 cd/sqm

TEST NUMBER: P702184

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-FF

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	181.8	8.8
10°-20°	489.4	23.8
20°-30°	484.1	23.6
30°-40°	227.1	11.1
40°-50°	181.3	8.8
50°-60°	140.0	6.8
60°-70°	117.5	5.7
70°-80°	100.8	4.9
80°-90°	78.7	3.8
90°-100°	45.4	2.2
100°-110°	8.3	0.4
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1155.3	56.2
0°-40°	1382.3	67.3
0°-60°	1703.6	82.9
0°-90°	2000.6	97.4
90°-120°	53.7	2.6
90°-150°	53.7	2.6
90°-180°	54.0	2.6
0°-180°	2054.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1951	
5°	1930	182
15°	1745	489
25°	1152	484
35°	358	227
45°	234	181
55°	155	140
65°	118	118
75°	95	101
85°	72	61
90°	59	33
95°	44	30
105°	5	8
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702184

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-FF

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1950.9
2.5°	1945.7
5°	1930.3
7.5°	1899.4
10°	1853.0
12.5°	1801.4
15°	1744.7
17.5°	1680.3
20°	1605.6
22.5°	1492.2
25°	1152.0
27.5°	662.3
30°	463.9
32.5°	399.5
35°	358.2
37.5°	324.7
40°	288.6
42.5°	260.3
45°	234.5
47.5°	208.7
50°	188.1
52.5°	170.1
55°	154.6
57.5°	141.7
60°	131.4
62.5°	123.7
65°	118.5
67.5°	113.4
70°	105.7
72.5°	100.5
75°	95.4
77.5°	90.2
80°	85.0
82.5°	77.3
85°	72.2
87.5°	67.0
90°	59.3
92.5°	54.1
95°	43.8
97.5°	28.3
100°	20.6
102.5°	12.9
105°	5.2
107.5°	2.6
110°	0.0

TEST NUMBER: P702184

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9727-4LBW1LI-FF

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)