

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702191

Luminaire Tested: 340-4C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-FF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702191
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-2)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-FF
Description: FARALLON 4" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.
Light Source: 3000K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2135.5 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.73
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702191

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-FF

Luminous Intensity Polar Plot



TEST NUMBER: P702191

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-FF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		100	100	100	97
1	109	105	102	98	107	103	99	96	98	95	93		94	92	90		90	88	86	84
2	102	95	89	85	99	93	88	83	89	85	81		86	82	79		82	80	77	75
3	95	87	80	75	93	85	79	74	82	77	72		79	75	71		76	73	69	67
4	89	80	73	67	87	78	72	67	76	70	65		73	68	64		71	67	63	61
5	84	74	66	61	82	73	66	61	70	64	60		68	63	59		66	62	58	56
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		62	58	54	52
7	75	64	57	52	73	63	56	52	62	56	51		60	55	51		59	54	50	49
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		55	51	47	45
9	68	57	50	45	66	56	50	45	55	49	45		54	48	44		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	235214
5°	203409
10°	174591
15°	149688
20°	127325
25°	85536
30°	32613
35°	24091
40°	18741
45°	14824
50°	11674
55°	9489
60°	8041
65°	7286
70°	6574
75°	6054
80°	5556
85°	4891

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14824 cd/sqm

TEST NUMBER: P702191

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-FF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	8.8
10°-20°	508.7	23.8
20°-30°	503.2	23.6
30°-40°	236.0	11.1
40°-50°	188.5	8.8
50°-60°	145.5	6.8
60°-70°	122.2	5.7
70°-80°	104.8	4.9
80°-90°	81.8	3.8
90°-100°	47.2	2.2
100°-110°	8.6	0.4
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1200.9	56.2
0°-40°	1437.0	67.3
0°-60°	1770.9	82.9
0°-90°	2079.7	97.4
90°-120°	55.8	2.6
90°-150°	55.8	2.6
90°-180°	56.0	2.6
0°-180°	2135.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2028	
5°	2007	189
15°	1814	509
25°	1198	503
35°	372	236
45°	244	188
55°	161	145
65°	123	122
75°	99	105
85°	75	64
90°	62	34
95°	46	31
105°	5	9
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702191

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-FF

CANDELA DISTRIBUTION (FULL):

0°	
0°	2028.0
2.5°	2022.7
5°	2006.6
7.5°	1974.4
10°	1926.2
12.5°	1872.6
15°	1813.7
17.5°	1746.7
20°	1669.0
22.5°	1551.2
25°	1197.5
27.5°	688.5
30°	482.2
32.5°	415.2
35°	372.4
37.5°	337.6
40°	300.1
42.5°	270.6
45°	243.8
47.5°	217.0
50°	195.6
52.5°	176.8
55°	160.7
57.5°	147.3
60°	136.6
62.5°	128.6
65°	123.2
67.5°	117.9
70°	109.8
72.5°	104.5
75°	99.1
77.5°	93.8
80°	88.4
82.5°	80.4
85°	75.0
87.5°	69.7
90°	61.6
92.5°	56.3
95°	45.5
97.5°	29.5
100°	21.4
102.5°	13.4
105°	5.4
107.5°	2.7
110°	0.0

TEST NUMBER: P702191

CATALOG NUMBER: 340-4C-35-D010 / 340-EU4C-3040-9730-4LBW1LI-FF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)