

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P600600

Luminaire Tested: 205-90-30K-LL7-UNV-STD-X-X-WHHR-SR-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 205-90-30K-LL7-UNV-STD-X-X-WHHR-SR-X
Description: SHAPER PrentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5686.0 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 55.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600600
CATALOG NUMBER: 205-90-30K-LL7-UNV-STD-X-X-WHHR-SR-X

Luminous Intensity Polar Plot





TEST NUMBER: P600600

CATALOG NUMBER: 205-90-30K-LL7-UNV-STD-X-X-WHHR-SR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100															
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	88					88															
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77															
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68					68															
4	89	79	71	65	87	77	70	65	75	69	64	73	68	63	71	66	63	61					61															
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54					54															
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49					49															
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	56	50	46	44					44															
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41					41															
9	64	52	44	39	62	51	44	39	50	44	39	49	43	39	48	43	39	37					37															
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34					34															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28858
5°	25627
10°	23676
15°	23095
20°	22846
25°	22795
30°	22639
35°	22443
40°	19893
45°	8097
50°	7126
55°	6895
60°	6749
65°	6467
70°	6205
75°	5957
80°	5714
85°	5608

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8097 cd/sqm



TEST NUMBER: P600600

CATALOG NUMBER: 205-90-30K-LL7-UNV-STD-X-X-WHHR-SR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	308.4	5.4
10°-20°	818.0	14.4
20°-30°	1234.6	21.7
30°-40°	1472.3	25.9
40°-50°	761.3	13.4
50°-60°	459.2	8.1
60°-70°	351.8	6.2
70°-80°	211.0	3.7
80°-90°	69.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2361.0	41.5
0°-40°	3833.4	67.4
0°-60°	5053.9	88.9
0°-90°	5686.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5686.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3743	
5°	3312	308
15°	2894	818
25°	2680	1235
35°	2385	1472
45°	743	761
55°	513	459
65°	354	352
75°	200	211
85°	63	69
90°	0	



TEST NUMBER: P600600

CATALOG NUMBER: 205-90-30K-LL7-UNV-STD-X-X-WHHR-SR-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	3743.4
2.5°	3624.6
5°	3311.6
7.5°	3121.5
10°	3024.5
12.5°	2955.1
15°	2893.7
17.5°	2838.3
20°	2784.8
22.5°	2735.3
25°	2679.8
27.5°	2618.4
30°	2543.2
32.5°	2454.0
35°	2384.7
37.5°	2311.4
40°	1976.7
42.5°	1317.1
45°	742.7
47.5°	661.5
50°	594.2
52.5°	546.7
55°	513.0
57.5°	477.3
60°	437.7
62.5°	396.1
65°	354.5
67.5°	314.9
70°	275.3
72.5°	235.7
75°	200.0
77.5°	162.4
80°	128.7
82.5°	95.1
85°	63.4
87.5°	31.7
90°	0.0

(END OF REPORT)