

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P600605

Luminaire Tested: 205-90-35K-LL1-UNV-STD-X-X-WHHR-FL-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 205-90-35K-LL1-UNV-STD-X-X-WHHR-FL-X
Description: SHAPER PrentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1124.8 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600605
CATALOG NUMBER: 205-90-35K-LL1-UNV-STD-X-X-WHHR-FL-X

Luminous Intensity Polar Plot





TEST NUMBER: P600605

CATALOG NUMBER: 205-90-35K-LL1-UNV-STD-X-X-WHHR-FL-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100															
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	88					88															
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77					77															
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68					68															
4	89	79	71	65	87	77	70	65	75	69	64	73	68	63	71	66	63	61					61															
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54					54															
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49					49															
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	56	50	46	44					44															
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41					41															
9	64	52	44	39	62	51	44	39	50	44	39	49	43	39	48	43	39	37					37															
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34					34															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5709
5°	5070
10°	4684
15°	4568
20°	4520
25°	4509
30°	4478
35°	4439
40°	3935
45°	1602
50°	1409
55°	1364
60°	1335
65°	1279
70°	1228
75°	1180
80°	1132
85°	1106

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1602 cd/sqm



TEST NUMBER: P600605

CATALOG NUMBER: 205-90-35K-LL1-UNV-STD-X-X-WHHR-FL-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.0	5.4
10°-20°	161.8	14.4
20°-30°	244.2	21.7
30°-40°	291.2	25.9
40°-50°	150.6	13.4
50°-60°	90.8	8.1
60°-70°	69.6	6.2
70°-80°	41.8	3.7
80°-90°	13.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	467.1	41.5
0°-40°	758.3	67.4
0°-60°	999.7	88.9
0°-90°	1124.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	740	
5°	655	61
15°	572	162
25°	530	244
35°	472	291
45°	147	151
55°	102	91
65°	70	70
75°	40	42
85°	12	14
90°	0	



TEST NUMBER: P600605
CATALOG NUMBER: 205-90-35K-LL1-UNV-STD-X-X-WHHR-FL-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	740.5
2.5°	717.0
5°	655.1
7.5°	617.5
10°	598.3
12.5°	584.6
15°	572.4
17.5°	561.5
20°	550.9
22.5°	541.1
25°	530.1
27.5°	518.0
30°	503.1
32.5°	485.4
35°	471.7
37.5°	457.2
40°	391.0
42.5°	260.5
45°	146.9
47.5°	130.9
50°	117.5
52.5°	108.1
55°	101.5
57.5°	94.4
60°	86.6
62.5°	78.4
65°	70.1
67.5°	62.3
70°	54.5
72.5°	46.6
75°	39.6
77.5°	32.1
80°	25.5
82.5°	18.8
85°	12.5
87.5°	6.3
90°	0.0

(END OF REPORT)