

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702212

Luminaire Tested: 340-4C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702212  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-4C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-FF  
Description: FARALLON 4" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2476.7 lumens  
Efficiency: N/A  
Efficacy: 52.7 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.73  
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702212

CATALOG NUMBER: 340-4C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

### Luminous Intensity Polar Plot



TEST NUMBER: P702212

CATALOG NUMBER: 340-4C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		100	100	100	97
1	109	105	102	98	107	103	99	96	98	95	93		94	92	90		90	88	86	84
2	102	95	89	85	99	93	88	83	89	85	81		86	82	79		82	80	77	75
3	95	87	80	75	93	85	79	74	82	77	72		79	75	71		76	73	69	67
4	89	80	73	67	87	78	72	67	76	70	65		73	68	64		71	67	63	61
5	84	74	66	61	82	73	66	61	70	64	60		68	63	59		66	62	58	56
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		62	58	54	52
7	75	64	57	52	73	63	56	52	62	56	51		60	55	51		59	54	50	49
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		55	51	47	45
9	68	57	50	45	66	56	50	45	55	49	45		54	48	44		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	272804
5°	235909
10°	202490
15°	173606
20°	147672
25°	99207
30°	37828
35°	27940
40°	21732
45°	17189
50°	13536
55°	11007
60°	9331
65°	8451
70°	7627
75°	7025
80°	6442
85°	5674

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17189 cd/sqm

TEST NUMBER: P702212

CATALOG NUMBER: 340-4C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	219.2	8.8
10°-20°	590.0	23.8
20°-30°	583.6	23.6
30°-40°	273.8	11.1
40°-50°	218.6	8.8
50°-60°	168.8	6.8
60°-70°	141.7	5.7
70°-80°	121.5	4.9
80°-90°	94.9	3.8
90°-100°	54.7	2.2
100°-110°	9.9	0.4
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1392.8	56.2
0°-40°	1666.6	67.3
0°-60°	2053.9	82.9
0°-90°	2412.0	97.4
90°-120°	64.7	2.6
90°-150°	64.7	2.6
90°-180°	65.0	2.6
0°-180°	2476.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2352	
5°	2327	219
15°	2104	590
25°	1389	584
35°	432	274
45°	283	219
55°	186	169
65°	143	142
75°	115	122
85°	87	74
90°	72	40
95°	53	36
105°	6	10
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P702212

CATALOG NUMBER: 340-4C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2352.1
2.5°	2345.9
5°	2327.2
7.5°	2289.9
10°	2234.0
12.5°	2171.9
15°	2103.5
17.5°	2025.8
20°	1935.7
22.5°	1799.0
25°	1388.9
27.5°	798.5
30°	559.3
32.5°	481.6
35°	431.9
37.5°	391.5
40°	348.0
42.5°	313.8
45°	282.7
47.5°	251.7
50°	226.8
52.5°	205.1
55°	186.4
57.5°	170.9
60°	158.5
62.5°	149.1
65°	142.9
67.5°	136.7
70°	127.4
72.5°	121.2
75°	115.0
77.5°	108.7
80°	102.5
82.5°	93.2
85°	87.0
87.5°	80.8
90°	71.5
92.5°	65.2
95°	52.8
97.5°	34.2
100°	24.9
102.5°	15.5
105°	6.2
107.5°	3.1
110°	0.0

TEST NUMBER: P702212

CATALOG NUMBER: 340-4C-40-D010 / 340-EU4C-3040-9030-4LBW1LI-FF

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)