

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701797

Luminaire Tested: 340-4C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P701797
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-4)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-CF
Description: FARALLON 4" LED GLASS DOWNLIGHT. CYLINDRICAL FROSTED GLASS KIT.
Light Source: 3000K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 433.0 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.45
Luminous Opening: (L: -0.34 ' x W: 0 ' x H: 0.46 '
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P701797

CATALOG NUMBER: 340-4C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

Luminous Intensity Polar Plot




TEST NUMBER: P701797

CATALOG NUMBER: 340-4C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	98	106	103	99	96	98	95	92		94	91	89		90	88	86	84
2	101	94	88	83	98	92	86	82	88	83	80		85	81	77		81	78	75	73
3	94	85	78	72	91	83	76	71	80	74	70		77	72	68		74	70	67	65
4	87	77	70	64	85	76	69	63	73	67	62		71	65	61		68	64	60	58
5	82	71	63	57	80	70	62	57	67	61	56		65	60	55		63	59	55	53
6	77	65	58	52	75	64	57	52	62	56	51		61	55	51		59	54	50	48
7	72	61	53	48	71	60	53	48	58	52	47		57	51	47		55	50	46	45
8	69	57	49	44	67	56	49	44	55	48	44		53	48	43		52	47	43	41
9	65	53	46	41	64	53	46	41	52	45	41		50	45	41		49	44	40	39
10	62	50	43	39	61	50	43	39	49	43	39		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):



MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: -
 Vertical Angle: -
 Luminance: -

TEST NUMBER: P701797

CATALOG NUMBER: 340-4C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.7	11.9
10°-20°	81.5	18.8
20°-30°	56.7	13.1
30°-40°	58.1	13.4
40°-50°	58.9	13.6
50°-60°	47.7	11.0
60°-70°	33.7	7.8
70°-80°	22.0	5.1
80°-90°	13.8	3.2
90°-100°	7.5	1.7
100°-110°	1.4	0.3
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	189.9	43.9
0°-40°	247.9	57.3
0°-60°	354.5	81.9
0°-90°	424.1	98.0
90°-120°	8.9	2.0
90°-150°	8.9	2.0
90°-180°	9.0	2.1
0°-180°	433.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	836	
5°	632	52
15°	320	82
25°	121	57
35°	93	58
45°	77	59
55°	53	48
65°	34	34
75°	21	22
85°	13	11
90°	10	5
95°	7	5
105°	1	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P701797

CATALOG NUMBER: 340-4C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

CANDELA DISTRIBUTION (FULL):

0°	
0°	836.4
1°	833.4
2°	812.6
3°	765.1
4°	700.9
5°	631.6
6°	561.8
7°	499.1
8°	454.1
9°	418.7
10°	392.9
11°	374.2
12°	359.0
13°	346.4
14°	334.3
15°	319.6
16°	296.3
17°	264.5
18°	228.1
19°	193.2
20°	166.9
21°	150.7
22°	140.1
23°	133.5
24°	127.4
25°	121.4
27.5°	108.2
30°	99.6
32.5°	94.6
35°	93.0
37.5°	90.0
40°	86.5
42.5°	81.9
45°	76.9
47.5°	70.8
50°	64.7
52.5°	58.7
55°	53.1
57.5°	48.0
60°	43.0
62.5°	37.9
65°	33.9
67.5°	29.8
70°	26.3
72.5°	23.3

TEST NUMBER: P701797

CATALOG NUMBER: 340-4C-05-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

CANDELA DISTRIBUTION (continued):

	0°
75°	20.7
77.5°	18.2
80°	16.2
82.5°	14.2
85°	12.6
87.5°	11.1
90°	9.6
92.5°	8.6
95°	7.1
97.5°	5.1
100°	3.5
102.5°	2.0
105°	1.0
107.5°	0.5
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)