

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P155284

Luminaire Tested: **AVM-F06-LED-E-U-T3-HSS-7030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P155284  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33724)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: AVM-F06-LED-E-U-T3-HSS-7030  
Description: VISION SITE MEDIUM LED LUMINAIRE  
(6) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 AREA W/ HOUSE SIDE SHIELD  
Light Source: (42) 3000K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7375.5 lumens  
Efficiency: N/A  
Efficacy: 47.1 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type III - Short - Non-Cutoff  
BUG Rating: B0 - U0 - G2  
  
Input Watts (W): 156.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P155284  
 CATALOG NUMBER: AVM-F06-LED-E-U-T3-HSS-7030

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 10.7 fc  
 Type III - Short - Non-Cutoff

REPORT NUMBER: P155284  
CATALOG NUMBER: AVM-F06-LED-E-U-T3-HSS-7030

### Luminous Intensity Polar Plot



— Vertical Plane Through 66-Deg Lateral    - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P155284

CATALOG NUMBER: AVM-F06-LED-E-U-T3-HSS-7030

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	148.1	0.0	148.1
	% Fixture	2.0	0.0	2.0
<b>Street Side</b>	Lumens	7227.4	0.0	7227.4
	% Fixture	98.0	0.0	98.0
<b>Total</b>	Lumens	7375.5	0.0	7375.5
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.1	0.3
10°-20°	119.9	1.6
20°-30°	274.0	3.7
30°-40°	521.2	7.1
40°-50°	1046.1	14.2
50°-60°	1851.0	25.1
60°-70°	2418.5	32.8
70°-80°	994.4	13.5
80°-90°	125.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7375.5	100.0
0°-180°	7375.5	100.0



REPORT NUMBER: P155284


CATALOG NUMBER: AVM-F06-LED-E-U-T3-HSS-7030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	372.7	5.1			
FM	(30°-60°)	3354.9	45.5			
FH	(60°-80°)	3380.1	45.8			G2/5000
FVH	(80°-90°)	119.7	1.6			G2/225
BL	(0°-30°)	46.3	0.6	B0/110		
BM	(30°-60°)	63.4	0.9	B0/220		
BH	(60°-80°)	32.8	0.4	B0/110		G0/110
BVH	(80°-90°)	5.6	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B0-U0-G2**

Type III Short





REPORT NUMBER: P155284

CATALOG NUMBER: AVM-F06-LED-E-U-T3-HSS-7030

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	56°	57°	58°	59°
0°	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1
2.5°	271.4	266.9	268.4	259.4	253.3	245.8	239.8	238.3	236.8	233.7	235.2
5°	390.6	386.0	375.5	357.4	340.8	315.2	289.5	288.0	283.5	279.0	276.0
7.5°	542.9	535.3	523.3	493.1	452.4	407.2	355.9	351.4	345.3	339.3	333.3
10°	719.3	714.8	692.2	657.5	595.7	521.8	435.8	431.3	417.7	410.2	404.1
12.5°	904.8	885.2	876.1	815.8	744.9	643.9	533.8	517.2	506.7	496.1	481.0
15°	1045.0	1048.1	1026.9	978.7	895.7	778.1	640.9	622.8	607.7	588.1	570.0
17.5°	1171.7	1165.7	1143.1	1112.9	1034.5	915.3	755.5	731.4	707.2	696.7	671.1
20°	1274.2	1271.2	1253.1	1224.5	1164.2	1049.6	876.1	856.5	829.4	811.3	782.6
22.5°	1355.7	1355.7	1345.1	1328.5	1269.7	1177.7	1004.3	983.2	956.1	933.4	901.8
25°	1420.5	1419.0	1420.5	1413.0	1373.8	1289.3	1135.5	1111.4	1088.8	1061.6	1031.5
27.5°	1494.4	1497.4	1494.4	1489.9	1473.3	1405.4	1268.2	1251.6	1226.0	1197.3	1167.2
30°	1609.0	1600.0	1598.5	1595.5	1575.8	1533.6	1405.4	1385.8	1366.2	1346.6	1325.5
32.5°	1729.7	1714.6	1710.1	1710.1	1696.5	1658.8	1563.8	1553.2	1524.6	1509.5	1491.4
35°	1866.9	1860.9	1854.8	1856.3	1850.3	1811.1	1732.7	1735.7	1726.6	1696.5	1678.4
37.5°	2067.5	2069.0	2058.4	2038.8	2038.8	2004.1	1958.9	1952.8	1930.2	1922.7	1912.1
40°	2354.0	2346.4	2337.4	2308.7	2298.2	2239.4	2197.1	2182.1	2164.0	2162.5	2150.4
42.5°	2685.7	2676.7	2676.7	2655.6	2634.5	2563.6	2483.7	2473.1	2453.5	2459.5	2455.0
45°	2993.4	3000.9	3011.4	3026.5	3029.5	2999.4	2883.3	2869.7	2859.1	2853.1	2848.6
47.5°	3258.8	3272.3	3307.0	3371.9	3454.8	3465.4	3373.4	3337.2	3329.6	3319.1	3310.0
50°	3448.8	3468.4	3546.8	3673.5	3834.8	3934.3	3884.6	3854.4	3852.9	3824.3	3821.2
52.5°	3557.3	3578.5	3706.6	3898.1	4148.5	4343.0	4404.8	4403.3	4400.3	4374.7	4364.1
55°	3581.5	3604.1	3757.9	4018.8	4376.2	4712.5	4949.2	4955.2	4968.8	4961.3	4961.3
57.5°	3515.1	3543.8	3711.2	4033.9	4495.3	5005.0	5522.2	5556.9	5573.5	5632.3	5700.2
60°	3393.0	3414.1	3581.5	3941.9	4516.4	5271.9	6267.2	6377.3	6463.2	6579.3	6689.4
62.5°	3166.8	3209.0	3368.8	3760.9	4453.1	5579.6	7156.9	7360.5	7527.9	7704.3	7916.9
65°	2892.3	2910.4	3046.1	3388.4	4169.6	5697.2	7648.5	7847.6	8061.7	8250.2	8440.2
67.5°	2548.5	2563.6	2681.2	2827.5	3441.2	5146.8	7164.4	7384.6	7577.6	7733.0	7981.8
70°	1669.3	1702.5	1990.5	2135.3	2405.2	3804.7	5858.5	6071.2	6218.9	6324.5	6612.5
72.5°	1223.0	1244.1	1360.2	1658.8	1725.1	2248.4	4122.8	4353.6	4407.8	4606.9	4741.1
75°	746.5	799.2	1061.6	1420.5	1681.4	1539.7	2470.1	2581.7	2706.8	2851.6	2979.8
77.5°	150.8	171.9	346.8	978.7	1479.3	1645.2	1474.8	1495.9	1557.8	1571.3	1619.6
80°	24.1	25.6	45.2	422.2	856.5	1330.0	1474.8	1455.2	1420.5	1396.4	1372.3
82.5°	10.6	12.1	19.6	107.1	182.5	443.3	1275.8	1375.3	1489.9	1553.2	1569.8
85°	4.5	4.5	7.5	21.1	27.1	30.2	215.6	285.0	508.2	675.6	778.1
87.5°	3.0	3.0	4.5	4.5	6.0	7.5	10.6	10.6	12.1	13.6	19.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155284

CATALOG NUMBER: AVM-F06-LED-E-U-T3-HSS-7030

**CANDELA DISTRIBUTION (continued):**

	60°	61°	62°	64°	65°	66°	67°	68°	69°	70°	71°
0°	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1
2.5°	235.2	233.7	233.7	229.2	229.2	227.7	227.7	226.2	226.2	223.2	224.7
5°	274.5	271.4	268.4	263.9	262.4	259.4	256.4	251.8	250.3	247.3	245.8
7.5°	327.2	324.2	318.2	309.1	303.1	297.1	291.0	285.0	280.5	276.0	272.9
10°	392.1	383.0	380.0	361.9	354.4	342.3	334.8	328.7	319.7	312.2	307.6
12.5°	470.5	463.0	447.9	423.7	411.7	401.1	387.6	375.5	366.4	352.9	343.8
15°	551.9	545.9	524.8	497.6	482.6	463.0	449.4	437.3	417.7	408.7	392.1
17.5°	654.5	636.4	615.3	576.1	556.4	539.9	515.7	497.6	485.6	458.4	443.3
20°	760.0	740.4	713.3	669.5	642.4	616.8	597.2	573.0	547.4	529.3	503.7
22.5°	880.7	849.0	827.9	773.6	741.9	714.8	681.6	656.0	630.3	601.7	573.0
25°	1008.8	977.2	951.5	889.7	856.5	829.4	790.2	754.0	722.3	690.7	657.5
27.5°	1143.1	1114.4	1085.8	1022.4	993.8	956.1	919.9	877.6	836.9	808.3	763.0
30°	1298.4	1274.2	1242.6	1174.7	1143.1	1103.8	1066.1	1016.4	977.2	938.0	894.2
32.5°	1465.8	1446.2	1413.0	1352.7	1315.0	1281.8	1241.1	1192.8	1137.0	1096.3	1045.0
35°	1669.3	1636.2	1616.6	1559.3	1530.6	1494.4	1452.2	1410.0	1351.2	1293.9	1250.1
37.5°	1901.6	1886.5	1860.9	1806.6	1785.5	1747.8	1720.6	1678.4	1633.1	1560.8	1514.0
40°	2139.8	2129.3	2106.7	2052.4	2031.3	2005.6	1974.0	1933.2	1879.0	1841.3	1771.9
42.5°	2442.9	2426.4	2408.3	2357.0	2316.3	2284.6	2271.0	2236.3	2179.0	2130.8	2076.5
45°	2827.5	2819.9	2795.8	2744.5	2703.8	2682.7	2661.6	2602.8	2565.1	2516.8	2479.1
47.5°	3291.9	3267.8	3255.7	3198.4	3184.9	3168.3	3114.0	3080.8	3026.5	2988.8	2942.1
50°	3794.1	3768.5	3770.0	3700.6	3703.6	3691.6	3650.8	3611.6	3564.9	3531.7	3503.1
52.5°	4334.0	4346.0	4315.9	4337.0	4312.8	4285.7	4278.2	4229.9	4189.2	4187.7	4148.5
55°	4997.5	4977.9	4985.4	5006.5	4973.3	5003.5	4988.4	4926.6	4928.1	4940.2	4894.9
57.5°	5710.7	5739.4	5801.2	5814.8	5872.1	5832.9	5935.4	5861.5	5906.8	5906.8	5876.6
60°	6757.3	6871.9	7021.2	7137.3	7244.4	7209.7	7343.9	7259.4	7319.8	7268.5	7242.9
62.5°	8018.0	8170.3	8346.7	8535.2	8643.8	8670.9	8651.3	8689.0	8630.2	8592.5	8494.5
65°	8624.2	8775.0	8928.8	9155.0	9185.1	9207.8	9198.7	9135.4	9063.0	8955.9	8827.8
67.5°	8120.5	8331.6	8417.6	8678.5	8765.9	8734.3	8744.8	8663.4	8550.3	8444.7	8256.2
70°	6733.2	6974.4	7019.7	7393.7	7497.7	7648.5	7594.2	7570.1	7446.4	7357.5	7149.4
72.5°	4902.5	5091.0	5075.9	5496.6	5478.5	5540.3	5686.6	5680.6	5550.9	5522.2	5347.3
75°	3017.5	3130.6	3124.5	3423.1	3298.0	3279.9	3320.6	3302.5	3180.3	3053.7	2945.1
77.5°	1598.5	1649.7	1595.5	1506.5	1497.4	1396.4	1367.7	1366.2	1272.7	1158.1	1073.7
80°	1346.6	1293.9	1230.5	1100.8	1025.4	957.6	894.2	835.4	772.1	687.6	585.1
82.5°	1572.8	1547.2	1502.0	1339.1	1260.7	1125.0	1023.9	928.9	812.8	725.3	594.1
85°	766.1	764.5	800.7	784.2	755.5	749.5	649.9	628.8	582.1	533.8	446.4
87.5°	21.1	15.1	18.1	15.1	18.1	19.6	13.6	31.7	19.6	18.1	21.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P155284

CATALOG NUMBER: AVM-F06-LED-E-U-T3-HSS-7030

**CANDELA DISTRIBUTION (continued):**

	72°	73°	74°	75°	76°	77°	78°	79°	80°	81°	82°
0°	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1
2.5°	223.2	221.7	220.2	220.2	218.7	218.7	217.2	215.6	215.6	214.1	214.1
5°	242.8	239.8	238.3	236.8	233.7	232.2	229.2	227.7	224.7	223.2	220.2
7.5°	266.9	263.9	257.9	254.8	250.3	248.8	241.3	238.3	235.2	232.2	227.7
10°	297.1	289.5	283.5	277.5	269.9	263.9	257.9	253.3	247.3	239.8	236.8
12.5°	334.8	324.2	315.2	304.6	295.6	286.5	276.0	268.4	259.4	251.8	244.3
15°	377.0	361.9	349.9	334.8	319.7	309.1	298.6	288.0	276.0	265.4	256.4
17.5°	425.3	405.6	389.1	371.0	354.4	339.3	321.2	307.6	294.1	279.0	266.9
20°	476.5	456.9	434.3	414.7	390.6	374.0	351.4	333.3	313.7	298.6	282.0
22.5°	544.4	518.7	490.1	463.0	437.3	411.7	387.6	364.9	340.8	318.2	301.6
25°	624.3	592.6	556.4	529.3	493.1	464.5	434.3	405.6	380.0	351.4	324.2
27.5°	723.8	681.6	642.4	604.7	565.5	529.3	490.1	456.9	422.2	389.1	358.9
30°	839.9	799.2	740.4	698.2	659.0	609.2	570.0	526.3	487.1	438.8	405.6
32.5°	993.8	941.0	879.2	823.4	772.1	716.3	662.0	606.2	554.9	511.2	461.4
35°	1194.3	1132.5	1058.6	987.7	930.4	862.6	793.2	729.9	671.1	607.7	545.9
37.5°	1447.7	1390.4	1310.4	1224.5	1147.6	1066.1	993.8	904.8	826.4	749.5	671.1
40°	1699.5	1646.7	1563.8	1471.8	1372.3	1278.8	1186.8	1085.8	986.2	889.7	808.3
42.5°	2010.1	1931.7	1842.8	1738.7	1642.2	1530.6	1416.0	1299.9	1180.8	1064.6	948.5
45°	2400.7	2340.4	2215.2	2103.6	1989.0	1857.8	1716.1	1583.4	1431.1	1293.9	1140.0
47.5°	2875.7	2767.2	2675.2	2572.6	2429.4	2302.7	2121.7	1964.9	1774.9	1592.4	1408.5
50°	3436.7	3376.4	3254.2	3126.1	2970.7	2819.9	2643.5	2417.3	2189.6	1995.1	1743.2
52.5°	4092.7	4006.7	3929.8	3797.1	3638.8	3445.8	3245.2	2999.4	2720.4	2446.0	2177.5
55°	4870.8	4810.5	4736.6	4631.0	4429.0	4210.3	3969.0	3675.0	3344.7	2975.3	2663.1
57.5°	5875.1	5811.8	5740.9	5523.8	5386.5	5118.1	4768.3	4463.6	4107.8	3634.2	3246.7
60°	7245.9	7159.9	7060.4	6884.0	6597.4	6249.1	5873.6	5422.7	4986.9	4469.7	3961.5
62.5°	8417.6	8280.4	8067.7	7840.0	7496.2	7096.6	6624.6	6093.8	5597.6	5015.6	4450.1
65°	8658.9	8470.4	8220.0	7923.0	7568.6	7117.7	6624.6	6116.4	5532.8	4985.4	4416.9
67.5°	8031.5	7812.9	7556.5	7224.8	6887.0	6422.5	5997.3	5480.0	4931.1	4457.6	3949.4
70°	7000.1	6675.9	6413.5	6060.6	5718.3	5353.4	4905.5	4517.9	4071.6	3635.8	3246.7
72.5°	5256.8	4937.1	4698.9	4416.9	4213.3	3827.3	3498.5	3209.0	2945.1	2619.4	2331.3
75°	2833.5	2593.7	2433.9	2305.7	2123.2	1868.4	1711.6	1512.5	1400.9	1265.2	1134.0
77.5°	924.4	814.3	695.2	579.1	497.6	374.0	361.9	288.0	271.4	263.9	203.6
80°	473.5	364.9	263.9	190.0	144.8	128.2	122.1	116.1	110.1	105.6	98.0
82.5°	475.0	343.8	236.8	164.4	119.1	99.5	93.5	90.5	86.0	81.4	75.4
85°	346.8	256.4	176.4	120.6	82.9	66.4	63.3	58.8	55.8	54.3	48.3
87.5°	22.6	16.6	15.1	13.6	13.6	13.6	15.1	13.6	15.1	15.1	13.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155284

CATALOG NUMBER: AVM-F06-LED-E-U-T3-HSS-7030

**CANDELA DISTRIBUTION (continued):**

	83°	84°	85°	86°	87°	88°	89°	90°	95°	105°	115°
0°	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1	205.1
2.5°	212.6	211.1	211.1	209.6	208.1	208.1	206.6	206.6	202.1	194.5	188.5
5°	218.7	215.6	214.1	212.6	211.1	208.1	206.6	205.1	197.5	182.5	170.4
7.5°	223.2	220.2	218.7	215.6	211.1	209.6	206.6	203.6	191.5	170.4	156.8
10°	230.7	226.2	221.7	217.2	212.6	209.6	205.1	202.1	184.0	159.8	146.3
12.5°	238.3	232.2	226.2	218.7	214.1	209.6	205.1	199.1	177.9	150.8	135.7
15°	247.3	238.3	230.7	223.2	215.6	209.6	202.1	197.5	171.9	143.3	129.7
17.5°	256.4	245.8	235.2	224.7	217.2	208.1	202.1	194.5	165.9	137.2	122.1
20°	266.9	251.8	241.3	229.2	218.7	208.1	199.1	191.5	159.8	129.7	114.6
22.5°	282.0	263.9	247.3	233.7	220.2	209.6	199.1	188.5	153.8	123.7	108.6
25°	301.6	279.0	259.4	242.8	226.2	212.6	200.6	190.0	149.3	119.1	101.0
27.5°	330.2	301.6	280.5	257.9	236.8	220.2	205.1	193.0	146.3	114.6	96.5
30°	364.9	336.3	303.1	276.0	253.3	230.7	214.1	196.0	143.3	110.1	90.5
32.5°	416.2	375.5	336.3	303.1	271.4	245.8	221.7	203.6	141.8	102.5	84.4
35°	490.1	434.3	387.6	343.8	300.1	268.4	239.8	215.6	140.2	96.5	78.4
37.5°	595.7	529.3	469.0	407.2	352.9	307.6	268.4	236.8	140.2	92.0	72.4
40°	708.8	622.8	545.9	469.0	399.6	342.3	289.5	250.3	137.2	86.0	66.4
42.5°	836.9	731.4	625.8	530.8	444.9	371.0	309.1	260.9	129.7	79.9	60.3
45°	1008.8	870.1	743.4	621.3	509.7	413.2	334.8	272.9	122.1	75.4	54.3
47.5°	1224.5	1063.1	898.8	744.9	598.7	476.5	372.5	292.5	117.6	69.4	49.8
50°	1545.7	1316.5	1099.3	903.3	717.8	558.0	428.3	321.2	113.1	64.8	45.2
52.5°	1898.6	1616.6	1361.7	1109.9	879.2	668.0	493.1	358.9	108.6	60.3	40.7
55°	2328.3	1981.5	1670.8	1343.6	1048.1	796.2	573.0	401.1	102.5	55.8	37.7
57.5°	2859.1	2420.3	2052.4	1652.8	1281.8	962.1	680.1	472.0	96.5	49.8	33.2
60°	3451.8	2955.7	2492.7	2023.7	1574.3	1182.3	838.4	573.0	90.5	43.7	28.7
62.5°	3878.5	3334.2	2804.9	2278.6	1785.5	1346.6	966.6	651.5	81.4	37.7	25.6
65°	3874.0	3322.1	2789.8	2271.0	1791.5	1352.7	971.1	666.5	72.4	33.2	22.6
67.5°	3451.8	2987.3	2512.3	2046.3	1627.1	1230.5	898.8	618.3	61.8	30.2	19.6
70°	2839.5	2470.1	2094.6	1725.1	1388.9	1054.1	776.6	538.4	52.8	27.1	16.6
72.5°	2073.5	1803.6	1574.3	1313.5	1084.2	832.4	619.8	422.2	42.2	22.6	15.1
75°	1030.0	921.4	790.2	708.8	604.7	494.6	384.5	245.8	34.7	18.1	13.6
77.5°	196.0	174.9	167.4	144.8	132.7	117.6	104.1	73.9	27.1	13.6	12.1
80°	90.5	82.9	75.4	67.9	60.3	51.3	45.2	39.2	21.1	10.6	13.6
82.5°	70.9	64.8	57.3	51.3	45.2	39.2	33.2	28.7	13.6	9.0	13.6
85°	46.7	40.7	36.2	31.7	27.1	24.1	21.1	18.1	9.0	9.0	9.0
87.5°	13.6	13.6	12.1	12.1	10.6	10.6	9.0	9.0	7.5	7.5	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155284

CATALOG NUMBER: AVM-F06-LED-E-U-T3-HSS-7030

**CANDELA DISTRIBUTION (continued):**

	125°	135°	145°	155°	165°	175°	180°
0°	205.1	205.1	205.1	205.1	205.1	205.1	205.1
2.5°	182.5	174.9	171.9	170.4	170.4	171.9	170.4
5°	161.4	153.8	150.8	147.8	147.8	147.8	149.3
7.5°	147.8	140.2	135.7	134.2	132.7	134.2	134.2
10°	135.7	129.7	123.7	120.6	120.6	120.6	120.6
12.5°	126.7	119.1	113.1	111.6	110.1	110.1	110.1
15°	119.1	110.1	105.6	102.5	101.0	101.0	102.5
17.5°	110.1	102.5	96.5	95.0	95.0	95.0	95.0
20°	104.1	95.0	90.5	87.5	87.5	87.5	87.5
22.5°	96.5	89.0	82.9	79.9	79.9	79.9	79.9
25°	90.5	82.9	76.9	73.9	73.9	73.9	73.9
27.5°	84.4	76.9	70.9	67.9	67.9	67.9	67.9
30°	78.4	70.9	64.8	61.8	61.8	61.8	61.8
32.5°	73.9	64.8	58.8	55.8	55.8	57.3	55.8
35°	66.4	58.8	52.8	49.8	49.8	49.8	49.8
37.5°	60.3	52.8	46.7	43.7	43.7	43.7	42.2
40°	55.8	46.7	40.7	37.7	36.2	36.2	36.2
42.5°	48.3	39.2	34.7	31.7	30.2	30.2	30.2
45°	43.7	34.7	28.7	25.6	25.6	25.6	25.6
47.5°	39.2	30.2	24.1	21.1	21.1	22.6	22.6
50°	34.7	25.6	19.6	19.6	19.6	21.1	21.1
52.5°	30.2	22.6	18.1	18.1	19.6	21.1	21.1
55°	27.1	19.6	16.6	18.1	19.6	21.1	21.1
57.5°	24.1	16.6	16.6	18.1	19.6	21.1	21.1
60°	21.1	15.1	15.1	16.6	19.6	21.1	21.1
62.5°	18.1	15.1	15.1	16.6	19.6	21.1	21.1
65°	16.6	15.1	15.1	16.6	19.6	21.1	21.1
67.5°	15.1	13.6	15.1	16.6	18.1	19.6	19.6
70°	13.6	13.6	15.1	16.6	18.1	19.6	19.6
72.5°	13.6	13.6	13.6	15.1	16.6	18.1	18.1
75°	13.6	13.6	13.6	15.1	16.6	18.1	18.1
77.5°	13.6	12.1	12.1	13.6	16.6	18.1	18.1
80°	13.6	12.1	12.1	13.6	15.1	18.1	18.1
82.5°	10.6	10.6	12.1	13.6	15.1	16.6	16.6
85°	9.0	10.6	10.6	12.1	13.6	16.6	16.6
87.5°	7.5	7.5	9.0	10.6	12.1	13.6	13.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)