

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701813

Luminaire Tested: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-FF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P701813
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-2)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-FF
Description: FARALLON 4" LED GLASS DOWNLIGHT. FLARED FROSTED GLASS KIT.
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 520.9 lumens
Efficiency: N/A
Efficacy: 52.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.73
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P701813

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-FF

Luminous Intensity Polar Plot



TEST NUMBER: P701813

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-FF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	110	110	110		104	104	104		100	100	100	97
1	109	105	102	98	107	103	99	96	98	95	93		94	92	90		90	88	86	84
2	102	95	89	85	99	93	88	83	89	85	81		86	82	79		82	80	77	75
3	95	87	80	75	93	85	79	74	82	77	72		79	75	71		76	73	69	67
4	89	80	73	67	87	78	72	67	76	70	65		73	68	64		71	67	63	61
5	84	74	66	61	82	73	66	61	70	64	60		68	63	59		66	62	58	56
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		62	58	54	52
7	75	64	57	52	73	63	56	52	62	56	51		60	55	51		59	54	50	49
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		55	51	47	45
9	68	57	50	45	66	56	50	45	55	49	45		54	48	44		53	48	44	43
10	64	53	47	43	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57377
5°	49621
10°	42592
15°	36512
20°	31057
25°	20864
30°	7954
35°	5874
40°	4571
45°	3618
50°	2847
55°	2315
60°	1960
65°	1780
70°	1604
75°	1478
80°	1357
85°	1194

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3618 cd/sqm

TEST NUMBER: P701813

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-FF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.1	8.8
10°-20°	124.1	23.8
20°-30°	122.8	23.6
30°-40°	57.6	11.1
40°-50°	46.0	8.8
50°-60°	35.5	6.8
60°-70°	29.8	5.7
70°-80°	25.6	4.9
80°-90°	20.0	3.8
90°-100°	11.5	2.2
100°-110°	2.1	0.4
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.0	56.2
0°-40°	350.5	67.3
0°-60°	432.0	82.9
0°-90°	507.3	97.4
90°-120°	13.6	2.6
90°-150°	13.6	2.6
90°-180°	14.0	2.7
0°-180°	520.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	495	
5°	490	46
15°	442	124
25°	292	123
35°	91	58
45°	60	46
55°	39	35
65°	30	30
75°	24	26
85°	18	16
90°	15	8
95°	11	8
105°	1	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P701813

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-FF

CANDELA DISTRIBUTION (FULL):

0°	
0°	494.7
2.5°	493.4
5°	489.5
7.5°	481.6
10°	469.9
12.5°	456.8
15°	442.4
17.5°	426.1
20°	407.1
22.5°	378.4
25°	292.1
27.5°	168.0
30°	117.6
32.5°	101.3
35°	90.8
37.5°	82.3
40°	73.2
42.5°	66.0
45°	59.5
47.5°	52.9
50°	47.7
52.5°	43.1
55°	39.2
57.5°	35.9
60°	33.3
62.5°	31.4
65°	30.1
67.5°	28.8
70°	26.8
72.5°	25.5
75°	24.2
77.5°	22.9
80°	21.6
82.5°	19.6
85°	18.3
87.5°	17.0
90°	15.0
92.5°	13.7
95°	11.1
97.5°	7.2
100°	5.2
102.5°	3.3
105°	1.3
107.5°	0.7
110°	0.0

TEST NUMBER: P701813

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9027-4LBW1LI-FF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)