

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P701853

Luminaire Tested: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P701853  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF  
Description: FARALLON 4" LED GLASS DOWNLIGHT. CYLINDRICAL FROSTED GLASS KIT.  
Light Source: 3000K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 581.7 lumens  
Efficiency: N/A  
Efficacy: 58.8 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.45  
Luminous Opening: Vertical Cylinder (Dia: 0.34' x H: 0.46')  
CIE Type: Direct  
  
Input Watts (W): 9.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P701853

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

### Luminous Intensity Polar Plot



TEST NUMBER: P701853

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	98	106	103	99	96	98	95	92		94	91	89		90	88	86	84
2	101	94	88	83	98	92	86	82	88	83	80		85	81	77		81	78	75	73
3	94	85	78	72	91	83	76	71	80	74	70		77	72	68		74	70	67	65
4	87	77	70	64	85	76	69	63	73	67	62		71	65	61		68	64	60	58
5	82	71	63	57	80	70	62	57	67	61	56		65	60	55		63	59	55	53
6	77	65	58	52	75	64	57	52	62	56	51		61	55	51		59	54	50	48
7	72	61	53	48	71	60	53	48	58	52	47		57	51	47		55	50	46	45
8	69	57	49	44	67	56	49	44	55	48	44		53	48	43		52	47	43	41
9	65	53	46	41	64	53	46	41	52	45	41		50	45	41		49	44	40	39
10	62	50	43	39	61	50	43	39	49	43	39		48	42	38		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	130330
5°	86013
10°	47849
15°	35439
20°	17104
25°	11643
30°	9050
35°	8086
40°	7256
45°	6281
50°	5193
55°	4210
60°	3397
65°	2691
70°	2113
75°	1704
80°	1364
85°	1109

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6281 cd/sqm

TEST NUMBER: P701853

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.4	11.9
10°-20°	109.5	18.8
20°-30°	76.1	13.1
30°-40°	78.0	13.4
40°-50°	79.1	13.6
50°-60°	64.1	11.0
60°-70°	45.3	7.8
70°-80°	29.6	5.1
80°-90°	18.6	3.2
90°-100°	10.0	1.7
100°-110°	1.9	0.3
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.1	43.8
0°-40°	333.1	57.3
0°-60°	476.3	81.9
0°-90°	569.8	97.9
90°-120°	11.9	2.1
90°-150°	11.9	2.1
90°-180°	12.0	2.1
0°-180°	581.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1124	
5°	848	69
15°	429	110
25°	163	76
35°	125	78
45°	103	79
55°	71	64
65°	46	45
75°	28	30
85°	17	15
90°	13	7
95°	10	7
105°	1	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P701853

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1123.7
1°	1119.6
2°	1091.7
3°	1027.9
4°	941.6
5°	848.5
6°	754.8
7°	670.5
8°	610.1
9°	562.5
10°	527.9
11°	502.7
12°	482.3
13°	465.4
14°	449.1
15°	429.4
16°	398.1
17°	355.3
18°	306.4
19°	259.5
20°	224.2
21°	202.5
22°	188.2
23°	179.4
24°	171.2
25°	163.0
27.5°	145.4
30°	133.8
32.5°	127.0
35°	125.0
37.5°	120.9
40°	116.2
42.5°	110.1
45°	103.3
47.5°	95.1
50°	87.0
52.5°	78.8
55°	71.3
57.5°	64.5
60°	57.7
62.5°	51.0
65°	45.5
67.5°	40.1
70°	35.3
72.5°	31.3

TEST NUMBER: P701853

CATALOG NUMBER: 340-4C-08-D010 / 340-EU4C-1020-9730-4LBW1LI-CF

**CANDELA DISTRIBUTION (continued):**

	0°
75°	27.9
77.5°	24.5
80°	21.7
82.5°	19.0
85°	17.0
87.5°	14.9
90°	12.9
92.5°	11.5
95°	9.5
97.5°	6.8
100°	4.8
102.5°	2.7
105°	1.4
107.5°	0.7
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)