

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702407

Luminaire Tested: 340-6C-10-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702407
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-13)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-10-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ
Description: FARALLON 6" LED GLASS DOWNLIGHT CYLINDRICAL FROSTED, QUADRATE ETCHED GLASS KIT.
Light Source: 2700K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 676.5 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.54
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702407

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ

Luminous Intensity Polar Plot



TEST NUMBER: P702407

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	110	105	102	98	107	103	100	97	98	96	93		94	92	90		90	89	87	85
2	102	95	89	84	99	93	87	83	89	84	81		85	82	78		82	79	76	74
3	95	86	79	73	92	84	78	72	81	75	71		78	73	70		75	71	68	66
4	88	78	71	65	86	77	70	64	74	68	63		72	67	62		69	65	61	59
5	83	72	64	58	81	71	63	58	68	62	57		66	61	57		64	60	56	54
6	78	66	59	53	76	65	58	53	63	57	52		62	56	52		60	55	51	49
7	73	62	54	49	71	61	54	49	59	53	48		58	52	48		56	51	47	46
8	69	58	50	45	68	57	50	45	55	49	45		54	48	44		53	48	44	42
9	66	54	47	42	64	53	47	42	52	46	42		51	45	41		50	45	41	40
10	62	51	44	40	61	50	44	39	49	43	39		48	43	39		47	42	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67504
5°	48489
10°	30767
15°	24632
20°	16946
25°	9396
30°	7368
35°	6184
40°	5433
45°	4508
50°	3702
55°	2930
60°	2333
65°	1837
70°	1462
75°	1178
80°	953
85°	787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4508 cd/sqm

TEST NUMBER: P702407

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.8	10.5
10°-20°	135.9	20.1
20°-30°	105.5	15.6
30°-40°	95.9	14.2
40°-50°	89.0	13.2
50°-60°	68.5	10.1
60°-70°	46.9	6.9
70°-80°	30.4	4.5
80°-90°	18.9	2.8
90°-100°	11.0	1.6
100°-110°	3.5	0.5
110°-120°	0.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	312.2	46.1
0°-40°	408.1	60.3
0°-60°	565.7	83.6
0°-90°	661.9	97.8
90°-120°	14.6	2.2
90°-150°	14.6	2.2
90°-180°	15.0	2.2
0°-180°	676.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1035	
5°	828	71
15°	498	136
25°	213	105
35°	152	96
45°	115	89
55°	76	69
65°	47	47
75°	28	30
85°	17	15
90°	13	7
95°	10	8
105°	3	3
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P702407

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ

CANDELA DISTRIBUTION (FULL):

0°	
0°	1034.7
2.5°	988.9
5°	828.5
7.5°	673.7
10°	575.8
12.5°	527.6
15°	497.6
17.5°	458.9
20°	364.9
22.5°	255.1
25°	213.3
27.5°	192.7
30°	174.6
32.5°	160.3
35°	151.6
37.5°	146.1
40°	136.6
42.5°	125.6
45°	115.3
47.5°	105.0
50°	95.6
52.5°	85.3
55°	75.8
57.5°	67.9
60°	60.0
62.5°	52.9
65°	46.6
67.5°	41.9
70°	36.3
72.5°	32.4
75°	28.4
77.5°	25.3
80°	22.1
82.5°	19.7
85°	17.4
87.5°	15.0
90°	12.6
92.5°	11.8
95°	10.3
97.5°	8.7
100°	6.3
102.5°	4.7
105°	3.2
107.5°	1.6
110°	0.8

TEST NUMBER: P702407

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9727-4LBW1LI-CQ

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)