

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P147536

Luminaire Tested: **AVM-F04-LED-E-U-5MQ-7050**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P147536  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33674)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: AVM-F04-LED-E-U-5MQ-7050  
Description: VISION SITE MEDIUM LED LUMINAIRE  
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE MEDIUM  
Light Source: (28) 5000K CCT, 70 CRI LEDs  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10923.1 lumens  
Efficiency: N/A  
Efficacy: 106.9 lumens/watt  
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')  
IES Classification: Type V - Short - Full Cutoff  
BUG Rating: B3 - U0 - G2


Input Watts (W): 102.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P147536  
 CATALOG NUMBER: AVM-F04-LED-E-U-5MQ-7050

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 2.1 fc  
 Type V - Short - Full Cutoff

REPORT NUMBER: P147536  
CATALOG NUMBER: AVM-F04-LED-E-U-5MQ-7050

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral    - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P147536

CATALOG NUMBER: AVM-F04-LED-E-U-5MQ-7050

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	5461.5	0.0	5461.5
	% Fixture	50.0	0.0	50.0
<b>Street Side</b>	Lumens	5461.5	0.0	5461.5
	% Fixture	50.0	0.0	50.0
<b>Total</b>	Lumens	10923.1	0.0	10923.1
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.7	0.7
10°-20°	245.6	2.2
20°-30°	474.9	4.3
30°-40°	919.6	8.4
40°-50°	1660.3	15.2
50°-60°	2887.1	26.4
60°-70°	3277.6	30.0
70°-80°	1270.7	11.6
80°-90°	114.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10923.1	100.0
0°-180°	10923.1	100.0



REPORT NUMBER: P147536


CATALOG NUMBER: AVM-F04-LED-E-U-5MQ-7050

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	396.6	3.6			
FM	(30°-60°)	2733.5	25.0			
FH	(60°-80°)	2274.1	20.8			G2/5000
FVH	(80°-90°)	57.3	0.5			G1/100
BL	(0°-30°)	396.6	3.6	B1/500		
BM	(30°-60°)	2733.5	25.0	B3/5000		
BH	(60°-80°)	2274.1	20.8	B3/2500		G2/5000
BVH	(80°-90°)	57.3	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G2**

Type V Short





REPORT NUMBER: P147536

CATALOG NUMBER: AVM-F04-LED-E-U-5MQ-7050

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	725.1	725.1	725.1	725.1	725.1	725.1	725.1	725.1	725.1	725.1	725.1
2.5°	729.6	731.9	731.3	730.2	730.2	730.2	729.6	728.0	727.3	728.4	729.6
5°	746.6	746.6	746.6	746.6	745.4	745.4	744.3	743.2	743.7	742.6	742.0
7.5°	772.6	770.8	770.8	770.3	770.3	769.1	767.4	765.2	765.8	765.2	764.7
10°	803.1	803.6	801.9	803.6	800.8	800.2	798.0	796.8	796.2	794.6	794.6
12.5°	839.8	838.0	838.0	837.0	835.8	834.6	831.2	830.7	828.4	827.4	825.6
15°	874.2	873.6	871.4	869.1	868.5	867.4	863.5	861.2	860.6	857.8	855.6
17.5°	908.6	907.5	904.7	903.6	901.3	899.6	896.2	892.8	891.1	890.0	887.2
20°	945.4	944.2	941.4	939.1	936.3	934.0	929.0	926.1	924.4	922.8	920.5
22.5°	991.1	988.8	984.3	980.4	974.1	971.9	965.1	961.2	958.4	956.1	954.9
25°	1040.8	1041.3	1035.1	1030.0	1022.8	1016.5	1008.0	1003.5	1000.7	998.4	997.8
27.5°	1102.9	1103.4	1097.8	1090.4	1079.2	1072.4	1061.1	1055.4	1053.8	1051.5	1050.9
30°	1201.2	1196.0	1186.5	1174.6	1164.4	1149.8	1133.4	1127.8	1122.1	1120.4	1120.4
32.5°	1381.9	1379.0	1371.2	1341.8	1328.2	1297.8	1268.9	1252.6	1234.0	1224.9	1219.2
35°	1508.4	1507.2	1501.0	1490.8	1482.4	1476.2	1459.2	1456.4	1453.0	1453.0	1457.6
37.5°	1601.5	1594.8	1593.6	1595.3	1593.1	1594.2	1607.8	1626.4	1642.2	1650.1	1649.0
40°	1739.4	1729.8	1735.4	1731.4	1726.4	1725.2	1729.8	1737.1	1744.4	1744.4	1742.7
42.5°	1919.4	1924.0	1926.2	1909.9	1899.2	1896.3	1907.0	1904.8	1912.2	1909.3	1902.0
45°	2187.2	2184.3	2180.4	2160.6	2143.7	2130.2	2132.9	2129.0	2129.6	2125.0	2119.4
47.5°	2457.0	2466.6	2450.3	2440.7	2421.5	2411.9	2419.8	2413.0	2426.0	2402.3	2391.0
50°	2719.1	2725.8	2720.2	2706.7	2706.7	2720.2	2729.8	2742.2	2760.3	2733.2	2692.6
52.5°	2933.7	2939.4	2947.8	2959.1	2986.8	3015.6	3056.2	3099.8	3134.2	3129.1	3082.8
55°	3064.7	3071.5	3085.6	3124.6	3174.3	3250.0	3342.0	3443.0	3522.2	3560.5	3526.6
57.5°	3108.8	3113.8	3152.2	3199.1	3276.5	3388.8	3543.0	3717.6	3869.4	3966.0	3950.8
60°	3098.6	3098.6	3137.6	3202.0	3310.4	3459.4	3677.4	3919.2	4151.8	4296.4	4274.9
62.5°	2991.9	2997.6	3053.4	3130.8	3261.8	3440.3	3700.0	4008.9	4287.3	4466.9	4449.4
65°	2758.1	2762.0	2822.4	2914.5	3060.8	3272.0	3556.0	3898.2	4217.3	4390.1	4357.4
67.5°	2380.3	2384.2	2433.4	2537.3	2692.0	2912.8	3219.4	3596.2	3908.4	4045.0	3946.8
70°	1893.5	1904.8	1936.5	2046.5	2164.0	2380.3	2662.6	3039.4	3334.0	3463.4	3355.0
72.5°	1290.4	1319.2	1357.6	1455.2	1567.6	1747.2	1972.0	2289.4	2526.0	2675.6	2579.0
75°	726.8	767.4	779.3	853.3	945.9	1087.6	1252.0	1479.6	1718.4	1839.8	1723.5
77.5°	314.0	347.3	362.0	396.5	468.7	528.0	628.0	781.6	966.2	1051.5	912.0
80°	154.7	162.6	168.8	179.6	199.9	219.1	266.6	333.8	409.4	428.6	341.0
82.5°	119.7	125.4	136.1	144.6	149.6	154.7	159.2	168.3	175.6	179.6	169.4
85°	84.2	91.4	103.4	113.0	118.6	122.6	126.5	129.4	122.6	111.8	117.5
87.5°	22.0	28.8	40.1	43.4	49.1	52.0	50.8	52.6	47.4	34.4	38.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147536

CATALOG NUMBER: AVM-F04-LED-E-U-5MQ-7050

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	725.1	725.1	725.1	725.1	725.1	725.1	725.1	725.1
2.5°	729.0	728.5	729.0	729.0	729.0	728.5	728.4	728.5
5°	742.1	742.0	742.6	741.5	741.4	742.0	741.4	740.9
7.5°	764.1	763.5	763.5	763.0	763.5	763.0	763.0	762.4
10°	793.4	792.3	792.8	791.2	791.2	790.6	790.6	790.6
12.5°	825.0	823.4	824.0	822.2	819.4	820.0	820.6	820.0
15°	855.6	853.8	852.2	851.0	849.3	849.9	849.9	849.3
17.5°	886.6	883.2	882.6	881.0	880.4	880.4	880.4	881.0
20°	918.8	916.6	916.0	914.2	913.7	915.4	916.0	914.8
22.5°	953.2	952.1	953.2	952.2	953.8	954.9	955.5	954.4
25°	996.8	995.6	997.3	1001.2	1003.5	1004.6	1007.4	1006.3
27.5°	1052.6	1051.5	1055.4	1061.1	1064.5	1070.2	1073.0	1074.1
30°	1124.9	1130.0	1132.2	1143.6	1145.8	1154.8	1154.8	1158.8
32.5°	1230.0	1239.6	1256.4	1274.0	1298.3	1315.8	1315.8	1324.8
35°	1460.4	1464.3	1477.3	1480.1	1485.2	1490.8	1485.2	1489.7
37.5°	1637.1	1619.6	1607.2	1589.7	1579.0	1579.0	1580.1	1578.9
40°	1727.4	1720.7	1715.0	1700.4	1698.1	1697.6	1697.6	1699.8
42.5°	1889.0	1872.6	1863.6	1851.2	1847.2	1846.1	1845.5	1846.6
45°	2099.0	2072.5	2048.2	2035.8	2025.0	2014.9	2018.3	2018.3
47.5°	2343.6	2302.4	2262.8	2241.4	2222.7	2214.2	2208.6	2206.9
50°	2641.2	2583.6	2532.8	2492.6	2465.6	2465.0	2467.8	2449.7
52.5°	3006.0	2915.0	2851.8	2797.6	2772.2	2769.4	2760.4	2750.2
55°	3410.3	3302.4	3198.0	3139.8	3106.5	3088.4	3077.7	3060.8
57.5°	3827.0	3682.0	3531.8	3438.6	3379.8	3339.2	3317.7	3308.1
60°	4148.4	3950.2	3752.0	3602.4	3504.6	3444.2	3407.0	3391.7
62.5°	4274.9	4006.1	3752.0	3555.4	3414.3	3330.7	3280.4	3258.4
65°	4124.1	3805.6	3516.5	3299.6	3142.1	3048.9	2994.1	2970.4
67.5°	3702.8	3421.6	3107.0	2891.4	2729.2	2637.2	2578.0	2560.4
70°	3104.2	2816.9	2516.4	2323.8	2179.2	2104.2	2042.6	2035.2
72.5°	2332.8	2084.9	1827.4	1668.2	1551.8	1427.6	1396.0	1411.8
75°	1495.4	1263.2	1034.0	890.6	784.4	665.8	620.0	631.4
77.5°	708.2	548.3	395.9	306.1	257.0	219.7	210.1	204.4
80°	262.6	212.9	188.0	178.4	171.6	165.4	161.0	155.9
82.5°	170.0	166.0	161.0	159.2	154.2	146.2	131.6	125.4
85°	127.0	127.0	120.2	120.8	116.9	106.8	93.2	85.8
87.5°	37.2	33.3	30.5	28.2	27.7	24.8	18.1	15.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)