

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702377

Luminaire Tested: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702377  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CC  
Description: FARALLON 6" LED GLASS DOWNLIGHT. CYLINDRICAL CLEAR GLASS KIT.  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 753.7 lumens  
Efficiency: N/A  
Efficacy: 76.9 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.71  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702377

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CC

### Luminous Intensity Polar Plot



TEST NUMBER: P702377

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86	83	80	79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76	72	69	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	61		68	63	60	59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56	55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53	52
10	70	60	54	50	69	60	54	50	59	54	50		58	53	50		58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	85615
5°	69904
10°	51229
15°	44233
20°	37880
25°	35021
30°	28227
35°	18326
40°	13856
45°	7732
50°	4506
55°	2991
60°	2036
65°	1266
70°	1106
75°	832
80°	601
85°	599

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7732 cd/sqm

TEST NUMBER: P702377

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.3	12.2
10°-20°	183.3	24.3
20°-30°	216.7	28.7
30°-40°	151.6	20.1
40°-50°	70.7	9.4
50°-60°	24.5	3.3
60°-70°	9.3	1.2
70°-80°	3.8	0.5
80°-90°	0.9	0.1
90°-100°	0.5	0.1
100°-110°	0.3	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	492.2	65.3
0°-40°	643.8	85.4
0°-60°	739.1	98.1
0°-90°	753.1	99.9
90°-120°	0.9	0.1
90°-150°	0.9	0.1
90°-180°	1.0	0.1
0°-180°	753.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1312	
5°	1067	92
15°	655	183
25°	486	217
35°	230	152
45°	84	71
55°	26	25
65°	8	9
75°	3	4
85°	1	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702377

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1312.3
2.5°	1247.4
5°	1067.4
7.5°	889.9
10°	773.3
12.5°	704.2
15°	654.9
17.5°	610.6
20°	545.6
22.5°	497.2
25°	486.5
27.5°	445.4
30°	374.7
32.5°	295.0
35°	230.1
37.5°	188.2
40°	162.7
42.5°	126.5
45°	83.8
47.5°	58.3
50°	44.4
52.5°	33.7
55°	26.3
57.5°	20.5
60°	15.6
62.5°	11.5
65°	8.2
67.5°	7.4
70°	5.8
72.5°	4.9
75°	3.3
77.5°	2.5
80°	1.6
82.5°	0.8
85°	0.8
87.5°	0.8
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.8
100°	0.8
102.5°	0.8
105°	0.0
107.5°	0.0
110°	0.0

TEST NUMBER: P702377

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CC

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)