

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702379

Luminaire Tested: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CQ

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702379  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CQ  
Description: FARALLON 6" LED GLASS DOWNLIGHT CYLINDRICAL FROSTED, QUADRATE ETCHED GLASS KIT.  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 703.9 lumens  
Efficiency: N/A  
Efficacy: 71.8 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.54  
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')  
CIE Type: Direct  
  
Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702379

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CQ

### Luminous Intensity Polar Plot



TEST NUMBER: P702379

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CQ

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	110	105	102	98	107	103	100	97	98	96	93		94	92	90		90	89	87	85
2	102	95	89	84	99	93	87	83	89	84	81		85	82	78		82	79	76	74
3	95	86	79	73	92	84	78	72	81	75	71		78	73	70		75	71	68	66
4	88	78	71	65	86	77	70	64	74	68	63		72	67	62		69	65	61	59
5	83	72	64	58	81	71	63	58	68	62	57		66	61	57		64	60	56	54
6	78	66	59	53	76	65	58	53	63	57	52		62	56	52		60	55	51	49
7	73	62	54	49	71	61	54	49	59	53	48		58	52	48		56	51	47	46
8	69	58	50	45	68	57	50	45	55	49	45		54	48	44		53	48	44	42
9	66	54	47	42	64	53	47	42	52	46	42		51	45	41		50	45	41	40
10	62	51	44	40	61	50	44	39	49	43	39		48	43	39		47	42	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	70232
5°	50449
10°	32006
15°	25627
20°	17628
25°	9774
30°	7663
35°	6437
40°	5656
45°	4691
50°	3849
55°	3050
60°	2430
65°	1912
70°	1522
75°	1228
80°	992
85°	819

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4691 cd/sqm

TEST NUMBER: P702379

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CQ

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.7	10.5
10°-20°	141.4	20.1
20°-30°	109.7	15.6
30°-40°	99.8	14.2
40°-50°	92.6	13.2
50°-60°	71.3	10.1
60°-70°	48.8	6.9
70°-80°	31.7	4.5
80°-90°	19.7	2.8
90°-100°	11.4	1.6
100°-110°	3.6	0.5
110°-120°	0.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.8	46.1
0°-40°	424.6	60.3
0°-60°	588.6	83.6
0°-90°	688.7	97.9
90°-120°	15.1	2.1
90°-150°	15.1	2.1
90°-180°	15.0	2.1
0°-180°	703.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1076	
5°	862	74
15°	518	141
25°	222	110
35°	158	100
45°	120	93
55°	79	71
65°	48	49
75°	30	32
85°	18	16
90°	13	7
95°	11	8
105°	3	4
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702379

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CQ

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1076.5
2.5°	1028.8
5°	862.0
7.5°	700.9
10°	599.0
12.5°	548.9
15°	517.7
17.5°	477.4
20°	379.6
22.5°	265.4
25°	221.9
27.5°	200.5
30°	181.6
32.5°	166.8
35°	157.8
37.5°	152.0
40°	142.2
42.5°	130.7
45°	120.0
47.5°	109.3
50°	99.4
52.5°	88.7
55°	78.9
57.5°	70.7
60°	62.5
62.5°	55.1
65°	48.5
67.5°	43.6
70°	37.8
72.5°	33.7
75°	29.6
77.5°	26.3
80°	23.0
82.5°	20.5
85°	18.1
87.5°	15.6
90°	13.1
92.5°	12.3
95°	10.7
97.5°	9.0
100°	6.6
102.5°	4.9
105°	3.3
107.5°	1.6
110°	0.8

TEST NUMBER: P702379

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-CQ

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)