

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P155278

Luminaire Tested: **AVM-E06-LED-E-U-T3-HSS-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P155278
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33724)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVM-E06-LED-E-U-T3-HSS-8030
Description: VISION SITE MEDIUM LED LUMINAIRE
(6) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 AREA W/ HOUSE SIDE SHIELD
Light Source: (126) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8255.8 lumens
Efficiency: N/A
Efficacy: 54.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type III - Short - Non-Cutoff
BUG Rating: B0 - U0 - G2


Input Watts (W): 150.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P155278
 CATALOG NUMBER: AVM-E06-LED-E-U-T3-HSS-8030

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 12 fc
 Type III - Short - Non-Cutoff

REPORT NUMBER: P155278
CATALOG NUMBER: AVM-E06-LED-E-U-T3-HSS-8030

Luminous Intensity Polar Plot



— Vertical Plane Through 66-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P155278

CATALOG NUMBER: AVM-E06-LED-E-U-T3-HSS-8030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	165.8	0.0	165.8
	% Fixture	2.0	0.0	2.0
Street Side	Lumens	8090.1	0.0	8090.1
	% Fixture	98.0	0.0	98.0
Total	Lumens	8255.8	0.0	8255.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.1	0.3
10°-20°	134.2	1.6
20°-30°	306.7	3.7
30°-40°	583.4	7.1
40°-50°	1171.0	14.2
50°-60°	2072.0	25.1
60°-70°	2707.2	32.8
70°-80°	1113.1	13.5
80°-90°	140.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8255.8	100.0
0°-180°	8255.8	100.0

Coefficient of Utilization



REPORT NUMBER: P155278


CATALOG NUMBER: AVM-E06-LED-E-U-T3-HSS-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	417.2	5.1			
FM	(30°-60°)	3755.4	45.5			
FH	(60°-80°)	3783.6	45.8			G2/5000
FVH	(80°-90°)	134.0	1.6			G2/225
BL	(0°-30°)	51.8	0.6	B0/110		
BM	(30°-60°)	71.0	0.9	B0/220		
BH	(60°-80°)	36.7	0.4	B0/110		G0/110
BVH	(80°-90°)	6.3	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type III Short





REPORT NUMBER: P155278

CATALOG NUMBER: AVM-E06-LED-E-U-T3-HSS-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	56°	57°	58°	59°
0°	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6
2.5°	303.8	298.8	300.5	290.3	283.6	275.1	268.4	266.7	265.0	261.6	263.3
5°	437.2	432.1	420.3	400.1	381.5	352.8	324.1	322.4	317.3	312.3	308.9
7.5°	607.7	599.2	585.7	552.0	506.4	455.8	398.4	393.3	386.5	379.8	373.0
10°	805.2	800.1	774.8	736.0	666.8	584.0	487.8	482.8	467.6	459.1	452.4
12.5°	1012.8	990.8	980.7	913.2	833.9	720.8	597.5	579.0	567.2	555.3	538.5
15°	1169.8	1173.1	1149.5	1095.5	1002.7	871.0	717.4	697.1	680.3	658.3	638.1
17.5°	1311.6	1304.8	1279.5	1245.7	1158.0	1024.6	845.7	818.7	791.7	779.8	751.2
20°	1426.3	1423.0	1402.7	1370.6	1303.1	1174.8	980.7	958.8	928.4	908.1	876.1
22.5°	1517.5	1517.5	1505.7	1487.1	1421.3	1318.3	1124.2	1100.6	1070.2	1044.9	1009.4
25°	1590.1	1588.4	1590.1	1581.6	1537.8	1443.2	1271.1	1244.0	1218.7	1188.3	1154.6
27.5°	1672.8	1676.2	1672.8	1667.7	1649.2	1573.2	1419.6	1401.0	1372.3	1340.3	1306.5
30°	1801.1	1790.9	1789.3	1785.9	1763.9	1716.7	1573.2	1551.3	1529.3	1507.4	1483.7
32.5°	1936.1	1919.2	1914.2	1914.2	1899.0	1856.8	1750.4	1738.6	1706.5	1689.7	1669.4
35°	2089.7	2083.0	2076.2	2077.9	2071.2	2027.3	1939.5	1942.9	1932.7	1899.0	1878.7
37.5°	2314.2	2315.9	2304.1	2282.2	2282.2	2243.3	2192.7	2185.9	2160.6	2152.2	2140.4
40°	2634.9	2626.5	2616.4	2584.3	2572.5	2506.7	2459.4	2442.5	2422.3	2420.6	2407.1
42.5°	3006.3	2996.2	2996.2	2972.5	2948.9	2869.6	2780.1	2768.3	2746.3	2753.1	2748.0
45°	3350.6	3359.1	3370.9	3387.8	3391.2	3357.4	3227.4	3212.2	3200.4	3193.7	3188.6
47.5°	3647.7	3662.9	3701.7	3774.3	3867.2	3879.0	3776.0	3735.5	3727.1	3715.2	3705.1
50°	3860.4	3882.4	3970.1	4111.9	4292.5	4403.9	4348.2	4314.5	4312.8	4280.7	4277.3
52.5°	3981.9	4005.6	4149.1	4363.4	4643.6	4861.4	4930.6	4928.9	4925.5	4896.8	4885.0
55°	4009.0	4034.3	4206.5	4498.5	4898.5	5274.9	5540.0	5546.7	5561.9	5553.5	5553.5
57.5°	3934.7	3966.8	4154.1	4515.4	5031.9	5602.4	6181.4	6220.2	6238.8	6304.6	6380.6
60°	3798.0	3821.6	4009.0	4412.4	5055.5	5901.2	7015.3	7138.5	7234.7	7364.7	7487.9
62.5°	3544.8	3592.0	3771.0	4209.8	4984.6	6245.5	8011.2	8239.0	8426.4	8623.9	8861.9
65°	3237.5	3257.8	3409.7	3792.9	4667.3	6377.2	8561.4	8784.3	9024.0	9234.9	9447.6
67.5°	2852.7	2869.6	3001.2	3165.0	3852.0	5761.1	8019.6	8266.0	8482.1	8656.0	8934.5
70°	1868.6	1905.7	2228.1	2390.2	2692.3	4258.8	6557.8	6795.8	6961.2	7079.4	7401.8
72.5°	1369.0	1392.6	1522.6	1856.8	1931.1	2516.8	4614.9	4873.2	4934.0	5156.8	5307.0
75°	835.6	894.6	1188.3	1590.1	1882.1	1723.4	2764.9	2889.8	3029.9	3192.0	3335.5
77.5°	168.8	192.4	388.2	1095.5	1655.9	1841.6	1650.8	1674.5	1743.7	1758.9	1812.9
80°	27.0	28.7	50.6	472.6	958.8	1488.8	1650.8	1628.9	1590.1	1563.1	1536.1
82.5°	11.8	13.5	21.9	119.8	204.2	496.3	1428.0	1539.4	1667.7	1738.6	1757.2
85°	5.1	5.1	8.4	23.6	30.4	33.8	241.4	319.0	568.8	756.2	871.0
87.5°	3.4	3.4	5.1	5.1	6.8	8.4	11.8	11.8	13.5	15.2	21.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155278

CATALOG NUMBER: AVM-E06-LED-E-U-T3-HSS-8030

CANDELA DISTRIBUTION (continued):

	60°	61°	62°	64°	65°	66°	67°	68°	69°	70°	71°
0°	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6
2.5°	263.3	261.6	261.6	256.6	256.6	254.9	254.9	253.2	253.2	249.8	251.5
5°	307.2	303.8	300.5	295.4	293.7	290.3	287.0	281.9	280.2	276.8	275.1
7.5°	366.3	362.9	356.2	346.0	339.3	332.5	325.8	319.0	314.0	308.9	305.5
10°	438.9	428.7	425.4	405.1	396.7	383.2	374.7	368.0	357.9	349.4	344.3
12.5°	526.7	518.2	501.3	474.3	460.8	449.0	433.8	420.3	410.2	395.0	384.9
15°	617.8	611.0	587.4	557.0	540.2	518.2	503.0	489.5	467.6	457.4	438.9
17.5°	732.6	712.3	688.7	644.8	622.9	604.3	577.3	557.0	543.5	513.1	496.3
20°	850.7	828.8	798.4	749.5	719.1	690.4	668.4	641.4	612.7	592.5	563.8
22.5°	985.8	950.3	926.7	865.9	830.5	800.1	763.0	734.3	705.6	673.5	641.4
25°	1129.3	1093.8	1065.1	995.9	958.8	928.4	884.5	844.0	808.5	773.1	736.0
27.5°	1279.5	1247.4	1215.3	1144.5	1112.4	1070.2	1029.7	982.4	936.8	904.8	854.1
30°	1453.4	1426.3	1390.9	1314.9	1279.5	1235.6	1193.4	1137.7	1093.8	1049.9	1001.0
32.5°	1640.7	1618.8	1581.6	1514.1	1471.9	1434.8	1389.2	1335.2	1272.7	1227.2	1169.8
35°	1868.6	1831.5	1809.5	1745.4	1713.3	1672.8	1625.5	1578.3	1512.4	1448.3	1399.3
37.5°	2128.5	2111.7	2083.0	2022.2	1998.6	1956.4	1926.0	1878.7	1828.1	1747.1	1694.7
40°	2395.2	2383.4	2358.1	2297.3	2273.7	2245.0	2209.6	2164.0	2103.2	2061.0	1983.4
42.5°	2734.5	2716.0	2695.7	2638.3	2592.7	2557.3	2542.1	2503.3	2439.1	2385.1	2324.4
45°	3165.0	3156.5	3129.5	3072.1	3026.6	3002.9	2979.3	2913.5	2871.3	2817.2	2775.0
47.5°	3684.9	3657.9	3644.4	3580.2	3565.0	3546.4	3485.7	3448.5	3387.8	3345.6	3293.3
50°	4247.0	4218.3	4220.0	4142.3	4145.7	4132.2	4086.6	4042.7	3990.4	3953.3	3921.2
52.5°	4851.3	4864.8	4831.0	4854.6	4827.6	4797.2	4788.8	4734.8	4689.2	4687.5	4643.6
55°	5594.0	5572.0	5580.5	5604.1	5567.0	5600.7	5583.8	5514.6	5516.3	5529.8	5479.2
57.5°	6392.4	6424.5	6493.7	6508.9	6573.0	6529.1	6643.9	6561.2	6611.8	6611.8	6578.1
60°	7563.8	7692.1	7859.2	7989.2	8109.1	8070.2	8220.5	8125.9	8193.5	8136.1	8107.4
62.5°	8975.0	9145.5	9343.0	9554.0	9675.5	9705.9	9684.0	9726.2	9660.3	9618.1	9508.4
65°	9653.6	9822.4	9994.5	10247.7	10281.5	10306.8	10296.7	10225.8	10144.8	10024.9	9881.4
67.5°	9089.8	9326.1	9422.3	9714.3	9812.2	9776.8	9788.6	9697.5	9570.9	9452.7	9241.7
70°	7536.8	7806.9	7857.6	8276.2	8392.6	8561.4	8500.7	8473.7	8335.3	8235.7	8002.7
72.5°	5487.6	5698.6	5681.7	6152.7	6132.4	6201.6	6365.4	6358.6	6213.5	6181.4	5985.6
75°	3377.7	3504.3	3497.5	3831.7	3691.6	3671.4	3716.9	3696.7	3560.0	3418.2	3296.6
77.5°	1789.3	1846.7	1785.9	1686.3	1676.2	1563.1	1531.0	1529.3	1424.7	1296.4	1201.8
80°	1507.4	1448.3	1377.4	1232.2	1147.8	1071.9	1001.0	935.1	864.2	769.7	654.9
82.5°	1760.6	1731.9	1681.2	1498.9	1411.2	1259.2	1146.1	1039.8	909.8	811.9	665.1
85°	857.5	855.8	896.3	877.8	845.7	838.9	727.5	703.9	651.6	597.5	499.6
87.5°	23.6	16.9	20.3	16.9	20.3	21.9	15.2	35.4	21.9	20.3	23.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155278

CATALOG NUMBER: AVM-E06-LED-E-U-T3-HSS-8030

CANDELA DISTRIBUTION (continued):

	72°	73°	74°	75°	76°	77°	78°	79°	80°	81°	82°
0°	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6
2.5°	249.8	248.1	246.4	246.4	244.8	244.8	243.1	241.4	241.4	239.7	239.7
5°	271.8	268.4	266.7	265.0	261.6	259.9	256.6	254.9	251.5	249.8	246.4
7.5°	298.8	295.4	288.6	285.3	280.2	278.5	270.1	266.7	263.3	259.9	254.9
10°	332.5	324.1	317.3	310.6	302.1	295.4	288.6	283.6	276.8	268.4	265.0
12.5°	374.7	362.9	352.8	341.0	330.8	320.7	308.9	300.5	290.3	281.9	273.5
15°	422.0	405.1	391.6	374.7	357.9	346.0	334.2	322.4	308.9	297.1	287.0
17.5°	476.0	454.1	435.5	415.2	396.7	379.8	359.5	344.3	329.2	312.3	298.8
20°	533.4	511.5	486.1	464.2	437.2	418.6	393.3	373.0	351.1	334.2	315.7
22.5°	609.4	580.7	548.6	518.2	489.5	460.8	433.8	408.5	381.5	356.2	337.6
25°	698.8	663.4	622.9	592.5	552.0	519.9	486.1	454.1	425.4	393.3	362.9
27.5°	810.2	763.0	719.1	676.9	633.0	592.5	548.6	511.5	472.6	435.5	401.7
30°	940.2	894.6	828.8	781.5	737.6	681.9	638.1	589.1	545.2	491.2	454.1
32.5°	1112.4	1053.3	984.1	921.6	864.2	801.8	741.0	678.6	621.2	572.2	516.5
35°	1336.9	1267.7	1185.0	1105.6	1041.5	965.5	887.9	817.0	751.2	680.3	611.0
37.5°	1620.5	1556.3	1466.9	1370.6	1284.6	1193.4	1112.4	1012.8	925.0	838.9	751.2
40°	1902.4	1843.3	1750.4	1647.5	1536.1	1431.4	1328.4	1215.3	1103.9	995.9	904.8
42.5°	2250.1	2162.3	2062.7	1946.2	1838.2	1713.3	1585.0	1455.0	1321.7	1191.7	1061.7
45°	2687.3	2619.7	2479.6	2354.7	2226.4	2079.6	1920.9	1772.4	1601.9	1448.3	1276.1
47.5°	3219.0	3097.4	2994.5	2879.7	2719.3	2577.5	2375.0	2199.4	1986.8	1782.5	1576.6
50°	3846.9	3779.4	3642.7	3499.2	3325.3	3156.5	2959.0	2705.8	2450.9	2233.2	1951.3
52.5°	4581.2	4485.0	4398.9	4250.3	4073.1	3857.0	3632.5	3357.4	3045.1	2737.9	2437.4
55°	5452.2	5384.7	5302.0	5183.8	4957.6	4712.8	4442.8	4113.6	3743.9	3330.4	2981.0
57.5°	6576.4	6505.5	6426.1	6183.1	6029.5	5729.0	5337.4	4996.4	4598.1	4068.0	3634.2
60°	8110.8	8014.5	7903.1	7705.6	7384.9	6995.0	6574.7	6070.0	5582.2	5003.2	4434.3
62.5°	9422.3	9268.7	9030.7	8775.8	8391.0	7943.6	7415.3	6821.1	6265.8	5614.2	4981.2
65°	9692.4	9481.4	9201.2	8868.7	8472.0	7967.3	7415.3	6846.5	6193.2	5580.5	4944.1
67.5°	8990.2	8745.4	8458.5	8087.1	7709.0	7189.1	6713.1	6134.1	5519.7	4989.7	4420.8
70°	7835.6	7472.7	7179.0	6784.0	6400.8	5992.3	5491.0	5057.2	4557.6	4069.7	3634.2
72.5°	5884.3	5526.5	5259.8	4944.1	4716.2	4284.1	3916.1	3592.0	3296.6	2932.0	2609.6
75°	3171.7	2903.3	2724.4	2580.9	2376.7	2091.4	1915.9	1693.0	1568.1	1416.2	1269.4
77.5°	1034.7	911.5	778.2	648.2	557.0	418.6	405.1	322.4	303.8	295.4	227.9
80°	530.0	408.5	295.4	212.7	162.0	143.5	136.7	130.0	123.2	118.2	109.7
82.5°	531.7	384.9	265.0	184.0	133.4	111.4	104.7	101.3	96.2	91.2	84.4
85°	388.2	287.0	197.5	135.0	92.8	74.3	70.9	65.8	62.5	60.8	54.0
87.5°	25.3	18.6	16.9	15.2	15.2	15.2	16.9	15.2	16.9	16.9	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155278

CATALOG NUMBER: AVM-E06-LED-E-U-T3-HSS-8030

CANDELA DISTRIBUTION (continued):

	83°	84°	85°	86°	87°	88°	89°	90°	95°	105°	115°
0°	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6	229.6
2.5°	238.0	236.3	236.3	234.6	232.9	232.9	231.3	231.3	226.2	217.7	211.0
5°	244.8	241.4	239.7	238.0	236.3	232.9	231.3	229.6	221.1	204.2	190.7
7.5°	249.8	246.4	244.8	241.4	236.3	234.6	231.3	227.9	214.4	190.7	175.6
10°	258.3	253.2	248.1	243.1	238.0	234.6	229.6	226.2	205.9	178.9	163.7
12.5°	266.7	259.9	253.2	244.8	239.7	234.6	229.6	222.8	199.2	168.8	151.9
15°	276.8	266.7	258.3	249.8	241.4	234.6	226.2	221.1	192.4	160.4	145.2
17.5°	287.0	275.1	263.3	251.5	243.1	232.9	226.2	217.7	185.7	153.6	136.7
20°	298.8	281.9	270.1	256.6	244.8	232.9	222.8	214.4	178.9	145.2	128.3
22.5°	315.7	295.4	276.8	261.6	246.4	234.6	222.8	211.0	172.2	138.4	121.5
25°	337.6	312.3	290.3	271.8	253.2	238.0	224.5	212.7	167.1	133.4	113.1
27.5°	369.7	337.6	314.0	288.6	265.0	246.4	229.6	216.1	163.7	128.3	108.0
30°	408.5	376.4	339.3	308.9	283.6	258.3	239.7	219.4	160.4	123.2	101.3
32.5°	465.9	420.3	376.4	339.3	303.8	275.1	248.1	227.9	158.7	114.8	94.5
35°	548.6	486.1	433.8	384.9	335.9	300.5	268.4	241.4	157.0	108.0	87.8
37.5°	666.8	592.5	525.0	455.8	395.0	344.3	300.5	265.0	157.0	103.0	81.0
40°	793.4	697.1	611.0	525.0	447.3	383.2	324.1	280.2	153.6	96.2	74.3
42.5°	936.8	818.7	700.5	594.2	498.0	415.2	346.0	292.0	145.2	89.5	67.5
45°	1129.3	974.0	832.2	695.4	570.5	462.5	374.7	305.5	136.7	84.4	60.8
47.5°	1370.6	1190.0	1006.0	833.9	670.1	533.4	416.9	327.5	131.7	77.6	55.7
50°	1730.2	1473.6	1230.5	1011.1	803.5	624.6	479.4	359.5	126.6	72.6	50.6
52.5°	2125.2	1809.5	1524.2	1242.4	984.1	747.8	552.0	401.7	121.5	67.5	45.6
55°	2606.2	2218.0	1870.3	1504.0	1173.1	891.3	641.4	449.0	114.8	62.5	42.2
57.5°	3200.4	2709.2	2297.3	1850.0	1434.8	1076.9	761.3	528.3	108.0	55.7	37.1
60°	3863.8	3308.4	2790.2	2265.3	1762.3	1323.4	938.5	641.4	101.3	49.0	32.1
62.5°	4341.5	3732.1	3139.6	2550.5	1998.6	1507.4	1082.0	729.2	91.2	42.2	28.7
65°	4336.4	3718.6	3122.8	2542.1	2005.3	1514.1	1087.1	746.1	81.0	37.1	25.3
67.5°	3863.8	3343.9	2812.2	2290.6	1821.3	1377.4	1006.0	692.1	69.2	33.8	21.9
70°	3178.5	2764.9	2344.6	1931.1	1554.6	1179.9	869.3	602.6	59.1	30.4	18.6
72.5°	2321.0	2018.8	1762.3	1470.2	1213.7	931.8	693.8	472.6	47.3	25.3	16.9
75°	1152.9	1031.4	884.5	793.4	676.9	553.7	430.4	275.1	38.8	20.3	15.2
77.5°	219.4	195.8	187.4	162.0	148.5	131.7	116.5	82.7	30.4	15.2	13.5
80°	101.3	92.8	84.4	76.0	67.5	57.4	50.6	43.9	23.6	11.8	15.2
82.5°	79.3	72.6	64.1	57.4	50.6	43.9	37.1	32.1	15.2	10.1	15.2
85°	52.3	45.6	40.5	35.4	30.4	27.0	23.6	20.3	10.1	10.1	10.1
87.5°	15.2	15.2	13.5	13.5	11.8	11.8	10.1	10.1	8.4	8.4	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P155278

CATALOG NUMBER: AVM-E06-LED-E-U-T3-HSS-8030

CANDELA DISTRIBUTION (continued):

	125°	135°	145°	155°	165°	175°	180°
0°	229.6	229.6	229.6	229.6	229.6	229.6	229.6
2.5°	204.2	195.8	192.4	190.7	190.7	192.4	190.7
5°	180.6	172.2	168.8	165.4	165.4	165.4	167.1
7.5°	165.4	157.0	151.9	150.2	148.5	150.2	150.2
10°	151.9	145.2	138.4	135.0	135.0	135.0	135.0
12.5°	141.8	133.4	126.6	124.9	123.2	123.2	123.2
15°	133.4	123.2	118.2	114.8	113.1	113.1	114.8
17.5°	123.2	114.8	108.0	106.3	106.3	106.3	106.3
20°	116.5	106.3	101.3	97.9	97.9	97.9	97.9
22.5°	108.0	99.6	92.8	89.5	89.5	89.5	89.5
25°	101.3	92.8	86.1	82.7	82.7	82.7	82.7
27.5°	94.5	86.1	79.3	76.0	76.0	76.0	76.0
30°	87.8	79.3	72.6	69.2	69.2	69.2	69.2
32.5°	82.7	72.6	65.8	62.5	62.5	64.1	62.5
35°	74.3	65.8	59.1	55.7	55.7	55.7	55.7
37.5°	67.5	59.1	52.3	49.0	49.0	49.0	47.3
40°	62.5	52.3	45.6	42.2	40.5	40.5	40.5
42.5°	54.0	43.9	38.8	35.4	33.8	33.8	33.8
45°	49.0	38.8	32.1	28.7	28.7	28.7	28.7
47.5°	43.9	33.8	27.0	23.6	23.6	25.3	25.3
50°	38.8	28.7	21.9	21.9	21.9	23.6	23.6
52.5°	33.8	25.3	20.3	20.3	21.9	23.6	23.6
55°	30.4	21.9	18.6	20.3	21.9	23.6	23.6
57.5°	27.0	18.6	18.6	20.3	21.9	23.6	23.6
60°	23.6	16.9	16.9	18.6	21.9	23.6	23.6
62.5°	20.3	16.9	16.9	18.6	21.9	23.6	23.6
65°	18.6	16.9	16.9	18.6	21.9	23.6	23.6
67.5°	16.9	15.2	16.9	18.6	20.3	21.9	21.9
70°	15.2	15.2	16.9	18.6	20.3	21.9	21.9
72.5°	15.2	15.2	15.2	16.9	18.6	20.3	20.3
75°	15.2	15.2	15.2	16.9	18.6	20.3	20.3
77.5°	15.2	13.5	13.5	15.2	18.6	20.3	20.3
80°	15.2	13.5	13.5	15.2	16.9	20.3	20.3
82.5°	11.8	11.8	13.5	15.2	16.9	18.6	18.6
85°	10.1	11.8	11.8	13.5	15.2	18.6	18.6
87.5°	8.4	8.4	10.1	11.8	13.5	15.2	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)