

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702381

Luminaire Tested: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC

Issue Date: 8/30/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P702381  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/30/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: SHAPER  
Catalog Number: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC  
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, CLEAR INSIDE, CLEAR OUTSIDE GLA  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 816.0 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.89  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P702381

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC

### Luminous Intensity Polar Plot



TEST NUMBER: P702381

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	101	96	92	104	99	95	91	96	92	89		92	90	87		90	87	85	83
3	100	93	87	83	98	91	86	82	88	84	81		86	82	79		84	81	78	76
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	71	70
5	89	79	73	68	87	78	72	68	77	71	67		75	70	66		73	69	66	64
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61	59
7	79	69	62	58	78	68	62	57	67	61	57		66	60	57		64	60	56	55
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61	56	52	51
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57	52	49	48
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54	49	46	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	54469
5°	52359
10°	49811
15°	44902
20°	40567
25°	34603
30°	29531
35°	21273
40°	16233
45°	10915
50°	6760
55°	4857
60°	3536
65°	2408
70°	2041
75°	1664
80°	1540
85°	1198

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10915 cd/sqm

TEST NUMBER: P702381

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.9	9.2
10°-20°	187.5	23.0
20°-30°	221.0	27.1
30°-40°	171.8	21.1
40°-50°	94.3	11.6
50°-60°	39.3	4.8
60°-70°	16.6	2.0
70°-80°	7.1	0.9
80°-90°	2.0	0.2
90°-100°	0.9	0.1
100°-110°	0.5	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	483.4	59.2
0°-40°	655.3	80.3
0°-60°	788.8	96.7
0°-90°	814.6	99.8
90°-120°	1.4	0.2
90°-150°	1.4	0.2
90°-180°	1.0	0.1
0°-180°	816.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	835	
5°	800	75
15°	665	188
25°	481	221
35°	267	172
45°	118	94
55°	43	39
65°	16	17
75°	7	7
85°	2	2
90°	1	0
95°	1	1
105°	1	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702381

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	834.9
2.5°	825.8
5°	799.5
7.5°	775.7
10°	751.9
12.5°	708.3
15°	664.8
17.5°	636.8
20°	584.3
22.5°	521.0
25°	480.7
27.5°	441.3
30°	392.0
32.5°	332.0
35°	267.1
37.5°	220.2
40°	190.6
42.5°	161.9
45°	118.3
47.5°	85.5
50°	66.6
52.5°	52.6
55°	42.7
57.5°	34.5
60°	27.1
62.5°	19.7
65°	15.6
67.5°	13.1
70°	10.7
72.5°	8.2
75°	6.6
77.5°	4.9
80°	4.1
82.5°	2.5
85°	1.6
87.5°	0.8
90°	0.8
92.5°	0.8
95°	0.8
97.5°	0.8
100°	0.8
102.5°	0.8
105°	0.8
107.5°	0.0
110°	0.0

TEST NUMBER: P702381

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GCC

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)