

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702382

Luminaire Tested: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702382
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-15)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, CLEAR OUTSIDE C
KIT.
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 722.6 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.74
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702382

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC

Luminous Intensity Polar Plot



TEST NUMBER: P702382

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	109	105	101	97	106	102	99	96	98	95	92		94	91	89		90	88	86	84
2	101	93	87	82	98	91	86	81	88	83	79		84	80	77		81	78	75	73
3	93	84	76	71	91	82	75	70	79	73	69		76	71	67		73	69	66	64
4	86	76	68	62	84	74	67	61	72	65	60		69	64	60		67	62	59	57
5	81	69	61	55	78	68	60	55	66	59	54		64	58	53		62	57	53	51
6	75	63	55	50	73	62	55	49	60	54	49		59	53	48		57	52	48	46
7	71	58	51	45	69	58	50	45	56	49	44		54	49	44		53	48	44	42
8	66	54	47	41	65	54	46	41	52	46	41		51	45	41		50	44	40	38
9	63	51	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	47	40	35	46	39	35		45	39	35		44	38	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40795
5°	36649
10°	31616
15°	19935
20°	14234
25°	10933
30°	8807
35°	7408
40°	6535
45°	5590
50°	4488
55°	3495
60°	2749
65°	2172
70°	1756
75°	1398
80°	1134
85°	891

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5590 cd/sqm

TEST NUMBER: P702382

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.9	8.1
10°-20°	116.2	16.1
20°-30°	115.1	15.9
30°-40°	114.7	15.9
40°-50°	109.5	15.2
50°-60°	81.7	11.3
60°-70°	55.4	7.7
70°-80°	36.1	5.0
80°-90°	22.0	3.0
90°-100°	11.4	1.6
100°-110°	1.5	0.2
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	290.2	40.2
0°-40°	404.9	56.0
0°-60°	596.2	82.5
0°-90°	709.7	98.2
90°-120°	13.0	1.8
90°-150°	13.0	1.8
90°-180°	13.0	1.8
0°-180°	722.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	625	
5°	626	59
15°	403	116
25°	248	115
35°	182	115
45°	143	109
55°	90	82
65°	55	55
75°	34	36
85°	20	18
90°	15	8
95°	11	8
105°	1	2
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P702382

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC

CANDELA DISTRIBUTION (FULL):

0°	
0°	625.3
2.5°	626.2
5°	626.2
7.5°	621.2
10°	591.7
12.5°	500.4
15°	402.7
17.5°	347.6
20°	306.5
22.5°	273.6
25°	248.2
27.5°	226.8
30°	208.7
32.5°	193.1
35°	181.6
37.5°	172.6
40°	164.3
42.5°	155.3
45°	143.0
47.5°	129.8
50°	115.9
52.5°	102.7
55°	90.4
57.5°	79.7
60°	70.7
62.5°	62.5
65°	55.1
67.5°	49.3
70°	43.6
72.5°	38.6
75°	33.7
77.5°	29.6
80°	26.3
82.5°	23.0
85°	19.7
87.5°	17.3
90°	14.8
92.5°	13.1
95°	10.7
97.5°	8.2
100°	4.9
102.5°	2.5
105°	0.8
107.5°	0.0
110°	0.0

TEST NUMBER: P702382

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9030-4LBW1LI-GFC

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)