

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702386

Luminaire Tested: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-CQ

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-13)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-CQ
Description: FARALLON 6" LED GLASS DOWNLIGHT CYLINDRICAL FROSTED, QUADRATE ETCHED GLASS KIT.
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 712.8 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.54
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702386

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-CQ

Luminous Intensity Polar Plot



TEST NUMBER: P702386

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-CQ

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	110	105	102	98	107	103	100	97	98	96	93		94	92	90		90	89	87	85
2	102	95	89	84	99	93	87	83	89	84	81		85	82	78		82	79	76	74
3	95	86	79	73	92	84	78	72	81	75	71		78	73	70		75	71	68	66
4	88	78	71	65	86	77	70	64	74	68	63		72	67	62		69	65	61	59
5	83	72	64	58	81	71	63	58	68	62	57		66	61	57		64	60	56	54
6	78	66	59	53	76	65	58	53	63	57	52		62	56	52		60	55	51	49
7	73	62	54	49	71	61	54	49	59	53	48		58	52	48		56	51	47	46
8	69	58	50	45	68	57	50	45	55	49	45		54	48	44		53	48	44	42
9	66	54	47	42	64	53	47	42	52	46	42		51	45	41		50	45	41	40
10	62	51	44	40	61	50	44	39	49	43	39		48	43	39		47	42	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71119
5°	51087
10°	32413
15°	25954
20°	17856
25°	9898
30°	7760
35°	6519
40°	5728
45°	4750
50°	3900
55°	3089
60°	2457
65°	1935
70°	1542
75°	1245
80°	1005
85°	828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4750 cd/sqm

TEST NUMBER: P702386

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-CQ

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	10.5
10°-20°	143.2	20.1
20°-30°	111.1	15.6
30°-40°	101.1	14.2
40°-50°	93.8	13.2
50°-60°	72.2	10.1
60°-70°	49.4	6.9
70°-80°	32.1	4.5
80°-90°	20.0	2.8
90°-100°	11.6	1.6
100°-110°	3.7	0.5
110°-120°	0.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	328.9	46.1
0°-40°	430.0	60.3
0°-60°	596.0	83.6
0°-90°	697.5	97.8
90°-120°	15.4	2.2
90°-150°	15.4	2.2
90°-180°	15.0	2.1
0°-180°	712.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1090	
5°	873	75
15°	524	143
25°	225	111
35°	160	101
45°	122	94
55°	80	72
65°	49	49
75°	30	32
85°	18	16
90°	13	8
95°	11	8
105°	3	4
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702386

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-CQ

CANDELA DISTRIBUTION (FULL):

0°	
0°	1090.1
2.5°	1041.9
5°	872.9
7.5°	709.8
10°	606.6
12.5°	555.9
15°	524.3
17.5°	483.5
20°	384.5
22.5°	268.8
25°	224.7
27.5°	203.0
30°	183.9
32.5°	168.9
35°	159.8
37.5°	154.0
40°	144.0
42.5°	132.3
45°	121.5
47.5°	110.7
50°	100.7
52.5°	89.9
55°	79.9
57.5°	71.6
60°	63.2
62.5°	55.8
65°	49.1
67.5°	44.1
70°	38.3
72.5°	34.1
75°	30.0
77.5°	26.6
80°	23.3
82.5°	20.8
85°	18.3
87.5°	15.8
90°	13.3
92.5°	12.5
95°	10.8
97.5°	9.2
100°	6.7
102.5°	5.0
105°	3.3
107.5°	1.7
110°	0.8

TEST NUMBER: P702386

CATALOG NUMBER: 340-6C-10-D010 / 340-EU4C-1020-9035-4LBW1LI-CQ

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)