

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P148110

Luminaire Tested: **AVS-E04-LED-E-U-5WQ**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P148110
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E04-LED-E-U-5WQ
Description: VISION SITE SMALL LED LUMINAIRE
(4) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (84) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12735.2 lumens
Efficiency: N/A
Efficacy: 131.0 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B4 - U0 - G2


Input Watts (W): 97.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P148110
 CATALOG NUMBER: AVS-E04-LED-E-U-5WQ

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 1.9 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P148110
CATALOG NUMBER: AVS-E04-LED-E-U-5WQ

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P148110

CATALOG NUMBER: AVS-E04-LED-E-U-5WQ

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6367.6	0.0	6367.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6367.6	0.0	6367.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	12735.2	0.0	12735.2
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.4	0.5
10°-20°	234.5	1.8
20°-30°	474.8	3.7
30°-40°	796.1	6.3
40°-50°	1404.2	11.0
50°-60°	2476.3	19.4
60°-70°	3780.6	29.7
70°-80°	3159.1	24.8
80°-90°	343.3	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12735.2	100.0
0°-180°	12735.2	100.0



REPORT NUMBER: P148110


CATALOG NUMBER: AVS-E04-LED-E-U-5WQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	387.9	3.0			
FM	(30°-60°)	2338.3	18.4			
FH	(60°-80°)	3469.8	27.2			G2/5000
FVH	(80°-90°)	171.6	1.3			G2/225
BL	(0°-30°)	387.9	3.0	B1/500		
BM	(30°-60°)	2338.3	18.4	B2/2500		
BH	(60°-80°)	3469.8	27.2	B4/5000		G2/5000
BVH	(80°-90°)	171.6	1.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G2

Type V Short





REPORT NUMBER: P148110

CATALOG NUMBER: AVS-E04-LED-E-U-5WQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	661.3	661.3	661.3	661.3	661.3	661.3	661.3	661.3	661.3	661.3	661.3
2.5°	666.6	668.0	666.6	666.6	666.6	666.6	666.6	665.3	665.3	665.3	666.6
5°	680.0	681.3	680.0	681.3	681.3	681.3	681.3	680.0	680.0	680.0	680.0
7.5°	701.3	701.3	701.3	702.7	701.3	701.3	702.7	701.3	701.3	701.3	701.3
10°	732.0	730.7	730.7	730.7	730.7	730.7	732.0	732.0	732.0	730.7	730.7
12.5°	769.3	768.0	769.3	769.3	770.7	770.7	770.7	770.7	770.7	770.7	769.3
15°	814.7	814.7	814.7	816.0	818.7	818.7	817.3	818.7	818.7	818.7	818.7
17.5°	865.3	868.0	865.3	866.6	868.0	866.6	869.3	870.7	872.0	870.7	866.6
20°	917.3	918.7	918.7	918.7	918.7	921.3	922.7	922.7	926.6	925.3	924.0
22.5°	966.6	969.3	969.3	970.7	970.7	974.7	974.7	974.7	977.3	980.0	977.3
25°	1018.7	1017.3	1017.3	1020.0	1021.3	1026.6	1026.6	1029.3	1033.4	1034.7	1032.0
27.5°	1065.3	1064.0	1064.0	1068.0	1069.3	1076.0	1076.0	1081.3	1084.0	1085.3	1082.7
30°	1114.7	1114.7	1113.4	1117.3	1121.3	1126.6	1129.3	1134.7	1138.7	1140.0	1137.3
32.5°	1173.4	1170.7	1172.0	1174.7	1177.3	1182.7	1186.6	1193.4	1198.7	1200.0	1197.3
35°	1240.0	1236.0	1237.3	1240.0	1244.0	1252.0	1258.7	1262.7	1270.7	1273.4	1268.0
37.5°	1313.4	1314.7	1313.4	1320.0	1326.6	1336.0	1344.0	1349.3	1357.3	1361.3	1357.3
40°	1417.3	1413.4	1417.3	1424.0	1434.7	1446.6	1462.7	1466.6	1474.7	1482.7	1473.4
42.5°	1552.0	1549.3	1558.7	1564.0	1576.0	1589.3	1609.3	1620.0	1632.0	1637.3	1629.3
45°	1728.0	1728.0	1738.7	1740.0	1758.7	1776.0	1804.0	1817.3	1840.0	1840.0	1840.0
47.5°	1922.7	1930.7	1937.3	1950.7	1964.0	1996.0	2024.0	2053.4	2074.7	2077.3	2073.4
50°	2124.0	2132.0	2152.0	2170.7	2200.0	2240.0	2270.7	2309.3	2328.0	2344.0	2338.7
52.5°	2346.6	2348.0	2372.0	2396.0	2438.7	2482.7	2532.0	2572.0	2605.3	2620.0	2608.0
55°	2590.7	2593.4	2614.7	2640.0	2688.0	2738.7	2800.0	2841.3	2884.0	2910.7	2890.7
57.5°	2854.7	2856.0	2877.3	2908.0	2965.3	3016.0	3074.7	3133.4	3173.4	3197.3	3184.0
60°	3146.6	3153.4	3169.3	3208.0	3262.7	3316.0	3374.7	3426.6	3473.4	3498.7	3485.3
62.5°	3458.7	3465.3	3488.0	3518.7	3566.6	3625.3	3681.3	3748.0	3786.6	3814.7	3794.7
65°	3668.0	3680.0	3716.0	3757.3	3828.0	3904.0	3969.3	4060.0	4106.6	4140.0	4121.3
67.5°	3681.3	3688.0	3732.0	3794.7	3889.3	4004.0	4137.3	4278.7	4370.7	4414.7	4382.7
69°	3590.7	3600.0	3642.7	3713.4	3818.7	3952.0	4110.7	4286.6	4428.0	4493.4	4462.7
70°	3488.0	3508.0	3554.7	3632.0	3734.7	3874.7	4038.7	4226.6	4392.0	4481.3	4458.7
72.5°	3272.0	3277.3	3308.0	3369.3	3448.0	3564.0	3718.7	3896.0	4053.4	4181.3	4200.0
75°	2904.0	2921.3	2944.0	2985.3	3025.3	3109.3	3213.4	3334.7	3426.6	3525.3	3529.3
77.5°	2194.7	2246.6	2264.0	2273.4	2290.7	2357.3	2448.0	2553.4	2629.3	2645.3	2642.7
80°	985.3	1054.7	1070.7	1146.6	1193.4	1304.0	1442.7	1604.0	1712.0	1724.0	1694.7
82.5°	193.4	206.6	241.3	301.3	410.7	476.0	566.6	680.0	784.0	844.0	808.0
85°	64.0	68.0	78.7	86.6	100.0	113.4	137.3	170.7	212.0	234.7	209.3
87.5°	25.3	25.3	29.3	32.0	34.7	34.7	34.7	32.0	30.7	25.3	22.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P148110

CATALOG NUMBER: AVS-E04-LED-E-U-5WQ

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	661.3	661.3	661.3	661.3	661.3	661.3	661.3	661.3
2.5°	665.3	665.3	665.3	665.3	665.3	665.3	665.3	665.3
5°	680.0	678.7	678.7	677.3	677.3	677.3	677.3	677.3
7.5°	700.0	698.7	697.3	698.7	697.3	697.3	697.3	697.3
10°	730.7	728.0	726.6	725.3	725.3	725.3	724.0	724.0
12.5°	766.6	766.6	765.3	764.0	761.3	762.7	761.3	758.7
15°	816.0	813.4	812.0	810.7	808.0	808.0	808.0	806.6
17.5°	865.3	862.7	862.7	858.7	857.3	857.3	857.3	858.7
20°	920.0	916.0	913.4	910.7	908.0	909.3	906.6	909.3
22.5°	974.7	969.3	966.6	962.7	958.7	958.7	957.3	954.7
25°	1028.0	1021.3	1018.7	1014.7	1009.3	1009.3	1006.6	1004.0
27.5°	1078.7	1072.0	1069.3	1061.3	1056.0	1054.7	1052.0	1050.7
30°	1134.7	1126.6	1122.7	1114.7	1106.6	1105.3	1101.3	1101.3
32.5°	1193.4	1185.3	1182.7	1170.7	1164.0	1164.0	1161.3	1158.7
35°	1266.6	1254.7	1252.0	1240.0	1230.7	1230.7	1228.0	1229.3
37.5°	1353.4	1344.0	1334.7	1325.3	1314.7	1313.4	1310.7	1308.0
40°	1469.3	1458.7	1448.0	1434.7	1425.3	1422.7	1418.7	1417.3
42.5°	1624.0	1613.4	1592.0	1581.3	1572.0	1564.0	1562.7	1561.3
45°	1821.3	1808.0	1793.4	1773.4	1761.3	1744.0	1741.3	1734.7
47.5°	2058.7	2033.4	2008.0	1990.7	1972.0	1952.0	1948.0	1937.3
50°	2310.7	2290.7	2248.0	2220.0	2190.7	2170.7	2157.3	2153.4
52.5°	2581.3	2544.0	2501.3	2464.0	2421.3	2394.7	2370.7	2364.0
55°	2864.0	2810.7	2757.3	2713.4	2670.7	2638.7	2616.0	2605.3
57.5°	3146.6	3088.0	3029.3	2981.3	2945.3	2904.0	2881.3	2876.0
60°	3441.3	3385.3	3325.3	3277.3	3233.4	3197.3	3184.0	3158.7
62.5°	3753.4	3694.7	3638.7	3592.0	3536.0	3510.7	3488.0	3473.4
65°	4060.0	3992.0	3921.3	3872.0	3816.0	3780.0	3752.0	3732.0
67.5°	4297.3	4194.7	4100.0	4017.3	3941.3	3885.3	3849.3	3830.7
69°	4364.0	4236.0	4114.7	4006.6	3917.3	3854.7	3814.7	3796.0
70°	4356.0	4214.7	4081.3	3962.7	3865.3	3798.7	3760.0	3725.3
72.5°	4109.3	3980.0	3832.0	3702.7	3614.7	3550.7	3512.0	3493.4
75°	3506.6	3420.0	3313.4	3213.4	3149.3	3112.0	3064.0	3065.3
77.5°	2553.4	2556.0	2484.0	2381.3	2309.3	2296.0	2274.7	2253.4
80°	1584.0	1457.3	1374.7	1264.0	1182.7	1112.0	1081.3	1014.7
82.5°	730.7	570.7	442.7	334.7	257.3	201.3	176.0	144.0
85°	162.7	124.0	102.7	82.7	70.7	65.3	53.4	49.3
87.5°	22.7	20.0	18.7	17.3	14.7	10.7	8.0	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)