

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: SHAPER

Report Number: P702425

Luminaire Tested: 340-6C-15-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF

Issue Date: 8/30/2023

Test Information

Test Method: LM-79-2019
Report Number: P702425
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1705-068-14)
Test Lab: INNOVATION CENTER
Issue Date: 8/30/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: SHAPER
Catalog Number: 340-6C-15-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF
Description: FARALLON 6" LED GLASS DOWNLIGHT. GLASS-IN-A-GLASS, FROSTED INSIDE, FROSTED OUTSIDE KIT.
Light Source: 2400K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 871.9 lumens
Efficiency: N/A
Efficacy: 55.2 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.63
Luminous Opening: Vertical Cylinder (Dia: 0.46' x H: 0.49')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P702425

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF

Luminous Intensity Polar Plot



TEST NUMBER: P702425

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109		104	104	104		99	99	99	96
1	107	102	97	93	104	99	95	91	94	91	88		90	87	84		85	83	81	79
2	98	89	82	77	95	87	81	75	83	78	73		79	75	71		76	72	69	66
3	90	79	71	65	87	77	70	64	74	68	62		71	65	61		68	63	59	57
4	83	71	63	56	80	70	62	56	67	60	54		64	58	53		61	56	52	50
5	77	65	56	49	75	63	55	49	61	54	48		58	52	47		56	51	47	44
6	72	59	50	44	70	58	50	44	56	49	43		54	47	43		52	46	42	40
7	67	54	46	40	65	53	45	40	51	44	39		50	43	39		48	43	38	36
8	63	50	42	37	61	49	42	36	48	41	36		46	40	36		45	39	35	33
9	60	47	39	34	58	46	39	34	45	38	33		43	37	33		42	37	33	31
10	56	44	36	31	55	43	36	31	42	35	31		41	35	31		40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49146
5°	43590
10°	36329
15°	20331
20°	13588
25°	10497
30°	8486
35°	7074
40°	6304
45°	5782
50°	5275
55°	4732
60°	4219
65°	3650
70°	3129
75°	2647
80°	2246
85°	1878

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5782 cd/sqm

TEST NUMBER: P702425

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.2	7.9
10°-20°	120.6	13.8
20°-30°	110.6	12.7
30°-40°	109.9	12.6
40°-50°	114.2	13.1
50°-60°	109.8	12.6
60°-70°	91.8	10.5
70°-80°	67.7	7.8
80°-90°	45.8	5.3
90°-100°	26.6	3.1
100°-110°	5.5	0.6
110°-120°	0.1	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.4	34.5
0°-40°	410.3	47.1
0°-60°	634.3	72.7
0°-90°	839.7	96.3
90°-120°	32.3	3.7
90°-150°	32.3	3.7
90°-180°	32.0	3.7
0°-180°	871.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	753	
5°	745	69
15°	411	121
25°	238	111
35°	173	110
45°	148	114
55°	122	110
65°	93	92
75°	64	68
85°	42	36
90°	33	18
95°	26	18
105°	4	6
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P702425

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF

CANDELA DISTRIBUTION (FULL):

0°	
0°	753.3
2.5°	752.3
5°	744.8
7.5°	727.8
10°	679.9
12.5°	549.0
15°	410.7
17.5°	337.3
20°	292.6
22.5°	261.8
25°	238.3
27.5°	219.2
30°	201.1
32.5°	185.1
35°	173.4
37.5°	164.9
40°	158.5
42.5°	153.2
45°	147.9
47.5°	142.6
50°	136.2
52.5°	129.8
55°	122.4
57.5°	116.0
60°	108.5
62.5°	100.0
65°	92.6
67.5°	85.1
70°	77.7
72.5°	70.2
75°	63.8
77.5°	57.5
80°	52.1
82.5°	46.8
85°	41.5
87.5°	37.2
90°	33.0
92.5°	29.8
95°	25.5
97.5°	19.2
100°	12.8
102.5°	7.4
105°	4.3
107.5°	2.1
110°	1.1

TEST NUMBER: P702425

CATALOG NUMBER: 340-6C-15-D010 / 340-EU4C-1020-9024-4LBW1LI-GFF

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)